

Power Splitter/Combiner

ZX10-2-332-S+

2 Way-0° 50Ω 1600 to 3300 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1.5W max.
Internal Dissipation (as a combiner)	0.75W max.

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

SUM PORT	3
PORT 1	1
PORT 2	2

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.74	.90	.54	.50	.04	.16	.29
18.80	22.86	13.72	12.70	1.02	4.06	7.37

H	J	K	L	M	N	wt
.37	--	.122	.496	.106	.122	grams
9.40	--	3.10	12.60	2.69	3.10	20.0

Features

- wide bandwidth, 1600 to 3300 MHz
- excellent isolation, 24 dB typ.
- excellent amplitude unbalance, 0.02 dB typ.
- very good phase unbalance, 1 deg. typ.
- small size
- low cost
- protected under U.S. Patent 6,790,049

Applications

- WCDMA
- DCS
- PCS
- WiMax
- radar
- instrumentation
- navigation




Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 3.0 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)
f_L - f_U	Typ.	Min.	Typ.	Max.	Max.	Max.
1600-3300	24	17	0.8	1.5	5.0	0.2
2600-3200	28	19	0.8	1.5	5.0	0.2

Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
1600.0	4.10	4.10	0.01	22.27	0.31	1.21	1.17	1.19
1700.0	3.95	3.95	0.01	24.91	0.35	1.01	1.11	1.13
1900.0	3.90	3.89	0.01	21.49	0.38	1.29	1.14	1.14
2000.0	3.90	3.90	0.01	20.58	0.40	1.38	1.17	1.17
2100.0	3.91	3.90	0.01	20.24	0.42	1.44	1.20	1.19
2300.0	3.91	3.90	0.01	20.87	0.47	1.46	1.22	1.22
2400.0	3.90	3.89	0.01	21.65	0.48	1.43	1.23	1.23
2600.0	3.87	3.86	0.01	24.18	0.53	1.33	1.23	1.24
2700.0	3.86	3.85	0.00	26.19	0.56	1.26	1.24	1.24
2800.0	3.85	3.85	0.00	28.92	0.61	1.19	1.24	1.25
2900.0	3.84	3.85	0.01	32.85	0.68	1.13	1.25	1.26
3000.0	3.85	3.86	0.01	35.17	0.75	1.08	1.27	1.27
3100.0	3.87	3.88	0.01	31.33	0.82	1.10	1.30	1.30
3200.0	3.91	3.92	0.01	27.12	0.89	1.17	1.33	1.33
3300.0	3.95	3.96	0.02	24.05	0.95	1.26	1.37	1.37

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



2 Way-0° Power Splitter/Combiner

ZX10-2-332-S+

Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB) 1-2	PHASE UNBALANCE (deg.)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1600	4.10	4.10	0.01	22.27	0.31	1600	1.21	1.17	1.19
1650	4.01	4.01	0.00	24.32	0.33	1650	1.09	1.14	1.15
1700	3.95	3.95	0.01	24.91	0.35	1700	1.01	1.11	1.13
1750	3.92	3.92	0.01	24.21	0.36	1750	1.09	1.11	1.12
1800	3.90	3.90	0.01	23.17	0.37	1800	1.16	1.11	1.12
1850	3.89	3.89	0.00	22.25	0.38	1850	1.23	1.13	1.13
1900	3.90	3.89	0.01	21.49	0.38	1900	1.29	1.14	1.14
1950	3.90	3.89	0.01	20.94	0.40	1950	1.34	1.16	1.15
2000	3.90	3.90	0.01	20.58	0.40	2000	1.38	1.17	1.17
2050	3.91	3.90	0.01	20.36	0.41	2050	1.41	1.19	1.18
2100	3.91	3.90	0.01	20.24	0.42	2100	1.44	1.20	1.19
2150	3.91	3.90	0.01	20.29	0.44	2150	1.45	1.21	1.20
2200	3.91	3.90	0.01	20.39	0.45	2200	1.46	1.21	1.21
2250	3.91	3.90	0.01	20.57	0.46	2250	1.46	1.22	1.22
2300	3.91	3.90	0.01	20.87	0.47	2300	1.46	1.22	1.22
2350	3.91	3.89	0.01	21.22	0.48	2350	1.44	1.23	1.23
2400	3.90	3.89	0.01	21.65	0.48	2400	1.43	1.23	1.23
2450	3.89	3.88	0.01	22.12	0.50	2450	1.41	1.23	1.23
2500	3.88	3.87	0.01	22.76	0.51	2500	1.38	1.23	1.23
2550	3.88	3.87	0.01	23.42	0.52	2550	1.36	1.23	1.24
2600	3.87	3.86	0.01	24.18	0.53	2600	1.33	1.23	1.24
2650	3.86	3.86	0.01	25.12	0.55	2650	1.30	1.23	1.24
2700	3.86	3.85	0.00	26.19	0.56	2700	1.26	1.24	1.24
2750	3.85	3.85	0.00	27.47	0.59	2750	1.23	1.24	1.24
2800	3.85	3.85	0.00	28.92	0.61	2800	1.19	1.24	1.25
2850	3.85	3.85	0.00	30.85	0.64	2850	1.16	1.25	1.25
2900	3.84	3.85	0.01	32.85	0.68	2900	1.13	1.25	1.26
2950	3.85	3.85	0.00	34.73	0.71	2950	1.10	1.26	1.27
3000	3.85	3.86	0.01	35.17	0.75	3000	1.08	1.27	1.27
3050	3.86	3.87	0.01	33.64	0.79	3050	1.08	1.29	1.29
3100	3.87	3.88	0.01	31.33	0.82	3100	1.10	1.30	1.30
3150	3.89	3.90	0.01	29.01	0.85	3150	1.13	1.31	1.32
3200	3.91	3.92	0.01	27.12	0.89	3200	1.17	1.33	1.33
3250	3.92	3.94	0.01	25.48	0.94	3250	1.21	1.35	1.35
3300	3.95	3.96	0.02	24.05	0.95	3300	1.26	1.37	1.37

¹Total Loss = Insertion Loss + 3dB Splitter Loss




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


IF/RF MICROWAVE COMPONENTS

REV. OR
ZX10-2-332-S+
12/19/2018
Page 1 of 1

Typical Performance Curves



Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT, GRAM
FL905	.74 (18.80)	.90 (22.86)	.54 (13.72)	.50 (12.70)	.04 (1.02)	.16 (4.06)	.29 (7.37)	.37 (9.40)	- -	.122 (3.10)	.496 (12.60)	.106 (2.69)	.122 (3.10)	20.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$.

Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Notes:

- Case material: Brass.
- Case finish: Nickel plate.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I