



CASE #	A		B	C1	C2	D	E1	E2	F AF047-A-1M+	T		WEIGHT GRAMS
	INCH	MM								INCH	MM	
AAG3495-6	6.00	152.40								.10	2.54	21.2
AAG3495-12	12.00	304.80								.15	3.81	29.0
			.32 [8.1]	.236 [6.00]	.276 [7.00]	.32 [8.1]	.236 [6.00]	.276 [7.00]	.221±.008 [5.6±0.2]			

Unless Otherwise Specified dimensions are in inches [mm],
 Tolerances: 2 Pl.±0.03[0.76]; 3 Pl. ±0.015[0.38] inches[mm]

Notes:

1. AP-140 Armor Flexible Cable.
2. "A" Represents Length of Cable.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS