





Case Style

DG

Outline Dimensions

DG1677-8



Suggested Layout,
Tolerance to be within $\pm 0.050[0.002]$

NOTES:

1.  DENOTES METALLIZATION

Weight: .056 grams

Dimensions are in mm [inches]. Tolerances: 2 Pl. $\pm 0.254[0.01]$; 3 Pl. $\pm 0.127[0.005]$ mm [Inches]

Notes:

1. Case material: Plastic.
2. Termination finish: PPF (NiPdAu Plating $0.5 \mu\text{m}/0.02\mu\text{m}/0.05\mu\text{m}$)

 **Mini-Circuits**[®]
ISO 9001 ISO 14001 CERTIFIED

ALL NEW



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS