

Adaptor 1.35mm-Female to 1.85mm-Male**135F-185M+***Typical Performance Data (+25°C)*

FREQ.	INSERTION LOSS	1.35mm-FEMALE VSWR	1.85mm-MALE VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	0.01	1.01	1.01
0.2	0.01	1.01	1.01
0.4	0.02	1.01	1.01
0.6	0.03	1.01	1.01
0.8	0.04	1.01	1.02
1.0	0.04	1.02	1.02
3.0	0.08	1.02	1.03
5.0	0.10	1.06	1.06
7.0	0.10	1.03	1.03
9.0	0.10	1.02	1.05
11.0	0.09	1.03	1.03
13.0	0.10	1.04	1.04
15.0	0.11	1.01	1.02
17.0	0.12	1.01	1.03
19.0	0.13	1.04	1.04
21.0	0.14	1.05	1.03
23.0	0.15	1.03	1.02
25.0	0.16	1.04	1.03
27.0	0.17	1.04	1.04
29.0	0.17	1.04	1.06
31.0	0.18	1.07	1.09
33.0	0.18	1.07	1.05
35.0	0.19	1.08	1.09
37.0	0.21	1.10	1.11
39.0	0.19	1.03	1.02
41.0	0.20	1.10	1.10
43.0	0.21	1.05	1.06
45.0	0.19	1.04	1.06
47.0	0.22	1.09	1.08
49.0	0.23	1.02	1.03
51.0	0.23	1.07	1.05
53.0	0.24	1.05	1.06
55.0	0.24	1.09	1.10
57.0	0.23	1.08	1.09
59.0	0.22	1.09	1.13
61.0	0.23	1.09	1.08
63.0	0.23	1.06	1.05
65.0	0.26	1.07	1.07
67.0	0.22	1.06	1.09