

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
100	48.97	1123.66
200	43.23	1008.23
300	40.20	719.63
400	38.36	459.57
500	37.25	275.83
600	36.61	205.12
700	36.50	149.08
800	37.06	111.50
900	39.04	91.31
1000	45.89	70.29
1100	42.59	56.32
1200	30.84	43.55
1300	23.78	33.13
1400	17.95	22.37
1500	12.33	12.42
1600	6.74	4.92
1650	4.45	2.78
1700	3.01	1.61
1720	3.01	1.61
1740	3.01	1.61
1760	2.41	1.12
1780	2.41	1.12
1800	2.25	1.24
1820	2.25	1.24
1840	2.25	1.24
1860	2.23	1.35
1880	2.23	1.35
1900	2.23	1.33
1920	2.24	1.31
1940	2.26	1.29
1960	2.29	1.29
1980	2.34	1.30
2000	2.40	1.33
2020	2.48	1.37
2040	2.57	1.41
2060	2.67	1.46
2080	2.79	1.50
2100	2.91	1.53
2120	2.91	1.53
2140	2.91	1.53
2160	3.31	1.53
2180	3.31	1.53
2200	3.93	1.41
2220	3.93	1.41
2240	3.93	1.41
2260	5.20	1.32
2280	5.20	1.32
2300	8.21	2.10
2400	21.14	6.95
2600	36.41	16.66
2800	35.78	19.275
3000	36.61	16.68
3500	39.59	9.71
4000	64.43	14.75
4500	43.01	16.95
5000	38.75	8.65
5500	60.02	5.89
6000	35.56	16.38
6500	31.29	30.44
7000	27.84	35.08
7500	23.19	31.89
8000	13.85	3.69
8500	21.97	16.46
9000	31.21	36.35
9500	39.65	32.49
10000	32.29	20.56