

Fixed Attenuator**BW-W6-0.5W114+****Typical Performance Data (+25°C)**

FREQ.	ATTENUATION	MALE VSWR	FEMALE VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	5.4	1.0	1.0
0.1	5.4	1.0	1.0
0.5	5.5	1.0	1.0
1.0	5.5	1.0	1.0
3.0	5.6	1.1	1.1
6.0	5.7	1.1	1.1
9.0	5.7	1.0	1.1
12.0	5.7	1.0	1.0
15.0	5.8	1.0	1.0
18.0	5.8	1.0	1.0
21.0	5.8	1.1	1.0
24.0	5.9	1.1	1.0
27.0	5.9	1.2	1.1
30.0	6.0	1.1	1.1
33.0	6.0	1.1	1.2
36.0	6.0	1.1	1.2
39.0	6.0	1.1	1.1
42.0	6.1	1.1	1.1
45.0	6.1	1.1	1.1
48.0	6.2	1.2	1.1
51.0	6.3	1.2	1.1
54.0	6.3	1.2	1.2
57.0	6.4	1.1	1.3
60.0	6.5	1.1	1.4
63.0	6.5	1.2	1.3
66.0	6.5	1.2	1.2
69.0	6.6	1.4	1.2
72.0	6.8	1.5	1.3
75.0	7.1	1.7	1.5
78.0	7.0	1.7	1.6
81.0	7.0	1.7	1.6
84.0	7.1	1.8	1.7
87.0	7.2	1.8	1.9
90.0	7.0	1.6	1.8
93.0	6.7	1.4	1.6
96.0	6.6	1.4	1.3
99.0	6.5	1.4	1.2
102.0	6.3	1.3	1.1
105.0	6.5	1.4	1.3
108.0	6.8	1.7	1.7
110.0	7.2	1.8	1.8

