

Phase-Stable Flexible Cable SMA Male to SMA Male

CBN-10FT-SMSM+

Typical Performance Data

FREQ.	INSERTION LOSS	SMA MALE RETURN LOSS IN	SMA MALE RETURN LOSS OUT
(GHz)	(dB)	(dB)	(dB)
0	0.11	30.69	30.63
1	0.79	35.55	35.12
2	1.41	37.40	37.62
3	1.85	37.25	35.69
4	2.22	38.23	38.14
5	2.55	35.10	35.57
6	2.84	31.78	31.68
7	3.11	31.41	30.84
8	3.36	32.85	31.90
9	3.59	33.61	31.93
10	3.82	33.67	32.76
11	4.03	31.75	32.58
12	4.24	30.43	32.15
13	4.43	30.60	30.87
14	4.63	30.62	29.76
15	4.82	28.62	27.40
16	5.00	28.06	27.57
17	5.17	28.44	28.16
18	5.34	30.24	28.90
19	5.52	35.03	30.66
20	5.68	33.31	32.30
21	5.84	34.06	35.07
22	5.99	36.03	33.34
23	6.15	36.44	34.39
24	6.29	34.31	32.02
25	6.44	30.73	27.80
26	6.58	25.90	25.61
27	6.72	25.21	24.34