

Phase-Stable Flexible Cable SMA Male to SMA Male
CBN-6FT-SMSM+

Typical Performance Data			
FREQ.	INSERTION LOSS	SMA MALE RETURN LOSS IN	SMA MALE RETURN LOSS OUT
(GHz)	(dB)	(dB)	(dB)
0	0.07	33.12	32.97
1	0.48	41.51	41.96
2	0.86	37.15	35.81
3	1.13	33.27	33.20
4	1.35	32.23	32.42
5	1.55	31.80	31.83
6	1.72	34.47	34.73
7	1.89	36.05	36.68
8	2.03	38.50	39.75
9	2.18	42.96	43.98
10	2.31	41.06	44.04
11	2.44	39.67	39.78
12	2.57	38.82	38.06
13	2.68	37.36	38.99
14	2.80	37.22	39.14
15	2.92	37.11	40.14
16	3.02	37.08	39.71
17	3.13	36.22	39.63
18	3.23	35.63	36.03
19	3.34	30.99	31.24
20	3.44	28.39	27.65
21	3.54	26.14	25.94
22	3.64	23.97	24.02
23	3.74	22.31	22.80
24	3.83	22.37	22.23
25	3.91	22.07	21.87
26	3.99	22.37	23.12
27	4.08	24.54	23.66