

Metal Shield High Pass Filter

RHP-EDU1143

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.50	52.46	0.00	128.00	12.83
5.00	32.52	0.00	140.00	5.32
10.00	26.59	0.02	150.00	3.63
50.00	15.52	0.16	160.00	2.71
80.00	22.57	0.22	200.00	1.40
88.00	35.68	0.30	300.00	0.61
100.00	17.23	0.63	500.00	0.35
110.00	14.85	1.26	800.00	0.26
115.00	19.80	2.07	1000.00	0.25
117.50	13.23	3.30	1500.00	0.23
118.50	10.15	4.21	2000.00	0.23
120.00	6.65	6.27	2500.00	0.23
122.00	3.78	10.79	3000.00	0.24
123.00	2.93	14.03	3500.00	0.23
125.00	1.94	24.02	4000.00	0.24
128.00	1.29	22.36		
140.00	0.65	17.41		
160.00	0.34	27.23		
200.00	0.22	21.35		
300.00	0.16	19.02		
1000.00	0.21	28.22		
2000.00	0.33	25.75		
3000.00	0.53	38.81		
4000.00	0.72	22.91		