

16 Way-0° Power Splitter/Combiner

ZC16PD-900

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB) S-1	AMP. UNBAL. (dB)	ISOLATION (dB)		FREQ. (MHz)	VSWR (:1)	
			1-2	1-9		S	1
800.0	12.43	0.20	31.27	64.26	800.0	1.08	1.07
807.8	12.42	0.20	31.75	58.34	807.8	1.07	1.07
815.5	12.40	0.21	32.12	54.41	815.5	1.06	1.06
823.0	12.41	0.21	32.38	52.04	823.0	1.05	1.05
830.8	12.41	0.19	32.54	49.87	830.8	1.05	1.05
838.5	12.41	0.19	32.58	48.45	838.5	1.04	1.04
846.3	12.44	0.21	32.57	46.96	846.3	1.03	1.04
853.8	12.43	0.20	32.41	46.07	853.8	1.03	1.03
861.5	12.41	0.21	32.14	44.92	861.5	1.02	1.03
869.3	12.42	0.21	31.78	44.07	869.3	1.01	1.02
877.0	12.41	0.20	31.33	43.18	877.0	1.01	1.02
884.5	12.40	0.21	30.88	42.47	884.5	1.01	1.01
892.3	12.42	0.21	30.37	41.75	892.3	1.01	1.01
897.5	12.41	0.25	29.98	41.34	897.5	1.02	1.01
900.0	12.42	0.24	29.77	41.20	900.0	1.02	1.01

¹ Total Loss = Insertion Loss+ 12dB Splitter Loss