

Frequency Synthesizer

KSN-2026A-219+

50Ω 2011.5 to 2026.5 MHz

The Big Deal

- Fractional N synthesizer
- Low phase noise and spurious
- Robust design and construction
- Small size 0.80" x 0.58" x 0.24"



CASE STYLE: DK1171

Product Overview

The KSN-2026A-219+ is a Frequency Synthesizer, designed to operate from 2011.5 to 2026.5 MHz for CDMA cellular basestation application. The KSN-2026A-219+ is packaged in a metal case (size of 0.80" x 0.58" x 0.24") to shield against unwanted signals and noise.

Key Features

Feature	Advantages
Low phase noise and spurious: <ul style="list-style-type: none">• Phase Noise: -109 dBc/Hz typ. @ 10 kHz offset• Step Size Spurious: -91 dBc typ.• Comparison Spurious: -90 dBc typ.• Reference Spurious: -88 dBc typ.	Low phase noise and spurious improve system EVM (Error Vector Magnitude).
Robust design and construction	To enhance the robustness of KSN-2026A-219+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.
Small size, 0.80" x 0.58" x 0.24"	The small size enables the KSN-2026A-219+ to be used in compact designs.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Frequency Synthesizer

KSN-2026A-219+

50Ω 2011.5 to 2026.5 MHz

Features

- Fractional N synthesizer
- Integrated VCO + PLL
- Low phase noise and spurious
- Robust design and construction
- Low operating voltage (VCC VCO =+5V, VCC PLL =+3.3V)
- Small size 0.80" x 0.58" x 0.24"



CASE STYLE: DK1171

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Applications

- CDMA cellular basestation

General Description

The KSN-2026A-219+ is a Frequency Synthesizer, designed to operate from 2011.5 to 2026.5 MHz for CDMA cellular basestation application. The KSN-2026A-219+ is packaged in a metal case (size of 0.80" x 0.58" x 0.24") to shield against unwanted signals and noise. To enhance the robustness of KSN-2026A-219+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.

Simplified Schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Electrical Specifications (over operating temperature -40°C to +85°C)

Parameters	Test Conditions	Min.	Typ.	Max.	Units
Frequency Range	-	2011.5	-	2026.5	MHz
Step Size	-	-	250	-	kHz
Comparison Frequency	-	-	20	-	MHz
Settling Time	Within ± 1 kHz	-	5	-	mSec
Output Power	-	-3	-1	+3	dBm
SSB Phase Noise	@ 100 Hz offset	-	-84	-	dBc/Hz
	@ 1 kHz offset	-	-94	-89	
	@ 10 kHz offset	-	-109	-105	
	@ 100 kHz offset	-	-134	-130	
	@ 1 MHz offset	-	-154	-149	
Step Size Spurious Suppression	Step Size 250 kHz	-	-91	-70	dBc
0.5 Step Size Spurious Suppression	0.5 Step Size 125 kHz	-	-87	-70	
Reference Spurious Suppression	Ref. Freq. 60 MHz	-	-88	-75	
Comparison Spurious Suppression	Step Size 20 MHz	-	-90	-70	
Non - Harmonic Spurious Suppression	-	-	-90	-	
Harmonic Suppression	-	-	-28	-20	
VCO Supply Voltage	5.00	4.75	5.00	5.25	V
PLL Supply Voltage	3.30	3.15	3.30	3.45	
VCO Supply Current	-	-	46	55	mA
PLL Supply Current	-	-	15	25	
Reference Input (External)	Frequency	60 (square wave)	-	60	MHz
	Amplitude	1	-	1	V _{P-P}
	Input impedance	-	-	100	KΩ
	Phase Noise @ 1 kHz offset	-	-	-135	dBc/Hz
RF Output port Impedance	-	-	50	-	Ω
Input Logic Level	Input high voltage	-	2.65	-	V
	Input low voltage	-	-	0.60	V
Digital Lock Detect	Locked	-	2.60	3.30	V
	Unlocked	-	-	0.40	V
Frequency Synthesizer PLL	-	ADF4153			
PLL Programming	-	3-wire serial 3V CMOS			
Register Map @ 2026.5 MHz	R0_Register	-	(MSB) 110010100000001101000 (LSB)		
	R1_Register	-	(MSB) 101001100000101000001 (LSB)		
	R2_Register	-	(MSB) 1111100010 (LSB)		
	R3_Register	-	(MSB) 1111000111 (LSB)		

Absolute Maximum Ratings

Parameters	Ratings
VCO Supply Voltage	5.5V
PLL Supply Voltage	4.0V
VCO Supply Voltage to PLL Supply Voltage	-0.3V to +5.8V
Reference Frequency Voltage	-0.3V min, +3.4V max
Data, Clock, LE Levels	-0.3V min, +3.4V max
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

Permanent damage may occur if any of these limits are exceeded

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

FREQUENCY (MHz)	POWER OUTPUT (dBm)			VCO CURRENT (mA)			PLL CURENT (mA)		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
2011.5	-1.21	-1.18	-1.28	44.86	46.15	47.12	14.91	15.93	17.90
2013.0	-1.19	-1.16	-1.26	44.88	46.17	47.13	14.84	15.85	17.67
2014.5	-1.18	-1.13	-1.23	44.89	46.18	47.14	14.78	15.64	17.07
2016.0	-1.16	-1.12	-1.22	44.90	46.19	47.15	14.72	15.19	18.06
2017.5	-1.14	-1.10	-1.20	44.92	46.20	47.16	14.65	14.75	18.51
2019.0	-1.13	-1.08	-1.18	44.93	46.21	47.17	14.51	14.30	18.04
2020.5	-1.12	-1.07	-1.17	44.94	46.23	47.19	14.35	14.15	15.93
2022.0	-1.11	-1.06	-1.15	44.96	46.24	47.20	14.52	14.59	15.93
2023.5	-1.10	-1.05	-1.14	44.97	46.26	47.22	14.67	15.03	15.93
2025.0	-1.09	-1.04	-1.12	44.98	46.27	47.23	14.72	15.48	15.93
2026.5	-1.07	-1.02	-1.11	44.99	46.29	47.24	14.83	15.87	17.84

FREQUENCY (MHz)	HARMONICS (dBc)					
	F2			F3		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
2011.5	-33.05	-34.77	-36.30	-26.36	-26.93	-28.07
2013.0	-32.85	-34.87	-36.33	-26.40	-26.98	-28.14
2014.5	-32.61	-34.90	-36.33	-26.29	-27.00	-28.17
2016.0	-32.38	-34.80	-36.25	-26.24	-26.98	-28.14
2017.5	-32.16	-34.70	-36.18	-26.21	-26.96	-28.12
2019.0	-32.14	-34.60	-36.10	-26.17	-26.94	-28.09
2020.5	-32.17	-34.56	-36.06	-26.13	-26.92	-28.03
2022.0	-32.35	-34.63	-36.09	-26.07	-26.90	-27.89
2023.5	-32.52	-34.71	-36.12	-26.00	-26.88	-27.76
2025.0	-32.67	-34.78	-36.15	-25.89	-26.86	-27.63
2026.5	-32.71	-34.93	-35.75	-25.84	-26.36	-27.50

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	+25°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
2011.5	-89.93	-94.16	-109.35	-135.36	-153.48
2013.0	-86.60	-95.77	-109.48	-135.20	-154.04
2014.5	-84.45	-96.55	-109.59	-135.10	-154.48
2016.0	-84.67	-95.67	-109.68	-135.11	-154.64
2017.5	-84.88	-94.78	-109.78	-135.13	-154.81
2019.0	-85.10	-93.89	-109.87	-135.15	-154.98
2020.5	-85.36	-93.39	-109.89	-135.10	-155.01
2022.0	-85.72	-93.66	-109.77	-134.94	-154.78
2023.5	-86.08	-93.93	-109.66	-134.77	-154.55
2025.0	-86.44	-94.20	-109.54	-134.60	-154.32
2026.5	-84.02	-95.15	-109.39	-135.56	-153.09

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	-45°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
2011.5	-84.47	-95.71	-109.03	-135.25	-154.48
2013.0	-83.93	-95.86	-108.90	-135.08	-155.20
2014.5	-84.80	-95.09	-109.04	-135.11	-155.09
2016.0	-84.81	-94.57	-108.98	-135.35	-154.66
2017.5	-84.38	-94.18	-108.83	-135.69	-154.07
2019.0	-84.46	-94.32	-108.85	-135.55	-153.91
2020.5	-84.65	-94.58	-108.91	-135.31	-153.84
2022.0	-84.99	-94.38	-109.03	-135.42	-154.40
2023.5	-85.22	-94.20	-109.10	-135.52	-154.82
2025.0	-84.83	-94.05	-108.94	-135.58	-154.56
2026.5	-84.57	-93.59	-109.51	-135.18	-153.96

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	+85°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
2011.5	-85.29	-94.62	-108.90	-134.05	-152.17
2013.0	-85.30	-93.62	-109.04	-134.01	-152.10
2014.5	-85.32	-92.94	-109.16	-133.99	-152.26
2016.0	-85.34	-92.88	-109.20	-134.00	-152.85
2017.5	-85.37	-92.81	-109.25	-134.02	-153.44
2019.0	-85.39	-92.75	-109.30	-134.03	-154.04
2020.5	-85.45	-92.89	-109.26	-134.05	-154.37
2022.0	-85.55	-93.42	-109.05	-134.06	-154.20
2023.5	-85.66	-93.96	-108.83	-134.08	-154.03
2025.0	-85.76	-94.49	-108.62	-134.09	-153.86
2026.5	-86.72	-93.81	-108.87	-134.54	-153.82

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



COMPARISON SPURIOUS ORDER	COMPARISON SPURIOUS @Fcarrier 2011.5MHz+(n*Fcomparison) (dBc) note 1			COMPARISON SPURIOUS @Fcarrier 2019MHz+(n*Fcomparison) (dBc) note 1			COMPARISON SPURIOUS @Fcarrier 2026.5MHz+(n*Fcomparison) (dBc) note 1		
	n	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C
-5	-98.14	-100.39	-99.86	-91.60	-101.96	-100.16	-93.07	-107.71	-97.90
-4	-97.85	-101.59	-90.49	-87.45	-89.86	-88.18	-83.18	-85.15	-96.47
-3	-85.83	-82.18	-89.45	-90.36	-82.92	-90.20	-89.05	-83.30	-91.63
-2	-86.53	-87.28	-91.44	-99.21	-87.55	-92.11	-108.70	-87.39	-91.79
-1	-89.75	-89.74	-101.44	-97.13	-89.72	-103.36	-95.37	-91.57	-103.32
0 ^{note 2}	-	-	-	-	-	-	-	-	-
+1	-90.76	-90.09	-90.61	-91.97	-90.28	-91.94	-91.38	-90.70	-92.15
+2	-91.01	-91.09	-98.69	-93.40	-91.54	-96.44	-93.27	-92.36	-98.20
+3	-84.89	-87.51	-90.48	-90.61	-90.08	-92.12	-92.96	-90.60	-93.55
+4	-88.66	-88.11	-84.99	-80.22	-83.36	-81.07	-79.69	-85.50	-86.67
+5	-90.80	-89.69	-97.33	-87.50	-89.96	-97.33	-87.82	-89.36	-97.09

Note 1: Comparison frequency 20 MHz

Note 2: All spurs are referenced to carrier signal (n=0).

REFERENCE SPURIOUS ORDER	REFERENCE SPURIOUS @Fcarrier 2011.5MHz+(n*Freference) (dBc) note 3			REFERENCE SPURIOUS @Fcarrier 2019MHz+(n*Freference) (dBc) note 3			REFERENCE SPURIOUS @Fcarrier 2026.5MHz+(n*Freference) (dBc) note 3		
	n	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C
-5	-95.56	-85.95	-85.63	-94.78	-85.63	-85.81	-92.28	-92.99	-87.69
-4	-102.04	-88.42	-92.17	-97.05	-90.38	-90.90	-92.81	-90.34	-90.04
-3	-89.07	-90.76	-94.70	-89.65	-92.43	-92.37	-89.73	-92.72	-92.31
-2	-95.64	-86.64	-92.58	-92.95	-88.79	-94.69	-92.45	-88.33	-95.60
-1	-89.05	-85.40	-89.31	-90.47	-86.24	-90.51	-89.11	-87.73	-91.63
0 ^{note 4}	-	-	-	-	-	-	-	-	-
+1	-89.26	-91.17	-90.39	-90.74	-90.40	-92.34	-93.21	-92.34	-93.29
+2	-87.34	-92.90	-90.84	-88.85	-93.50	-90.64	-90.79	-96.68	-89.64
+3	-99.23	-93.82	-88.65	-99.26	-92.80	-88.49	-98.00	-92.44	-88.81
+4	-90.40	-95.93	-86.74	-91.27	-95.74	-86.27	-89.68	-94.58	-85.92
+5	-89.44	-91.17	-108.86	-89.86	-96.62	-114.49	-88.77	-98.73	-101.41

Note 3: Reference frequency 60 MHz

Note 4: All spurs are referenced to carrier signal (n=0).

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



STEP SIZE SPURIOUS ORDER n	0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 2011.5MHz+(n*Fstep size) (dBc) note 5			0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 2019MHz+(n*Fstep size) (dBc) note 5			0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 2026.5MHz+(n*Fstep size) (dBc) note 5		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
-5.0	-112.96	-109.21	-114.83	-111.86	-111.67	-111.48	-106.97	-115.64	-116.20
-4.5	-105.30	-118.05	-112.98	-114.57	-116.06	-118.84	-118.13	-116.64	-112.98
-4.0	-99.76	-107.69	-110.45	-94.59	-90.64	-91.40	-109.29	-107.48	-118.26
-3.5	-100.51	-115.43	-114.10	-110.93	-106.21	-116.24	-108.57	-106.70	-112.91
-3.0	-112.75	-114.50	-111.23	-107.68	-113.50	-111.66	-107.31	-107.80	-110.13
-2.5	-98.96	-108.89	-111.34	-108.98	-109.98	-105.97	-101.66	-110.89	-102.01
-2.0	-101.67	-109.46	-107.64	-107.33	-109.14	-108.73	-96.33	-110.87	-96.17
-1.5	-107.60	-101.54	-102.37	-107.35	-105.48	-105.33	-101.94	-103.37	-108.67
-1.0	-100.66	-98.51	-97.15	-99.47	-97.10	-99.14	-83.59	-78.87	-81.07
-0.5	-86.69	-87.08	-90.09	-86.96	-87.99	-89.04	-89.33	-88.49	-89.56
0 ^{note 6}	-	-	-	-	-	-	-	-	-
+0.5	-89.81	-85.50	-89.00	-88.15	-85.83	-83.76	-90.07	-89.67	-88.24
+1.0	-99.88	-102.06	-97.51	-98.61	-98.93	-102.19	-84.65	-81.71	-81.73
+1.5	-106.38	-104.46	-102.44	-102.44	-106.43	-106.68	-103.65	-106.49	-105.37
+2.0	-105.12	-102.85	-109.02	-108.99	-111.22	-111.17	-97.80	-108.00	-95.45
+2.5	-101.98	-112.02	-109.52	-110.03	-109.15	-105.01	-106.54	-111.39	-107.02
+3.0	-113.43	-110.63	-117.14	-107.95	-110.45	-111.47	-107.34	-108.12	-108.13
+3.5	-106.63	-115.79	-112.37	-116.20	-106.52	-116.87	-114.44	-110.45	-113.52
+4.0	-105.64	-109.71	-110.64	-95.69	-98.34	-94.44	-114.19	-109.56	-118.69
+4.5	-114.86	-118.32	-113.12	-117.11	-116.83	-116.73	-119.10	-115.94	-109.67
+5.0	-115.26	-117.43	-115.18	-118.41	-116.43	-116.28	-112.12	-113.12	-115.70

Note 5: Step size 250 kHz




Note 6: All spurs are referenced to carrier signal (n=0).

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp








Typical Performance Curves



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp











Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp








Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Pin Configuration




Pin Connection

Pin Number	Function
1	VCC PLL
2	GND
3	REF IN
4	GND
5	VCC VCO
6	GND
7	RF OUT
8	GND
9	LOCK DET
10	CLOCK
11	DATA
12	LE
13	GND
14	GND

Recommended Application Circuit

Note: REF IN and RF OUT ports are internally AC coupled.




Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Device Marking



Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

Case Style: DK1171

Tape & Reel: TR-F28

Suggested Layout for PCB Design: PL-249

Evaluation Board: TB-567-1+

Environment Ratings: ENV03T2

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

