

Ceramic

Low Pass Filter

LFCN-2000

50Ω DC⁽¹⁾ to 2000 MHz



Generic photo used for illustration purposes only

CASE STYLE: FV1206

Maximum Ratings


| | |
|-----------------------|-----------------|
| Operating Temperature | -55°C to 100°C |
| Storage Temperature | -55°C to 100°C |
| RF Power Input* | 9W max. at 25°C |

* Passband rating, derate linearly to 4W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

Pin Connections

| | |
|--------|-----|
| RF IN | 1 |
| RF OUT | 3 |
| GROUND | 2,4 |

Outline Drawing




Outline Dimensions (inch)

| A | B | C | D | E | F | G |
|------|------|------|------|------|------|------|
| .126 | .063 | .037 | .020 | .032 | .009 | .169 |
| 3.20 | 1.60 | 0.94 | 0.51 | 0.81 | 0.23 | 4.29 |

| H | J | K | L | M | N | P | wt |
|------|------|------|------|------|------|------|-------|
| .087 | .024 | .122 | .024 | .087 | .012 | .071 | grams |
| 2.21 | 0.61 | 3.10 | 0.61 | 2.21 | 0.30 | 1.80 | .020 |

Demo Board MCL P/N: TB-270 Suggested PCB Layout (PL-137)



Features

- excellent power handling, 9W
- small size
- 5 sections
- temperature stable
- LTCC construction

Applications


- harmonic rejection
- VHF/UHF transmitters/receivers
- lab use

Electrical Specifications^(1,2) at 25°C


| Parameter | F# | Frequency (MHz) | Min. | Typ. | Max. | Unit | |
|-----------|----------------|-----------------|-----------|------|------|------|----|
| Pass Band | Insertion Loss | DC-F1 | DC-2000 | — | — | 1.5 | dB |
| | Freq. Cut-Off | F2 | 2275 | — | 3.0 | — | dB |
| | VSWR | DC-F1 | DC-2000 | — | 1.3 | — | :1 |
| Stop Band | Rejection Loss | F3 | 3000 | 20 | — | — | dB |
| | | F4-F5 | 3100-3500 | — | 30 | — | dB |
| | | F6 | 4600 | — | 20 | — | dB |
| | VSWR | F3-F6 | 3000-4650 | — | 20 | — | :1 |

(1) In Applications where DC isolation to ground is required, coupling capacitors are recommended to avoid DC leakage. Alternatively, if DC pass IN-OUT is required, Mini-Circuits' "D" suffix version of this model will support DC IN-OUT, and provide >100 MOhm isolation to ground.
(2) Measured on Mini-Circuits Characterization Test Board TB-270.

Typical Frequency Response





Electrical Schematic



Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|-----------------|---------------------|-----------|
| 10.00 | 0.14 | 1.04 |
| 258.75 | 0.30 | 1.19 |
| 507.50 | 0.35 | 1.23 |
| 756.25 | 0.51 | 1.28 |
| 1005.00 | 0.49 | 1.21 |
| 1253.75 | 0.56 | 1.18 |
| 1502.50 | 0.60 | 1.14 |
| 1751.25 | 0.74 | 1.13 |
| 2250.00 | 4.73 | 5.33 |
| 2500.00 | 11.34 | 16.41 |
| 2750.00 | 19.65 | 43.44 |
| 3000.00 | 32.99 | 102.19 |
| 4244.00 | 20.09 | 217.15 |
| 4422.00 | 19.52 | 66.82 |
| 4600.00 | 20.32 | 46.96 |



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

