

Directional Coupler

PDC-10-22

50Ω 5 to 750 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections


INPUT	1
OUTPUT	4
COUPLED	3
GROUND	2,5,7,8
CASE GROUND	2,5,7,8
NOT USED	6

Features

- wideband, 5 to 750 MHz
- excellent directivity, 25 dB typ.
- good VSWR, 1.25:1 typ.
- rugged welded construction, hermetically sealed


Applications

- VHF/UHF
- defense & federal communications
- power levelling



CASE STYLE: A01

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F
.770	.800	.385	.400	.370	.400
19.56	20.32	9.78	10.16	9.40	10.16
G	H	J	K		wt
.200	.20	.14	.031		grams
5.08	5.08	3.56	0.79		5.2

Directional Coupler Electrical Specifications




FREQ. (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT, W	
			L		M		U		L		M		U			L	MU
	f _L -f _U	Nom.	Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.		Min.	Typ.
5-750	11.0±0.5	±0.5	1.1	1.6	1.2	1.7	1.6	1.9	35	30	25	20	25	20	1.25	1.0	2.0

L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U]


1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
5.00	1.17	10.76	56.00	26.72	17.45	17.54
10.00	1.13	10.72	55.00	31.54	18.12	18.32
20.00	1.21	10.74	54.00	34.28	18.19	18.42
50.00	1.26	10.79	52.00	30.97	17.69	17.87
100.00	1.20	10.85	45.27	29.52	17.58	17.66
200.00	1.24	10.84	36.71	29.28	17.84	17.74
366.22	1.34	10.87	31.90	29.98	19.03	18.34
500.00	1.22	10.90	30.51	29.97	20.33	18.48
727.43	1.28	10.96	30.19	27.90	23.20	16.88
750.00	1.27	10.94	29.66	27.62	23.46	16.58



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TERMINATIONS THAT ROUTES DC FROM RF PORTS TO GROUND.

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

