

Low Pass Filter

LPF-B0R7+

50Ω DC to 0.7 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.25W Max

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT	1
OUTPUT	2
GROUND	3, 4, 5, 6

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M
.472"	.826"	.220"	.551"	.118"	.047"	.078"	.076"	.142"	.543"	.078"	.236"
11.99	20.98	5.59	14.00	3.00	1.19	1.98	1.92	3.61	13.79	1.98	5.99
N	P	Q	S	T	U	V	W	X	Y	wt	
.079"	.138"	.162"	.098"	.096"	.217"	.067"	.157"	.866"	.512"	grams	
2.01	3.51	4.11	2.49	2.44	5.51	1.70	3.99	22.00	13.00	6.0	

Note: Please refer to case style drawing for details.

Demo Board MCL P/N: TB-400+ Suggested PCB Layout (PL-247)



- NOTES:
- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Features

- high rejection
- good VSWR, 1.2:1 typ. @ passband
- shielded case
- aqueous washable

Applications

- CDMA
- cellular infrastructure
- wireless communications
- receivers / transmitters




Generic photo used for illustration purposes only
CASE STYLE: HZ1198

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Low Pass Filter Electrical Specifications (T_{AMB} = 25°C)

PASSBAND (MHz)	f _{co} , MHz Nom.	STOPBAND (MHz)		VSWR (:1)	
		(Loss > 20dB)	(Loss > 40dB)	Passband Typ.	Stopband Typ.
DC - 0.7	1.08	1.30 - 1.46	1.46 - 1000	1.2	20

Typical Frequency Response






Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec.)
	\bar{x}	σ			
0.03	0.15	0.03	34.75	0.03	538.62
0.10	0.17	0.00	32.92	0.05	608.42
0.30	0.20	0.01	36.13	0.10	633.47
0.50	0.30	0.01	20.02	0.20	633.74
0.60	0.39	0.02	16.34	0.30	663.36
0.70	0.48	0.03	15.13	0.35	681.41
0.96	0.85	0.07	23.81	0.40	685.22
1.04	1.83	0.32	15.11	0.45	716.25
1.08	3.57	0.67	7.87	0.50	719.68
1.12	6.81	0.98	3.70	0.55	752.13
1.18	13.39	1.13	1.36	0.60	780.74
1.30	27.77	1.19	0.55	0.65	805.77
1.46	49.02	1.83	0.39	0.70	841.39
5.00	66.53	0.61	0.24	0.75	892.61
10.00	82.33	2.26	0.25	0.80	973.76
100.00	90.40	4.41	0.14	0.85	1086.39
500.00	77.60	1.99	0.20	0.88	1163.22
1000.00	60.51	0.93	0.31	0.90	1198.79



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

