

# Plug-In High Pass Filter

## PHP-1000+

50Ω 1000 to 2200 MHz

### Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Permanent damage may occur if any of these limits are exceeded.

### Pin Connections

INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7
CASE GROUND	2,3,4,5,6,7

### Features

- rugged shielded case, hermetically sealed
- other standard and custom PHP models available with wide selection of fco

### Applications

- lab use
- transmitters/receivers
- military/hi-rel application



Generic photo used for illustration purposes only

CASE STYLE: A01


**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### High Pass Filter Electrical Specifications

STOPBAND (MHz)	fco (MHz) Nom.	PASSBAND (MHz)	VSWR (:1)
(loss > 40 dB)	(loss > 20 dB)	(loss < 3 dB)	Stopband Typ. Passband Typ.
DC-550	550-720	900	17 1.9


### Outline Drawing




### Outline Dimensions (inch/mm)

A	B	C	D	E	F
.770	.800	.385	.400	.370	.400
19.56	20.32	9.78	10.16	9.40	10.16
G	H	J	K	wt	
.200	.20	.14	.031	grams	
5.08	5.08	3.56	0.79	5.2	

### typical frequency response





### electrical schematic



### Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$	$\sigma$			
10.00	83.18	2.8	0.1	420.00	2.22
200.00	87.50	7.1	0.1	430.00	1.93
330.00	81.91	4.5	0.1	440.00	0.04
410.00	69.01	3.7	0.1	450.00	1.38
430.00	64.76	2.6	0.1	480.00	1.80
440.00	63.14	2.6	0.1	500.00	0.67
450.00	61.53	2.3	0.1	550.00	0.76
480.00	56.69	1.8	0.1	610.00	1.26
500.00	53.07	1.3	0.2	620.00	1.48
550.00	45.76	1.0	0.2	640.00	1.37
610.00	36.92	0.6	0.3	650.00	1.22
640.00	32.87	0.5	0.3	660.00	1.18
660.00	30.45	0.5	0.3	670.00	1.18
670.00	29.21	0.5	0.3	700.00	1.23
700.00	25.28	0.4	0.4	720.00	1.37
720.00	22.61	0.4	0.5	770.00	1.95
770.00	15.62	0.4	0.6	790.00	2.35
820.00	9.80	0.5	1.2	820.00	2.04
860.00	4.84	0.4	2.9	840.00	1.97
880.00	2.75	0.4	4.4	860.00	2.88
885.00	2.41	0.4	4.9	880.00	3.59
900.00	1.81	0.4	6.7	885.00	3.56
920.00	1.40	0.3	9.8	900.00	3.22
1000.00	0.57	0.1	22.5	920.00	2.58
1560.00	0.53	0.1	18.5	1000.00	1.90
1745.00	0.42	0.1	15.8	1560.00	0.83
1925.00	0.62	0.1	14.0	1650.00	0.82
2015.00	0.59	0.1	13.5	1745.00	0.87
2110.00	0.77	0.1	12.9	1835.00	0.75
2200.00	0.71	0.1	12.2	1925.00	0.73



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

