

Surface Mount Voltage Controlled Oscillator

ROS-2500+

Wide Band 1600 to 2500 MHz



CASE STYLE: CK605

Features

- wideband, 1600 to 2500 MHz
- low phase noise, -133 dBc/Hz at 1 MHz offset, typ.
- aqueous washable

Applications

- PCS

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

FREQUENCY (MHz)	POWER OUTPUT (dBm)	TUNING VOLTAGE (V)	PHASE NOISE (dBc/Hz)				PULLING pk-pk @ 12 dB (MHz)	PUSHING (MHz/V)	TUNING SENSITIVITY (MHz/V)	HARMONICS (dBc)	3 dB MODULATION BANDWIDTH (MHz)	DC OPERATING POWER	
			SSB at offset frequencies: Typ.									Vcc (volts)	Current (mA) Max.
Min. Max.	Typ.	Min. Max.	1 kHz	10 kHz	100 kHz	1 MHz	Typ.	Typ.	Typ.	Typ. Max.	Typ.		
1600 2500	6.5	0.5 14	-66	-90	-113	-133	18.0	5.0	30-180	-14 -8	6	12	25

Pin Connections

RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16


Permanent damage may occur if any of these limits are exceeded.

Maximum Ratings


Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	+15V
Absolute Max. Tuning Voltage (Vtune)	+16V

all specifications: 50 ohm system
Permanent damage may occur if any of these limits are exceeded.

Outline Drawing



Demo Board MCL P/N: TB-10 Suggested PCB Layout (PL-012)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
.500	.500	.180	.100	.080	.115	.060	.040	.540	.060	.100	.135	.135	.115	.140	.070	.150	.070	grams
12.70	12.70	4.57	2.54	2.03	2.92	1.52	1.02	13.72	1.52	2.54	3.43	3.43	2.92	3.56	1.78	3.81	1.78	1.0

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com



REV. G
M151108
ED-7473B/3
ROS-2500+
RAV/MCL
151105
Page 1 of 2

Performance Data & Curves


ROS-2500+



V TUNE	TUNING SENS. (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)		
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C
1.00	156.40	1501.52	1473.06	1445.18	5.70	5.77	5.28
2.00	161.35	1671.28	1634.41	1603.80	6.20	5.99	5.34
3.00	162.52	1835.76	1796.93	1766.70	7.04	6.66	5.86
4.00	152.45	1986.50	1949.39	1922.75	7.48	7.06	6.23
5.00	143.59	2126.51	2092.98	2068.65	7.57	7.15	6.29
6.00	123.11	2245.23	2216.09	2194.09	7.53	7.06	6.28
7.00	95.41	2338.10	2311.50	2290.61	7.76	7.08	6.31
8.00	68.87	2405.31	2380.37	2360.90	7.98	7.24	6.44
9.00	54.46	2455.83	2434.83	2417.91	7.94	7.18	6.27
10.00	50.25	2504.20	2485.08	2467.35	7.45	6.74	5.88
11.00	45.50	2551.88	2530.58	2511.16	6.99	6.44	5.60



V TUNE	HARMONICS (dBc)			FREQ. PUSHING (MHz/V)
	F2	F3	F4	
1.00	-22.77	-22.05	-33.59	0.08
2.00	-22.77	-24.00	-46.07	0.19
3.00	-17.81	-24.11	-40.65	1.14
4.00	-15.93	-22.59	-40.02	2.78
5.00	-15.51	-25.38	-30.92	3.63
6.00	-14.73	-31.08	-36.45	4.26
7.00	-14.11	-35.78	-27.91	3.83
8.00	-14.60	-37.16	-28.17	2.58
9.00	-16.19	-39.47	-29.03	1.47
10.00	-17.95	-50.70	-30.33	0.79
11.00	-17.67	-38.68	-31.47	0.52



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

