

# Surface Mount Voltage Controlled Oscillator

## ROS-3900-419+

Linear Tuning 3650 to 3900 MHz

### Features

- linear tuning characteristics
- low pushing
- low pulling
- aqueous washable

### Applications

- wireless communications
- radio link



CASE STYLE: CK605

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, kHz				TUNING					NON HARMONIC SPURIOUS (dBc)	HARMONICS (dBc)		PULLING pk-pk @12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER	
	Min.	Max.		Typ.				VOLTAGE RANGE (V)	SENSI- TIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)	Typ.		Max.	Vcc			Current (mA)	
				1	10	100	1000	Min.	Max.	Typ.	Typ.	Typ.		Typ.	Max.			Max.	
ROS-3900-419+	3650	3900	+4.5	-72	-96	-118	-138	0.5	12	34-40	20	100	-90	-20	-12	2	4	5	40

### Pin Connections


RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16

### Maximum Ratings


Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	6V
Absolute Max. Tuning Voltage (Vtune)	14V
All specifications	50 ohm system

Permanent damage may occur if any of these limits are exceeded.

### Outline Drawing



### Demo Board MCL P/N: TB-10 Suggested PCB Layout (PL-012)



#### NOTES:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE BOTTOM IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
.500	.500	.180	.100	.080	.115	.060	.040	.540	.060	.100	.135	.135	.115	.140	.070	.150	.070	grams
12.70	12.70	4.57	2.54	2.03	2.92	1.52	1.02	13.72	1.52	2.54	3.43	3.43	2.92	3.56	1.78	3.81	1.78	1.0

#### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com







REV. A  
 M151447  
 EDR-11343  
 ROS-3900-419+  
 RAV  
 150602  
 Page 1 of 2

# Performance Data & Curves\*

# ROS-3900-419+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (kHz)	PHASE NOISE at 3775 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	40.56	3571.7	3552.4	3542.1	4.48	4.37	3.55	30.06	-21.6	-41.9	-61.5	2.57	0.07	-73.53	-95.7	-117.4	-137.5	1.0	-72.40
0.50	36.51	3591.4	3572.7	3562.9	4.53	4.30	3.60	30.06	-20.7	-40.4	-58.5	2.79	0.97	-71.95	-96.6	-117.1	-137.3	2.0	-79.71
1.00	34.37	3609.2	3590.9	3581.3	4.48	4.39	3.58	30.07	-17.5	-39.9	-60.4	2.72	1.47	-73.23	-96.4	-117.7	-137.4	3.5	-86.55
1.50	35.09	3626.2	3608.1	3598.5	4.33	4.37	3.65	30.07	-21.0	-42.6	-58.8	2.75	1.36	-73.91	-96.7	-117.4	-137.6	6.0	-91.47
2.00	36.03	3644.2	3625.7	3615.6	4.42	4.16	3.65	30.09	-23.8	-42.3	-62.4	2.74	0.68	-74.51	-96.6	-117.7	-137.7	8.5	-95.01
2.50	36.02	3661.8	3643.7	3633.2	4.44	4.24	3.50	30.08	-17.5	-39.3	-55.8	3.01	0.67	-73.93	-95.7	-116.9	-136.9	10.0	-96.38
3.00	36.65	3679.8	3661.7	3651.8	4.50	4.37	3.65	30.14	-19.4	-41.6	-62.6	2.79	1.25	-73.69	-97.0	-117.9	-138.1	20.8	-103.46
4.00	38.83	3718.3	3699.4	3688.2	4.35	4.16	3.87	30.18	-17.9	-40.0	-60.8	3.05	0.39	-72.67	-95.5	-117.2	-137.2	35.5	-108.40
5.00	38.12	3757.1	3738.2	3727.3	4.48	4.45	3.91	30.30	-22.8	-48.1	-58.5	2.84	1.38	-72.02	-97.2	-118.4	-138.5	60.7	-113.34
5.50	38.95	3776.8	3757.3	3745.9	4.11	4.52	4.07	30.34	-18.8	-43.8	-57.9	2.86	1.48	-73.03	-96.3	-118.1	-138.3	86.7	-116.55
6.00	36.93	3795.7	3776.8	3764.7	4.36	4.28	4.14	30.40	-19.1	-44.3	-52.3	3.00	0.58	-72.40	-96.6	-117.8	-137.9	100.0	-117.68
7.00	36.43	3833.3	3814.0	3802.0	4.26	4.52	4.15	30.52	-20.4	-40.4	-47.3	2.88	1.15	-71.97	-96.9	-118.5	-138.6	148.1	-121.25
8.00	36.40	3870.3	3850.4	3838.0	4.04	4.26	4.13	30.62	-22.7	-44.3	-48.1	2.88	0.30	-70.33	-95.8	-118.5	-138.8	177.0	-122.75
9.00	35.41	3906.5	3886.8	3873.7	4.04	4.17	3.98	30.76	-18.3	-45.6	-48.9	2.95	1.29	-71.95	-95.3	-118.1	-138.4	211.6	-124.39
9.50	34.86	3924.6	3904.5	3891.6	4.14	4.07	3.99	30.86	-20.1	-42.4	-56.4	2.74	1.20	-72.28	-96.3	-118.4	-138.9	302.4	-127.54
10.00	35.49	3942.5	3922.0	3908.9	4.09	4.27	3.93	30.87	-21.8	-43.0	-57.8	2.95	0.80	-71.56	-95.3	-117.8	-138.2	361.5	-129.04
10.50	35.29	3960.5	3939.7	3926.1	3.94	4.25	4.09	30.93	-19.3	-44.0	-53.8	2.84	0.22	-69.31	-95.7	-117.9	-138.3	507.5	-131.96
11.00	36.11	3978.2	3957.4	3943.5	3.72	4.22	4.07	30.99	-18.3	-44.9	-53.8	2.81	0.92	-68.16	-95.5	-117.8	-138.1	606.7	-133.56
11.50	32.57	3995.4	3975.4	3960.8	3.85	3.75	4.05	31.10	-22.0	-40.0	-51.4	2.74	0.74	-69.78	-95.8	-118.0	-138.5	851.6	-136.41
12.00	34.90	4013.2	3991.7	3978.5	3.91	3.99	3.70	31.14	-21.4	-39.1	-52.3	2.63	0.59	-67.57	-95.2	-118.1	-138.1	1000.0	-137.84

\*at 25°C unless mentioned otherwise



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form part of this specification.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test procedures.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms") to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits.com.



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500

CHECK PRINT (FOR INTERNAL USE ONLY)			
MODEL: ROS-3900-419+(A)		Updated by Vali S.	
NAME (PRINT)	SIGNATURE	DATE	FILE SIZE
Meir K.		June, 2015	200 KB
Oren B.		June, 2015	
Doron G.		June, 2015	
Haim H.		June, 2015	
Alin O.		June, 2015	
David E.		June, 2015	