

# Voltage Controlled Oscillator

## ROS-6520C-119+

Frequency Doubling 6385 to 6520 MHz

### Features

- frequency based on multiplication of carrier frequency
- low phase noise
- low pushing
- low pulling
- aqueous washable

### Applications

- wireless communications
- wireless broadband access



CASE STYLE: CK1113

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, kHz				TUNING					NON HARMONIC SPURIOUS (dBc)	HARMONICS (dBc)			PULLING pk-pk @12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER			
	F 2X(1/2F)			Typ.				VOLTAGE RANGE (V)	SENSITIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)	Max.		F0.5	F1.5	F2			Typ.	Typ.	Vcc	Current
	Min.	Max.		1	10	100	1000															
ROS-6520C-119+	6385	6520	+2	-72	-100	-123	-143	0.5	4.5	77-92	13	260	-90	-17	-14	-19	2.0	2.5	5	35		

### Pin Connections


RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16

### Maximum Ratings


Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	6.5V
Absolute Max. Tuning Voltage (Vtune)	6.5V
All specifications	50 ohm system

Permanent damage may occur if any of these limits are exceeded.


### Outline Drawing



### PCB Land Pattern



### Demo Board MCL P/N: TB-10 Suggested PCB Layout (PL-012)



### NOTES:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  2. BOTTOM SIDE OF THE BOTTOM IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
  - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
.500	.500	.220	.100	.080	.115	.060	.040	.540	.060	.100	.135	.135	.115	.140	.070	.150	.070	grams
12.70	12.70	5.59	2.54	2.03	2.92	1.52	1.02	13.72	1.52	2.54	3.43	3.43	2.92	3.56	1.78	3.81	1.78	1.2

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com







REV. B  
M151108  
EDR-9702/3F1  
ROS-6520C-119+  
RAV  
150921  
Page 1 of 2

# Performance Data & Curves\*

# ROS-6520C-119+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (KHz)	PHASE NOISE at 6453 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F0.5	F1.5	F2			1kHz	10kHz	100kHz	1MHz		
0.00	73.25	6264.7	6245.9	6229.3	-0.32	-1.01	-3.11	24.52	-24.5	-20.8	-25.5	1.84	2.61	-74.7	-101.3	-122.1	-142.1	1.0	-71.97
0.25	67.92	6282.0	6264.2	6248.5	0.18	-0.67	-2.20	24.65	-24.8	-20.7	-26.2	1.93	2.19	-75.2	-101.4	-122.7	-142.4	2.0	-81.13
0.50	65.72	6298.9	6281.2	6266.0	-0.19	-0.24	-1.83	24.78	-25.1	-21.1	-25.4	1.98	1.63	-74.8	-101.6	-123.1	-143.2	3.5	-88.20
0.75	67.18	6315.5	6297.6	6282.6	0.83	-0.29	-1.40	24.88	-24.7	-21.5	-26.5	2.10	1.24	-75.4	-101.6	-122.9	-143.1	5.0	-92.32
1.00	66.09	6331.8	6314.4	6298.8	1.15	0.30	-1.29	24.98	-24.7	-21.1	-26.5	2.14	1.44	-73.7	-101.1	-122.5	-143.3	7.1	-96.43
1.25	66.43	6348.2	6330.9	6315.4	1.35	0.77	-1.21	25.09	-24.8	-22.5	-26.0	2.19	1.16	-75.1	-101.5	-123.2	-142.6	8.5	-98.36
1.50	68.17	6365.0	6347.5	6332.0	1.32	0.99	-0.54	25.20	-25.0	-23.1	-27.3	2.22	0.34	-73.2	-101.0	-122.9	-143.5	20.8	-108.32
1.75	70.75	6382.2	6364.6	6348.8	1.79	0.98	-0.27	25.30	-25.5	-22.1	-26.6	2.33	1.79	-73.4	-100.6	-123.2	-143.4	35.5	-113.77
2.00	71.96	6399.8	6382.3	6366.0	2.09	1.34	-0.27	25.42	-26.2	-23.9	-26.5	2.34	2.81	-73.8	-101.2	-123.4	-143.6	60.7	-118.61
2.25	76.96	6418.5	6400.3	6384.0	1.87	1.68	0.01	25.52	-26.7	-24.7	-28.0	2.43	3.21	-72.4	-100.5	-123.2	-142.9	72.5	-120.21
2.50	79.28	6437.6	6419.5	6402.4	2.64	1.29	0.36	25.62	-26.4	-23.0	-26.1	2.60	2.83	-73.0	-100.4	-123.0	-142.9	86.7	-122.02
2.75	81.88	6457.5	6439.3	6422.0	2.94	2.11	-0.09	25.75	-27.2	-24.8	-27.9	2.54	2.42	-72.3	-100.7	-123.6	-143.9	148.1	-126.93
3.00	86.74	6478.5	6459.8	6442.4	2.62	2.37	0.66	25.85	-27.0	-25.1	-27.8	2.60	1.85	-72.2	-100.4	-123.2	-143.5	177.0	-128.07
3.25	92.18	6501.0	6481.5	6463.4	2.81	2.11	0.95	25.95	-26.2	-24.3	-26.7	2.64	0.90	-71.5	-99.8	-123.0	-143.1	211.6	-129.81
3.50	90.80	6523.4	6504.5	6485.5	3.31	1.88	0.72	26.10	-25.8	-24.0	-27.2	2.33	0.44	-71.6	-99.9	-123.1	-143.3	302.4	-132.82
3.75	96.10	6547.4	6527.2	6508.9	3.17	2.43	0.02	26.18	-27.0	-24.0	-27.7	2.16	2.60	-70.5	-99.2	-122.4	-142.8	361.5	-134.41
4.00	96.08	6571.9	6551.2	6531.7	2.16	2.32	0.89	26.29	-27.4	-23.6	-27.2	1.62	3.01	-69.8	-98.2	-121.9	-142.6	507.5	-137.54
4.25	90.58	6594.9	6575.3	6555.5	2.99	1.27	0.74	26.43	-26.4	-21.3	-26.1	0.80	1.94	-69.4	-98.1	-121.6	-141.4	606.7	-138.83
4.50	91.16	6618.8	6597.9	6579.0	2.44	2.01	-0.24	26.52	-27.0	-23.4	-27.0	0.04	1.47	-68.1	-96.3	-120.2	-140.8	851.6	-141.94

\*at 25°C unless mentioned otherwise



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

