

# NON-CATALOG

Surface Mount

# Voltage Controlled Oscillator

## ROS-3600-919+

Linear Tuning 3350 to 3600 MHz

### Features

- low phase noise
- low pushing
- low pulling
- aqueous washable

### Applications

- wireless communications
- WiMAX RF base station
- SAB / SAP



CASE STYLE: CK605

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications

| MODEL NO.     | FREQ. (MHz) |      | POWER OUTPUT (dBm) | PHASE NOISE dBc/Hz SSB at offset frequencies, kHz |      |      |      | TUNING |                   |                       |               |                                 | NON HARMONIC SPURIOUS (dBc) | HARMONICS (dBc) |      | PULLING pk-pk @12 dB (MHz) | PUSHING (MHz/V) | DC OPERATING POWER |      |      |             |              |
|---------------|-------------|------|--------------------|---|------|------|------|--------|-------------------|-----------------------|---------------|---------------------------------|-----------------------------|-----------------|------|----------------------------|-----------------|--------------------|------|------|-------------|--------------|
|               | Min.        | Max. |                    | Typ.  | 1    | 10   | 100  | 1000   | VOLTAGE RANGE (V) | SENSI- TIVITY (MHz/V) | PORT CAP (pF) | 3 dB MODULATION BANDWIDTH (MHz) |                             | Typ.            | Typ. |                            |                 | Max.               | Typ. | Typ. | Vcc (volts) | Current (mA) |
|               |             |      |                    |   |      |      |      |        |                   |                       |               |                                 |                             |                 |      |                            |                 |                    |      |      |             |              |
| ROS-3600-919+ | 3350        | 3600 | +5                 | -75   | -100 | -120 | -140 | 0.5    | 15                | 25-30                 | 30            | 300                             | -90                         | -29             | -17  | 1                          | 1               | 8                  | 52   |      |             |              |

### Pin Connections


|        |                                |
|--------|--------------------------------|
| RF OUT | 10                             |
| VCC    | 14                             |
| V-TUNE | 2                              |
| GROUND | 1,3,4,5,6,7,8,9,11,12,13,15,16 |

### Maximum Ratings


|                                      |                |
|--------------------------------------|----------------|
| Operating Temperature                | -55°C to 85°C  |
| Storage Temperature                  | -55°C to 100°C |
| Absolute Max. Supply Voltage (Vcc)   | 10V            |
| Absolute Max. Tuning Voltage (Vtune) | 17V            |
| All specifications                   | 50 ohm system  |

Permanent damage may occur if any of these limits are exceeded.

### Outline Drawing



### Demo Board MCL P/N: TB-10 Suggested PCB Layout (PL-012)



#### NOTES:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  2. BOTTOM SIDE OF THE BOTTOM IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Outline Dimensions (inch/mm)

| A     | B     | C    | D    | E    | F    | G    | H    | J     | K    | L    | M    | N    | P    | Q    | R    | S    | T    | wt.   |
|-------|-------|------|------|------|------|------|------|-------|------|------|------|------|------|------|------|------|------|-------|
| .500  | .500  | .180 | .100 | .080 | .115 | .060 | .040 | .540  | .060 | .100 | .135 | .135 | .115 | .140 | .070 | .150 | .070 | grams |
| 12.70 | 12.70 | 4.57 | 2.54 | 2.03 | 2.92 | 1.52 | 1.02 | 13.72 | 1.52 | 2.54 | 3.43 | 3.43 | 2.92 | 3.56 | 1.78 | 3.81 | 1.78 | 1.0   |



For detailed performance specs & shopping online see web site

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at [minicircuits.com](http://minicircuits.com)

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp).

REV. A  
M149087  
EDR-8525F1  
ROS-3600-919+  
RAV  
141229  
Page 1 of 2







# NON-CATALOG

## Performance Data & Curves\*

## ROS-3600-919+

| V TUNE | TUNE SENS (MHz/V) | FREQUENCY (MHz) |        |        | POWER OUTPUT (dBm) |       |       | Icc (mA) | HARMONICS (dBc) |       |       | FREQ. PUSH (MHz/V) | FREQ. PULL (MHz) | PHASE NOISE (dBc/Hz) at offsets |        |        |        | FREQ OFFSET (KHz) | PHASE NOISE at 3470 MHz (dBc/Hz) |
|--------|-------------------|-----------------|--------|--------|--------------------|-------|-------|----------|-----------------|-------|-------|--------------------|------------------|---------------------------------|--------|--------|--------|-------------------|----------------------------------|
|        |                   | -55°C           | +25°C  | +85°C  | -55°C              | +25°C | +85°C |          | F2              | F3    | F4    |                    |                  | 1kHz                            | 10kHz  | 100kHz | 1MHz   |                   |                                  |
| 0.00   | 30.73             | 3291.0          | 3278.5 | 3271.6 | 5.79               | 5.56  | 4.94  | 43.50    | -29.0           | -48.3 | -56.5 | 0.82               | 1.22             | -76.5                           | -102.2 | -122.5 | -142.2 | 1.0               | -75.86                           |
| 0.50   | 28.15             | 3305.9          | 3293.9 | 3286.8 | 5.81               | 5.40  | 4.83  | 43.47    | -29.4           | -46.2 | -58.3 | 0.97               | 1.89             | -75.5                           | -100.7 | -120.7 | -141.0 | 2.0               | -84.77                           |
| 1.00   | 24.77             | 3318.9          | 3308.0 | 3300.9 | 5.88               | 5.41  | 4.77  | 43.51    | -27.5           | -43.7 | -58.4 | 0.88               | 1.82             | -77.7                           | -101.7 | -122.3 | -142.1 | 3.5               | -90.66                           |
| 1.50   | 23.66             | 3331.2          | 3320.3 | 3313.8 | 5.95               | 5.51  | 4.84  | 43.55    | -27.8           | -45.0 | -58.3 | 0.85               | 1.40             | -77.3                           | -102.2 | -122.2 | -142.1 | 6.0               | -95.59                           |
| 2.00   | 23.44             | 3343.3          | 3332.2 | 3326.0 | 6.02               | 5.60  | 4.95  | 43.58    | -28.5           | -43.2 | -55.3 | 0.83               | 1.09             | -76.9                           | -101.8 | -122.6 | -142.9 | 8.5               | -99.69                           |
| 3.00   | 26.41             | 3367.2          | 3357.2 | 3349.9 | 5.96               | 5.55  | 5.15  | 43.55    | -28.4           | -42.6 | -56.1 | 0.95               | 1.20             | -77.0                           | -100.7 | -121.5 | -141.3 | 10.0              | -101.56                          |
| 4.00   | 25.38             | 3395.0          | 3383.1 | 3374.6 | 5.78               | 5.52  | 5.08  | 43.64    | -28.6           | -39.9 | -57.8 | 0.85               | 1.57             | -77.1                           | -101.4 | -122.6 | -142.2 | 20.8              | -108.27                          |
| 5.00   | 28.16             | 3421.4          | 3408.5 | 3402.1 | 5.97               | 5.53  | 4.92  | 43.66    | -28.4           | -41.0 | -58.2 | 0.86               | 1.04             | -74.5                           | -101.0 | -122.3 | -142.7 | 35.5              | -113.01                          |
| 6.00   | 26.68             | 3447.6          | 3436.3 | 3428.4 | 6.19               | 5.66  | 5.12  | 43.69    | -28.9           | -46.6 | -58.8 | 0.87               | 1.27             | -77.7                           | -101.8 | -122.2 | -141.9 | 60.7              | -117.29                          |
| 7.00   | 27.06             | 3474.9          | 3463.0 | 3454.6 | 6.03               | 5.81  | 5.36  | 43.77    | -29.4           | -52.3 | -58.2 | 0.84               | 1.38             | -77.7                           | -101.6 | -122.2 | -142.5 | 86.7              | -120.68                          |
| 8.00   | 28.60             | 3503.5          | 3491.1 | 3482.5 | 6.09               | 5.63  | 5.24  | 43.78    | -30.1           | -51.3 | -57.5 | 0.90               | 0.86             | -75.3                           | -101.5 | -121.4 | -141.6 | 100.0             | -121.98                          |
| 8.50   | 27.93             | 3517.5          | 3505.4 | 3496.9 | 6.25               | 5.68  | 5.21  | 43.82    | -29.6           | -50.4 | -58.0 | 0.87               | 0.87             | -75.8                           | -100.5 | -122.2 | -141.8 | 148.1             | -125.20                          |
| 9.00   | 27.75             | 3531.3          | 3519.4 | 3511.1 | 6.40               | 5.83  | 5.27  | 43.85    | -29.2           | -46.0 | -58.5 | 0.85               | 1.28             | -75.2                           | -101.5 | -122.3 | -141.9 | 177.0             | -126.75                          |
| 10.00  | 29.34             | 3559.9          | 3547.8 | 3539.1 | 6.44               | 6.05  | 5.59  | 43.88    | -30.6           | -45.3 | -59.1 | 0.86               | 1.38             | -75.1                           | -100.9 | -121.7 | -141.8 | 211.6             | -128.25                          |
| 11.00  | 29.11             | 3589.4          | 3577.0 | 3568.1 | 6.43               | 6.10  | 5.71  | 43.96    | -30.3           | -45.5 | -59.1 | 0.80               | 0.73             | -73.3                           | -101.5 | -122.2 | -142.4 | 302.4             | -131.08                          |
| 12.00  | 29.41             | 3618.3          | 3606.6 | 3597.5 | 6.62               | 6.10  | 5.75  | 43.99    | -31.3           | -46.8 | -58.6 | 0.78               | 1.43             | -73.9                           | -100.1 | -121.2 | -141.8 | 361.5             | -133.04                          |
| 13.00  | 28.33             | 3647.7          | 3635.6 | 3626.4 | 6.82               | 6.37  | 5.88  | 44.06    | -30.7           | -46.6 | -59.0 | 0.68               | 0.60             | -73.3                           | -100.1 | -121.9 | -141.6 | 507.5             | -136.33                          |
| 14.00  | 28.61             | 3676.6          | 3664.3 | 3655.2 | 6.76               | 6.49  | 6.13  | 44.08    | -32.0           | -51.1 | -58.5 | 0.62               | 1.34             | -73.1                           | -100.3 | -121.1 | -140.9 | 606.7             | -137.73                          |
| 14.50  | 27.94             | 3690.8          | 3678.6 | 3669.3 | 6.67               | 6.46  | 6.18  | 44.12    | -31.9           | -51.5 | -59.3 | 0.57               | 1.29             | -74.8                           | -100.1 | -120.8 | -141.3 | 851.6             | -140.79                          |
| 15.00  | 27.10             | 3704.6          | 3692.6 | 3683.2 | 6.66               | 6.39  | 6.16  | 44.14    | -32.2           | -53.1 | -59.0 | 0.51               | 1.30             | -74.7                           | -99.9  | -120.8 | -141.8 | 1000.0            | -141.60                          |

\*at 25°C unless mentioned otherwise



For detailed performance specs & shopping online see web site

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at [minicircuits.com](http://minicircuits.com)

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp).