

Coaxial High Pass Filter

NON-CATALOG

VHF-1200

50Ω 1220 to 4600 MHz



Maximum Ratings

Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
RF Power Input*	7W max.

* Passband rating, derate linearly to 3W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

Features

- rugged unibody construction, small size
- 7 sections
- temperature stable
- excellent power handling, 7W
- low cost

CASE STYLE: FF704

Connectors	Model
SMA	VHF-1200

Price: Contact Sales Dept.


Applications

- sub-harmonic rejection
- transmitters/receivers
- lab use

Electrical Specifications (T_{AMB}=25°C)

STOP BAND (MHz)		f _{co} , MHz	PASSBAND (MHz)		VSWR (:1)	NO. OF SECTIONS
Min.		Nom.	(loss < 1.3 dB)	(loss < 2 dB)	Typ.	
(loss > 40 dB)	(loss > 20 dB)	Typ.	Max.	Typ.	Stopband	
750	910	1180	1380-4000	1220-4600	1300-3200	7


Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1	104.60	1737.18
500	77.89	124.09
750	49.00	56.04
910	29.02	32.18
1050	13.46	12.18
1130	5.97	4.39
1180	3.08	2.29
1220	1.98	1.62
1300	1.24	1.39
1380	0.97	1.39
3200	0.46	1.43
4000	1.04	2.29
4600	1.72	3.14
7000	4.66	7.56



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

