

High IP3

Low Noise Amplifier

ZRL-1200+

50Ω

650 to 1200 MHz

Features

- High IP3, +46 dBm typ.
- Low Noise figure, 2.0 dB typ.
- Broadband flat gain response
- Internal voltage regulated
- Over-voltage and transient protected

Applications

- Low noise, high dynamic range
- Analog/digital cellular
- PCS, GSM, TDMA, CDMA
- UHF television
- Driver amplifier



Generic photo used for illustration purposes only

Case Style: FJ893

Connectors	Model
SMA	ZRL-1200+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Units
Frequency Range		650		1200	MHz
Noise Figure	650 - 1200	—	1.8	3.0	dB
	800 - 950	—	1.8	3.0	
Gain	650 - 1200	24	29	—	dB
	800 - 950	25	30	—	
Gain Flatness	650 - 1200	—	±0.8	±1.2	dB
	800 - 950	—	±0.4	±0.8	
Output Power at 1dB compression	650 - 1200	23.5	25	—	dBm
	800 - 950	23.5	25	—	
Output Power at 3dB compression	650 - 1200	—	25.7	—	dBm
	800 - 950	—	25.8	—	
Output third order intercept point ¹	650 - 1200	—	+46	—	dBm
	800 - 950	—	+46	—	
Input VSWR	650 - 1200	—	1.25	—	:1
	800 - 950	—	1.20	—	
Output VSWR	650 - 1200	—	1.25	—	:1
	800 - 950	—	1.20	—	
Active Directivity	650 - 1200	—	15	—	dB
	800 - 950	—	15	—	
DC Supply Voltage ²		—	12	—	V
Supply Current		—	540	575	mA

1. 1 MHz tone spacing.

2. Unit is internally voltage regulated for 6.5 to 17VDC input voltage range.

Maximum Ratings

Parameter	Ratings
Operating Temperature	-40°C to 80°C case -40°C to 60° ambient
Storage Temperature	-55°C to 100°C
DC Voltage	+17V
Input RF Power (no damage)	+10 dBm


Permanent damage may occur if any of these limits are exceeded.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Outline Drawing



Outline Dimensions (inch/mm)







A	B	C	D	E	F	G	H	J	K	L	M	N	P	wt
2.00	3.75	0.80	3.00	0.19	3.374	1.624	0.156	0.44	0.26	1.00	0.51	0.22	0.10	grams
50.80	95.25	20.32	76.20	4.83	85.70	41.25	3.96	11.18	6.60	25.40	12.95	5.59	2.54	135

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR (:1)		POUT at 1dB COMPR. (dBm)	NOISE FIGURE (dB)	OUTPUT IP3 (dBm)
	12V	12V	IN	OUT	12V	12V	12V
650	30.69	15.07	1.26	1.26	25.08	2.11	50.08
700	30.80	14.65	1.22	1.19	25.19	2.00	48.67
750	30.85	14.25	1.19	1.13	25.24	1.99	48.49
800	30.83	14.03	1.17	1.10	25.35	1.93	47.63
850	30.75	13.93	1.18	1.11	25.42	1.96	46.50
900	30.62	13.91	1.20	1.14	25.44	1.96	46.03
950	30.45	13.90	1.21	1.16	25.49	1.97	46.16
1000	30.25	13.91	1.21	1.15	25.51	1.99	45.97
1050	30.05	13.88	1.20	1.13	25.51	2.06	45.97
1100	29.82	14.03	1.18	1.11	25.50	2.09	45.73
1150	29.57	14.09	1.17	1.11	25.48	2.10	45.60
1200	29.29	14.28	1.20	1.15	25.47	2.10	45.40



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

