

Voltage Controlled Oscillator

ZX95-498+

5V Tuning for PLL IC's 449 to 499 MHz

Features

- linear tuning characteristics
- very low phase noise
- low pushing
- low pulling
- protected by US patent 6,790,049



CASE STYLE: GB956

Connectors	Model
SMA	ZX95-498-S+

Applications

- r & d
- lab
- instrumentation
- wireless broadband access
- GSM

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, kHz				TUNING					NON HARMONIC SPURIOUS (dBc)	HARMONICS (dBc)		PULLING pk-pk @12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER				
	Min.	Max.		Typ.	1	10	100	1000	VOLTAGE RANGE (V)	SENSI-TIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)		Typ.	Typ.			Max.	Typ.	Typ.	Vcc (volts)	Current (mA)
ZX95-498+	449	499	+5	-91	-118	-138	-158	0.25	5	13	100	22	-90	-20	-10	0.5	0.3	5	22			

Maximum Ratings


Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	7V
Absolute Max. Tuning Voltage (Vtune)	7V
All specifications	50 ohm system

Permanent damage may occur if any of these limits are exceeded.



NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note [AN-40-10](#).

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
1.20	.75	.46	1.18	.04	.38	.38	.57	.18	.33	.21	.22	.18	1.00	.50	.35	.18	.106	grams
30.48	19.05	11.68	29.97	1.02	9.65	9.65	14.48	4.57	8.38	5.33	5.59	4.57	25.40	12.70	8.89	4.57	2.69	35.0

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp









Performance Data & Curves*

ZX95-498+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (KHz)	PHASE NOISE at 474 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	17.26	439.7	437.5	435.1	4.33	4.18	3.24	14.06	-17.4	-60.7	-44.5	0.23	0.73	-88.8	-115.9	-136.8	-156.3	1.0	-90.08
0.50	14.60	447.7	445.7	443.6	4.70	4.58	3.90	14.40	-17.7	-67.2	-42.4	0.17	0.75	-89.2	-117.6	-137.5	-157.4	2.0	-99.36
0.75	13.98	451.3	449.3	447.3	4.83	4.71	4.09	14.54	-17.7	-61.7	-41.6	0.17	0.65	-91.3	-117.4	-138.0	-158.6	3.5	-107.45
1.00	13.59	454.7	452.8	450.9	4.95	4.82	4.24	14.66	-17.7	-58.8	-40.9	0.17	0.47	-91.4	-117.4	-138.2	-158.0	6.0	-113.15
1.25	13.36	458.1	456.2	454.3	5.04	4.91	4.35	14.77	-17.8	-57.8	-40.4	0.17	0.26	-90.0	-117.0	-138.0	-157.2	8.5	-117.13
1.50	13.24	461.4	459.6	457.6	5.10	4.97	4.44	14.87	-18.0	-56.9	-39.9	0.18	0.14	-90.6	-117.0	-138.1	-157.5	10.0	-117.74
1.75	13.19	464.7	462.9	461.0	5.13	5.01	4.50	14.95	-18.3	-56.3	-39.5	0.19	0.31	-90.2	-116.9	-138.5	-157.2	20.8	-125.20
2.00	13.20	468.0	466.2	464.3	5.14	5.03	4.55	15.02	-18.6	-55.7	-39.0	0.20	0.48	-91.7	-117.3	-138.5	-158.5	35.5	-129.74
2.25	13.23	471.2	469.5	467.6	5.13	5.04	4.59	15.08	-18.9	-54.7	-38.5	0.21	0.60	-92.2	-118.2	-138.7	-157.5	60.7	-134.40
2.50	13.28	474.5	472.8	470.9	5.09	5.03	4.60	15.12	-19.3	-53.3	-38.0	0.23	0.67	-90.8	-117.7	-138.9	-157.6	86.7	-137.62
2.75	13.34	477.8	476.1	474.2	5.04	5.00	4.60	15.15	-19.8	-51.5	-37.6	0.25	0.69	-91.4	-117.8	-139.1	-158.0	100.0	-138.82
3.00	13.40	481.1	479.4	477.6	4.97	4.96	4.59	15.17	-20.3	-49.7	-37.1	0.27	0.65	-91.8	-118.9	-138.9	-157.3	148.1	-142.54
3.25	13.47	484.5	482.8	481.0	4.89	4.90	4.56	15.18	-20.7	-48.2	-36.8	0.30	0.56	-90.1	-117.6	-139.9	-157.7	177.0	-144.01
3.50	13.54	487.8	486.2	484.4	4.79	4.82	4.52	15.19	-21.1	-46.5	-36.7	0.32	0.47	-89.5	-119.2	-139.5	-157.3	211.6	-145.27
3.75	13.60	491.1	489.5	487.8	4.67	4.73	4.45	15.18	-21.3	-44.9	-36.7	0.34	0.32	-90.1	-119.3	-140.0	-157.1	302.4	-148.29
4.00	13.66	494.5	492.9	491.2	4.53	4.62	4.38	15.17	-21.6	-43.7	-36.7	0.36	0.24	-89.9	-118.9	-140.2	-158.0	361.5	-149.66
4.25	13.72	497.9	496.3	494.7	4.38	4.50	4.29	15.14	-21.9	-42.5	-36.6	0.38	0.38	-90.4	-118.9	-140.3	-157.8	507.5	-152.76
4.50	13.77	501.3	499.8	498.1	4.22	4.36	4.19	15.11	-22.3	-41.3	-36.4	0.39	0.60	-88.5	-119.7	-140.4	-158.9	606.7	-154.22
4.75	13.82	504.7	503.2	501.6	4.04	4.21	4.07	15.07	-22.7	-39.9	-36.1	0.39	0.75	-88.2	-119.3	-140.2	-158.4	851.6	-156.86
5.00	13.87	508.2	506.7	505.1	3.86	4.05	3.94	15.03	-22.8	-38.7	-36.2	0.39	0.81	-88.7	-118.6	-140.5	-157.3	1000.0	-158.13

*at 25°C unless mentioned otherwise



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

