

Coaxial

# Voltage Controlled Oscillator

# ZX95-625+

Wide Band 280 to 625 MHz

## Features

- wide band frequency
- low phase noise
- low pushing
- protected by US patent 6,790,049



CASE STYLE: GB956

## Applications

- r & d
- lab
- instrumentation
- wireless communications
- broadcast equipment

| Connectors | Model       |
|------------|-------------|
| SMA        | ZX95-625-S+ |

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Electrical Specifications

| MODEL NO. | FREQ. (MHz) |      | POWER OUTPUT (dBm) | PHASE NOISE dBc/Hz SSB at offset frequencies, kHz |      |      |      | TUNING |                   |                     |               |                                 | NON HARMONIC SPURIOUS (dBc) | HARMONICS (dBc) |      | PULLING pk-pk @12 dB (MHz) | PUSHING (MHz/V) | DC OPERATING POWER |      |      |         |
|-----------|-------------|------|--------------------|---|------|------|------|--------|-------------------|---------------------|---------------|---------------------------------|-----------------------------|-----------------|------|----------------------------|-----------------|--------------------|------|------|---------|
|           | Min.        | Max. |                    | Typ.  | 1    | 10   | 100  | 1000   | VOLTAGE RANGE (V) | SENSITIVITY (MHz/V) | PORT CAP (pF) | 3 dB MODULATION BANDWIDTH (MHz) |                             | Typ.            | Max. |                            |                 | Typ.               | Max. | Vcc  | Current |
|           |             |      |                    |   | Typ. |      |      |        | Min.              | Max.                | Typ.          | Typ.                            |                             | Typ.            | Max. |                            |                 |                    |      | Max. |         |
| ZX95-625+ | 280         | 625  | +6.4               | -78   | -104 | -125 | -146 | 0.3    | 18                | 14-30               | 185           | 25                              | -90                         | -24             | -    | 1                          | 0.8             | 10                 | 30   |      |         |

## Maximum Ratings


|                                      |                |
|--------------------------------------|----------------|
| Operating Temperature                | -55°C to 85°C  |
| Storage Temperature                  | -55°C to 100°C |
| Absolute Max. Supply Voltage (Vcc)   | 12V            |
| Absolute Max. Tuning Voltage (Vtune) | 20V            |
| All specifications                   | 50 ohm system  |

Permanent damage may occur if any of these limits are exceeded.



NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note [AN-40-10](#).

## Outline Drawing



## Outline Dimensions (inch/mm)

| A     | B     | C     | D     | E    | F    | G    | H     | J    | K    | L    | M    | N    | P     | Q     | R    | S    | T    | wt.   |
|-------|-------|-------|-------|------|------|------|-------|------|------|------|------|------|-------|-------|------|------|------|-------|
| 1.20  | .75   | .46   | 1.18  | .04  | .38  | .38  | .57   | .18  | .33  | .21  | .22  | .18  | 1.00  | .50   | .35  | .18  | .106 | grams |
| 30.48 | 19.05 | 11.68 | 29.97 | 1.02 | 9.65 | 9.65 | 14.48 | 4.57 | 8.38 | 5.33 | 5.59 | 4.57 | 25.40 | 12.70 | 8.89 | 4.57 | 2.69 | 35.0  |

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com







REV. A  
M152326  
EDR-9223F2  
ZX95-625+  
RAV  
150923  
Page 1 of 2

# Performance Data & Curves\*

# ZX95-625+

| V TUNE | TUNE SENS (MHz/V) | FREQUENCY (MHz) |       |       | POWER OUTPUT (dBm) |       |       | Icc (mA) | HARMONICS (dBc) |       |       | FREQ. PUSH (MHz/V) | FREQ. PULL (MHz) | PHASE NOISE (dBc/Hz) at offsets |        |        |        | FREQ OFFSET (KHz) | PHASE NOISE at 453 MHz (dBc/Hz) |
|--------|-------------------|-----------------|-------|-------|--------------------|-------|-------|----------|-----------------|-------|-------|--------------------|------------------|---------------------------------|--------|--------|--------|-------------------|---------------------------------|
|        |                   | -55°C           | +25°C | +85°C | -55°C              | +25°C | +85°C |          | F2              | F3    | F4    |                    |                  | 1kHz                            | 10kHz  | 100kHz | 1MHz   |                   |                                 |
| 0.00   | 39.37             | 243.8           | 242.0 | 239.3 | 7.48               | 6.93  | 6.82  | 17.27    | -15.9           | -14.3 | -29.7 | 0.29               | 0.76             | -77.0                           | -98.0  | -118.8 | -139.9 | 1.0               | -82.44                          |
| 0.30   | 35.34             | 255.5           | 253.8 | 251.6 | 7.28               | 6.80  | 6.70  | 17.39    | -16.3           | -17.2 | -34.0 | 0.23               | 0.58             | -78.1                           | -99.4  | -120.2 | -141.2 | 2.0               | -89.91                          |
| 1.00   | 28.73             | 279.6           | 278.0 | 276.3 | 7.11               | 6.62  | 6.48  | 17.66    | -15.4           | -25.1 | -44.9 | 0.11               | 0.01             | -80.9                           | -102.9 | -123.1 | -143.7 | 3.5               | -96.96                          |
| 2.00   | 26.90             | 307.2           | 305.9 | 304.2 | 7.31               | 6.66  | 6.39  | 18.03    | -13.5           | -33.8 | -43.0 | 0.04               | 0.65             | -74.7                           | -102.2 | -124.5 | -144.1 | 6.0               | -100.94                         |
| 3.00   | 28.43             | 334.7           | 333.1 | 331.2 | 7.31               | 6.66  | 6.36  | 18.37    | -12.4           | -40.5 | -42.3 | 0.04               | 1.13             | -75.0                           | -101.1 | -124.0 | -143.8 | 8.5               | -103.70                         |
| 4.00   | 29.59             | 364.1           | 361.9 | 359.4 | 7.01               | 6.54  | 6.25  | 18.70    | -12.6           | -49.1 | -45.3 | 0.04               | 0.42             | -75.0                           | -102.8 | -124.8 | -144.5 | 10.0              | -105.33                         |
| 5.00   | 30.00             | 394.5           | 391.6 | 388.6 | 6.69               | 6.43  | 6.21  | 18.96    | -14.0           | -48.6 | -43.7 | 0.11               | 0.39             | -79.3                           | -103.0 | -125.6 | -145.5 | 20.8              | -111.42                         |
| 6.00   | 29.63             | 424.8           | 421.6 | 418.2 | 6.32               | 6.20  | 6.09  | 19.16    | -16.9           | -45.4 | -42.5 | 0.14               | 1.08             | -82.3                           | -104.1 | -125.2 | -145.3 | 35.5              | -116.70                         |
| 7.00   | 28.00             | 454.5           | 451.0 | 447.0 | 5.98               | 5.99  | 5.96  | 19.36    | -18.5           | -45.2 | -44.9 | 0.10               | 1.46             | -82.9                           | -105.7 | -125.6 | -146.0 | 60.7              | -121.11                         |
| 8.00   | 25.28             | 482.4           | 478.3 | 473.8 | 5.99               | 6.05  | 6.02  | 19.57    | -22.9           | -46.4 | -48.8 | 0.07               | 1.23             | -80.7                           | -103.1 | -125.7 | -146.8 | 86.7              | -124.34                         |
| 9.00   | 22.71             | 507.3           | 502.9 | 497.9 | 6.17               | 6.25  | 6.20  | 19.75    | -24.7           | -45.2 | -54.1 | 0.33               | 0.44             | -79.5                           | -104.5 | -126.1 | -147.6 | 100.0             | -125.46                         |
| 10.00  | 20.87             | 529.9           | 525.1 | 519.8 | 6.27               | 6.36  | 6.29  | 19.84    | -30.0           | -43.4 | -55.3 | 0.61               | 0.62             | -76.0                           | -103.2 | -126.5 | -147.9 | 148.1             | -129.18                         |
| 11.00  | 19.35             | 550.6           | 545.6 | 540.0 | 6.37               | 6.43  | 6.33  | 19.89    | -34.7           | -42.5 | -49.1 | 0.88               | 1.68             | -76.6                           | -103.2 | -126.5 | -148.3 | 177.0             | -130.61                         |
| 12.00  | 17.74             | 569.6           | 564.5 | 558.8 | 6.48               | 6.51  | 6.36  | 19.93    | -37.2           | -42.7 | -44.6 | 1.08               | 2.27             | -76.4                           | -103.4 | -126.6 | -148.1 | 211.6             | -131.99                         |
| 13.00  | 16.66             | 587.1           | 582.0 | 576.2 | 6.57               | 6.59  | 6.41  | 19.90    | -35.4           | -43.1 | -41.9 | 1.23               | 2.17             | -75.9                           | -103.1 | -126.6 | -148.4 | 302.4             | -135.45                         |
| 14.00  | 15.68             | 603.6           | 598.4 | 592.5 | 6.57               | 6.61  | 6.42  | 19.83    | -33.2           | -44.2 | -39.4 | 1.40               | 1.71             | -74.2                           | -103.0 | -126.7 | -147.9 | 361.5             | -136.75                         |
| 15.00  | 14.77             | 619.2           | 613.8 | 607.8 | 6.50               | 6.55  | 6.37  | 19.75    | -31.4           | -44.3 | -37.2 | 1.60               | 1.10             | -76.2                           | -102.1 | -126.4 | -147.7 | 507.5             | -139.96                         |
| 16.00  | 13.75             | 633.8           | 628.4 | 622.3 | 6.39               | 6.44  | 6.26  | 19.68    | -30.2           | -43.5 | -35.8 | 1.83               | 0.49             | -75.3                           | -102.7 | -126.2 | -147.5 | 606.7             | -141.49                         |
| 17.00  | 12.32             | 647.0           | 641.8 | 635.8 | 6.30               | 6.34  | 6.14  | 19.61    | -29.3           | -42.0 | -34.0 | 1.98               | 0.10             | -74.7                           | -103.2 | -126.2 | -147.0 | 851.6             | -144.17                         |
| 18.00  | 11.19             | 658.9           | 653.8 | 648.0 | 6.21               | 6.25  | 6.05  | 19.52    | -28.9           | -40.1 | -33.0 | 2.19               | 0.61             | -74.9                           | -102.6 | -125.9 | -146.5 | 1000.0            | -145.10                         |

\*at 25°C unless mentioned otherwise



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

