

Coaxial

# Voltage Controlled Oscillator

## ZX95-3015+

Linear Tuning 2570 to 3015 MHz

### Features

- high power, +9 dBm typ.
- low phase noise
- low pushing
- protected by US patent 6,790,049

### Applications

- r & d
- lab
- instrumentation
- CATV
- satellite systems



CASE STYLE: GB956

Connectors	Model
SMA	ZX95-3015-S+

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, KHz				TUNING					NON HARMONIC SPURIOUS (dBc)	HARMONICS (dBc)		PULLING pk-pk @ 12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER	
	Min.	Max.		Typ.	1	10	100	1000	VOLTAGE RANGE (V)	SENSITIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)		Typ.	Typ.			Typ.	Typ.
ZX95-3015+	2570	3015	+9	-72	-99	-120	-140	0.5	24	30-43	30	60	-90	-14	-	17	0.8	10	35

### Maximum Ratings


Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	12V
Absolute Max. Tuning Voltage (Vtune)	26V
All specifications	50 ohm system

Permanent damage may occur if any of these limits are exceeded.



NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note AN-40-10.

### Outline Drawing



### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
1.20	.75	.46	1.18	.04	.38	.38	.57	.18	.33	.21	.22	.18	1.00	.50	.35	.18	.106	grams
30.48	19.05	11.68	29.97	1.02	9.65	9.65	14.48	4.57	8.38	5.33	5.59	4.57	25.40	12.70	8.89	4.57	2.69	35.0

#### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com







REV. A  
M152326  
EDR-6434/1  
ZX95-3015+  
RAV  
150923  
Page 1 of 2

# Performance Data & Curves\*

# ZX95-3015+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (KHz)	PHASE NOISE at 2793 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	35.84	2450.6	2426.9	2409.9	8.97	8.98	8.50	29.76	-15.1	-20.4	-42.6	1.65	11.43	-70.3	-98.0	-118.4	-139.1	1.0	-70.41
0.50	32.69	2467.9	2444.8	2427.5	9.22	8.86	8.39	29.75	-14.8	-20.9	-42.7	1.67	16.44	-71.7	-97.8	-118.5	-138.8	2.0	-82.16
2.00	26.01	2512.9	2492.3	2475.2	9.05	8.83	8.24	29.74	-14.4	-21.6	-42.5	1.65	10.56	-73.3	-97.7	-118.5	-138.5	3.5	-87.08
3.00	26.70	2539.1	2518.3	2502.7	8.90	8.89	8.37	29.76	-14.0	-21.7	-42.3	1.46	22.61	-72.6	-98.4	-119.7	-139.9	6.0	-93.41
4.00	28.67	2566.9	2545.0	2527.9	8.90	8.75	8.35	29.73	-13.6	-21.4	-41.2	1.57	22.77	-73.1	-97.3	-118.7	-139.0	8.5	-97.22
5.00	29.72	2595.0	2573.7	2556.5	9.35	8.83	8.32	29.73	-13.2	-21.3	-40.4	1.45	10.19	-72.6	-98.1	-119.0	-139.2	10.0	-98.42
6.00	31.47	2624.7	2603.4	2586.4	9.50	8.93	8.49	29.73	-12.7	-22.5	-40.7	1.37	19.36	-73.3	-98.9	-119.5	-139.2	20.8	-104.95
8.00	35.48	2692.0	2669.4	2651.7	9.05	9.26	8.88	29.74	-12.6	-24.1	-41.7	0.99	22.57	-72.4	-98.9	-119.8	-140.3	35.5	-110.09
10.00	41.15	2764.5	2741.9	2726.8	9.86	9.46	8.86	29.75	-14.0	-29.8	-47.5	0.59	17.01	-71.8	-98.3	-119.8	-139.8	60.7	-114.57
12.00	43.01	2842.1	2824.4	2811.0	9.67	8.85	8.25	29.73	-15.4	-33.6	-54.7	0.54	23.60	-71.4	-98.1	-119.1	-138.8	86.7	-118.34
13.00	40.43	2886.6	2867.5	2852.1	9.19	8.46	8.06	29.71	-15.1	-31.9	-57.1	0.57	20.38	-71.6	-98.3	-119.9	-139.4	100.0	-119.32
14.00	37.42	2926.7	2907.9	2893.0	8.34	8.26	7.94	29.73	-14.7	-32.0	-55.1	0.59	13.81	-70.4	-98.4	-119.3	-139.9	148.1	-123.05
16.00	33.45	3003.4	2981.6	2964.7	8.23	8.04	7.93	29.72	-14.1	-30.7	-54.9	0.69	19.13	-71.1	-99.1	-119.7	-139.1	177.0	-124.26
18.00	28.23	3067.6	3045.2	3028.0	7.90	8.01	8.07	29.74	-13.5	-31.8	-52.8	0.74	18.46	-70.1	-97.9	-119.2	-139.2	211.6	-125.89
19.00	26.37	3097.5	3073.5	3055.7	8.28	8.02	7.90	29.73	-13.9	-32.8	-54.2	0.76	10.31	-69.7	-97.1	-118.8	-139.2	302.4	-129.05
20.00	22.42	3123.4	3099.8	3081.2	8.28	8.12	7.84	29.75	-13.9	-33.9	-53.8	0.77	22.68	-68.6	-97.5	-119.1	-139.3	361.5	-129.93
21.00	18.64	3145.1	3122.3	3103.9	8.34	8.12	8.04	29.77	-13.7	-34.0	-58.1	0.75	18.85	-68.2	-97.6	-119.6	-139.7	507.5	-133.59
22.00	16.81	3164.9	3140.9	3123.3	8.32	8.07	8.16	29.79	-13.9	-35.4	-60.8	0.76	3.81	-72.0	-98.9	-119.7	-139.9	606.7	-135.04
23.00	16.37	3183.7	3157.7	3139.7	7.88	8.06	8.18	29.79	-14.0	-35.7	-59.3	0.79	11.18	-73.3	-98.2	-119.7	-139.3	851.6	-137.77
24.00	15.19	3199.8	3174.1	3154.5	8.27	8.08	8.10	29.78	-14.1	-35.8	-60.5	0.85	16.32	-71.8	-98.5	-118.8	-139.1	1000.0	-139.34

\*at 25°C unless mentioned otherwise



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

