

Coaxial Directional Coupler

ZNDC-18-2G-S+

50Ω 18dB 800 to 2000 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power input	3W Max.

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

INPUT	1
OUTPUT	2
COUPLED	3

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	
2.00	1.25	0.75	0.17	1.656	0.15	
50.80	31.75	19.05	4.32	42.06	3.81	
G	H	J	K			wt
0.14	0.63	0.44	0.38			grams
3.56	16.00	11.18	9.65			57.0

Features

- excellent mainline loss, 0.5 dB typ.
- excellent VSWR, 1.15:1 typ.
- very flat coupling ± 0.3 dB typ.

Applications

- cellular
- PCS
- ISM



Generic photo used for illustration purposes only

CASE STYLE: FM587

Connectors Model No.
SMA ZNDC-18-2G-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Directional Coupler Electrical Specifications

FREQ. RANGE (MHz)	COUPLING (dB)		MAINLINE LOSS (dB)		DIRECTIVITY (dB)		VSWR (:1)	POWER INPUT (W)
	Nom.	Max. Flatness	Typ.	Max.	Typ.	Min.		
800-2000								
800-1000	18.5±0.5	±0.3	0.3	0.6	22	17	1.1	3
1000-1700	18.2±0.5	±0.4	0.5	0.9	22	18	1.2	3
1700-2000	18.0±0.5	±0.35	0.6	1.1	25	14	1.3	3


Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
800.00	0.35	18.76	23.37	21.37	21.29	21.05
900.00	0.36	18.64	24.53	22.59	22.52	21.97
1000.00	0.38	18.53	25.86	24.03	23.48	22.73
1100.00	0.41	18.42	27.49	25.01	24.10	23.40
1300.00	0.46	18.23	30.98	25.09	23.78	23.61
1500.00	0.53	18.09	39.09	23.97	22.61	21.52
1700.00	0.58	17.98	35.88	23.18	21.27	19.43
1800.00	0.63	17.96	29.68	22.92	20.69	18.20
1900.00	0.67	17.97	25.97	22.85	20.31	16.89
2000.00	0.70	17.98	22.69	23.35	20.36	15.85


ZNDC-18-2G-S+ MAINLINE LOSS




ZNDC-18-2G-S+ COUPLING & DIRECTIVITY



ZNDC-18-2G-S+ RETURN LOSS



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. F
M171494
ED-10022
ZNDC-18-2G+
WZ/TD/CP/AM
190129
Page 1 of 1

Directional Coupler

ZNDC-18-2G+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	(dB) OUT	CPL
800.0	0.35	18.76	23.37	21.37	21.29	21.05
810.0	0.35	18.75	23.52	21.50	21.33	21.14
825.0	0.35	18.73	23.79	21.75	21.43	21.25
850.0	0.36	18.70	23.89	22.18	21.89	21.48
875.0	0.36	18.67	24.14	22.41	22.24	21.75
900.0	0.36	18.64	24.53	22.59	22.52	21.97
925.0	0.37	18.61	24.91	23.11	22.68	22.15
950.0	0.37	18.58	25.02	23.40	23.06	22.31
975.0	0.38	18.56	25.23	23.48	23.29	22.44
1000.0	0.38	18.53	25.86	24.03	23.48	22.73
1025.0	0.39	18.50	26.04	24.21	23.64	23.02
1050.0	0.39	18.47	26.29	24.24	23.82	23.07
1075.0	0.40	18.44	26.67	24.73	24.13	23.13
1100.0	0.41	18.42	27.49	25.01	24.10	23.40
1150.0	0.42	18.37	27.78	25.10	24.07	23.48
1200.0	0.43	18.31	28.80	25.23	24.23	23.79
1250.0	0.45	18.27	29.66	25.47	24.30	23.58
1300.0	0.46	18.23	30.98	25.09	23.78	23.61
1350.0	0.48	18.19	32.64	24.80	24.02	23.31
1400.0	0.50	18.15	34.14	24.57	23.07	22.66
1450.0	0.51	18.12	36.73	24.31	23.19	22.59
1500.0	0.53	18.09	39.09	23.97	22.61	21.52
1550.0	0.55	18.06	44.38	23.61	22.11	21.33
1600.0	0.56	18.04	46.64	23.15	21.94	20.48
1625.0	0.57	18.02	43.66	23.40	21.67	20.36
1650.0	0.58	18.01	41.88	23.07	21.32	19.80
1675.0	0.58	17.99	38.60	22.85	21.48	19.50
1700.0	0.58	17.98	35.88	23.18	21.27	19.43
1725.0	0.60	17.97	33.83	22.99	20.91	18.89
1750.0	0.60	17.97	33.35	22.70	20.80	18.46
1775.0	0.61	17.96	31.33	22.84	20.90	18.48
1800.0	0.63	17.96	29.68	22.92	20.69	18.20
1825.0	0.64	17.97	28.68	22.66	20.58	17.64
1850.0	0.64	17.97	28.20	22.74	20.52	17.50
1875.0	0.65	17.97	26.99	23.16	20.31	17.38
1900.0	0.67	17.97	25.97	22.85	20.31	16.89
1925.0	0.67	17.97	25.38	22.81	20.28	16.63
1950.0	0.68	17.97	24.55	23.32	20.13	16.57
1975.0	0.70	17.98	23.59	23.25	20.14	16.20
2000.0	0.70	17.98	22.69	23.35	20.36	15.85

REV. X1
ZNDC-18-2G+
060718
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661






The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Directional Coupler

ZNDC-18-2G+

Typical Performance Curves



Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	WT, GRAM
FM587	2.00 (50.80)	1.24 (31.50)	.75 (19.05)	.17 (4.32)	1.656 (42.06)	.15 (3.81)	.140 (3.56)	.62 (15.75)	.44 (11.18)	.38 (9.65)	57

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:

For RoHS Case Styles:

Clear chemical conversion coating, non-chrome or trivalent chrome based.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I