

Coaxial

Voltage Controlled Oscillator

ZX95-4000+

Linear Tuning 3850 to 4000 MHz

Features

- linear tuning characteristics
- low phase noise
- low pushing
- low pulling
- protected by US patent 6,790,049

Applications

- r & d
- lab
- instrumentation
- wireless communications
- WiMAX



CASE STYLE: GB956

Connectors	Model
SMA	ZX95-4000-S+

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, KHz				TUNING					NON HARMONIC SPURIOUS (dBc)	HARMONICS (dBc)		PULLING pk-pk @12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER	
	Min.	Max.		Typ.	1	10	100	1000	VOLTAGE RANGE (V)	SENSI- TIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)		Typ.	Typ.			Max.	Typ.
ZX95-4000+	3850	4000	+5	-72	-96	-117	-137	0.5	10	26-36	50	13	-90	-26	-15	3	2.5	5	40

Maximum Ratings


Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	7V
Absolute Max. Tuning Voltage (Vtune)	12V
All specifications	50 ohm system

Permanent damage may occur if any of these limits are exceeded.



NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note AN-40-10.

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
1.20	.75	.46	1.18	.04	.38	.38	.57	.18	.33	.21	.22	.18	1.00	.50	.35	.18	.106	grams
30.48	19.05	11.68	29.97	1.02	9.65	9.65	14.48	4.57	8.38	5.33	5.59	4.57	25.40	12.70	8.89	4.57	2.69	35.0

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com







REV. B
M152326
EDR-7880
ZX95-4000+
RAV
151016
Page 1 of 2

Performance Data & Curves*

ZX95-4000+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (KHz)	PHASE NOISE at 3925 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	25.05	3783.5	3769.7	3761.9	5.18	4.94	3.56	34.10	-26.7	-41.5	-50.9	2.91	1.12	-73.1	-96.0	-117.0	-137.2	1.0	-73.30
0.50	22.50	3795.5	3782.2	3774.5	5.13	4.95	3.64	34.14	-27.3	-42.8	-53.0	2.92	1.16	-74.3	-96.3	-117.1	-137.3	2.0	-81.28
1.00	21.38	3806.4	3793.5	3785.7	5.25	4.94	3.69	34.17	-26.9	-43.8	-53.8	2.90	2.10	-72.6	-96.1	-116.7	-136.9	3.5	-85.58
1.50	20.82	3817.3	3804.2	3796.3	5.23	4.94	3.73	34.21	-26.4	-45.0	-55.4	2.79	2.89	-70.8	-95.7	-116.7	-136.8	6.0	-91.83
2.00	21.71	3828.2	3814.6	3806.5	5.22	5.00	3.78	34.24	-26.1	-46.2	-57.7	2.74	3.37	-71.1	-96.2	-116.6	-137.1	8.5	-93.62
2.50	22.95	3839.3	3825.4	3817.0	5.25	5.06	3.87	34.26	-26.0	-47.2	-55.2	2.78	3.40	-74.4	-96.7	-117.3	-137.2	10.0	-95.95
3.00	23.78	3851.0	3836.9	3828.2	5.27	5.07	3.95	34.29	-25.8	-48.7	-53.3	2.76	3.13	-73.9	-96.7	-117.3	-137.4	20.8	-102.85
3.50	24.82	3863.4	3848.8	3839.7	5.25	5.05	4.02	34.33	-25.3	-50.3	-50.4	2.62	1.80	-73.9	-96.1	-117.1	-137.3	35.5	-107.67
4.00	26.26	3875.7	3861.2	3851.9	5.31	5.13	4.12	34.37	-25.3	-51.2	-50.1	2.61	1.33	-72.5	-96.4	-117.1	-137.2	60.7	-112.75
4.50	27.84	3889.0	3874.3	3865.1	5.42	5.20	4.18	34.41	-25.8	-52.7	-48.6	2.49	2.73	-72.1	-95.2	-117.0	-136.8	86.7	-115.66
5.00	29.08	3903.4	3888.2	3878.5	5.44	5.21	4.26	34.45	-26.6	-54.6	-54.5	2.41	3.59	-73.6	-95.6	-116.9	-137.1	100.0	-116.92
6.00	33.19	3934.3	3917.9	3907.8	5.52	5.37	4.46	34.52	-26.2	-56.4	-51.6	2.02	2.96	-73.3	-96.0	-116.7	-136.2	148.1	-120.21
6.50	34.17	3951.1	3934.5	3923.5	5.44	5.38	4.55	34.55	-25.5	-57.7	-52.6	1.82	1.57	-73.9	-95.7	-116.3	-136.5	177.0	-121.98
7.00	34.81	3968.2	3951.6	3940.4	5.65	5.40	4.62	34.59	-25.7	-58.5	-53.1	1.44	2.21	-71.8	-95.5	-116.6	-136.5	211.6	-123.60
7.50	36.39	3986.6	3969.0	3957.7	5.69	5.52	4.57	34.60	-26.1	-58.2	-54.6	1.04	3.47	-70.1	-95.5	-116.5	-136.6	302.4	-126.37
8.00	34.88	4004.2	3987.2	3975.0	5.73	5.56	4.74	34.60	-26.2	-57.9	-54.4	0.60	3.37	-69.2	-94.2	-115.7	-135.8	361.5	-128.09
8.50	36.62	4022.8	4004.7	3993.3	5.69	5.59	4.74	34.60	-25.9	-56.6	-53.3	0.04	2.06	-70.7	-94.6	-115.6	-136.0	507.5	-130.92
9.00	35.91	4040.9	4023.0	4010.8	5.64	5.55	4.80	34.56	-25.6	-56.9	-53.2	0.38	2.34	-68.7	-94.1	-115.9	-135.7	606.7	-132.12
9.50	34.94	4059.4	4040.9	4028.9	5.70	5.48	4.76	34.53	-25.8	-55.4	-51.7	0.84	3.32	-68.5	-93.3	-114.8	-134.6	851.6	-135.48
10.00	36.62	4077.8	4058.4	4046.3	5.61	5.52	4.70	34.45	-26.8	-55.8	-50.0	1.24	4.00	-69.8	-94.3	-115.7	-135.8	1000.0	-136.75

*at 25°C unless mentioned otherwise



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

