

# Voltage Controlled Oscillator

## ZX95-530+

5V Tuning for PLL IC's 500 to 530 MHz

### Features

- linear tuning characteristics
- low phase noise
- low pushing
- low pulling
- 0.5-5V tuning voltage range
- protected by US patent 6,790,049



CASE STYLE: GB956

Connectors	Model
SMA	ZX95-530-S+

### Applications

- r & d
- lab
- instrumentation
- PLL circuitry
- wireless microphones

**+RoHS Compliant**  
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, KHz				TUNING					NON HARMONIC SPURIOUS (dBc)	HARMONICS (dBc)		PULLING pk-pk @12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER						
								VOLTAGE RANGE (V)	SENSI-TIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)	Typ.								Typ.	Typ.	Typ.	Typ.	Typ.
ZX95-530+	500	530	-0.5	-90	-111	-132	-151	0.5	5	10 - 11	70	80	-90	-23	-15	0.4	0.1	5	15					


### Maximum Ratings

Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	7V
Absolute Max. Tuning Voltage (Vtune)	7V
All specifications	50 ohm system

Permanent damage may occur if any of these limits are exceeded.

**NOTE:** When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note AN-40-10.

### Outline Drawing



### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
1.20	.75	.46	1.18	.04	.38	.38	.57	.18	.33	.21	.22	.18	1.00	.50	.35	.18	.106	grams
30.48	19.05	11.68	29.97	1.02	9.65	9.65	14.48	4.57	8.38	5.33	5.59	4.57	25.40	12.70	8.89	4.57	2.69	35.0

#### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




# Performance Data & Curves\*

# ZX95-530+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (KHz)	PHASE NOISE at 512 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	12.47	487.3	485.0	482.9	-0.98	-0.62	-0.47	10.05	-21.5	-35.0	-44.4	0.07	0.19	-89.6	-111.8	-132.3	-151.7	1.0	-87.58
0.50	10.89	493.1	491.0	489.1	-0.95	-0.56	-0.39	10.06	-22.2	-35.4	-45.3	0.03	0.21	-88.9	-111.5	-132.3	-151.0	2.0	-96.63
0.75	10.58	495.8	493.7	491.8	-0.94	-0.54	-0.36	10.07	-22.3	-35.5	-45.3	0.01	0.21	-90.2	-111.8	-132.5	-152.1	3.5	-101.36
1.00	10.42	498.5	496.3	494.5	-0.92	-0.51	-0.32	10.07	-22.3	-35.4	-45.4	0.01	0.22	-91.5	-111.8	-132.1	-150.2	6.0	-106.39
1.25	10.38	501.1	498.9	497.0	-0.91	-0.48	-0.29	10.08	-22.4	-35.1	-45.2	0.02	0.22	-89.3	-111.2	-132.1	-151.7	8.5	-109.63
1.50	10.41	503.7	501.5	499.6	-0.89	-0.45	-0.25	10.08	-22.5	-35.1	-45.0	0.03	0.23	-90.3	-111.8	-132.0	-150.8	10.0	-111.36
1.75	10.50	506.4	504.1	502.2	-0.87	-0.42	-0.23	10.08	-22.7	-35.3	-44.6	0.03	0.23	-88.4	-111.2	-132.2	-150.9	20.8	-118.46
2.00	10.63	509.0	506.8	504.8	-0.84	-0.39	-0.20	10.09	-22.9	-35.2	-44.7	0.03	0.24	-90.3	-112.1	-132.2	-150.5	35.5	-123.18
2.25	10.78	511.7	509.4	507.4	-0.81	-0.37	-0.18	10.09	-23.0	-35.0	-44.4	0.03	0.24	-89.8	-110.9	-132.0	-150.2	60.7	-127.58
2.50	10.94	514.5	512.1	510.1	-0.78	-0.35	-0.17	10.09	-23.1	-34.9	-44.4	0.01	0.25	-89.1	-111.5	-131.7	-150.8	86.7	-130.46
2.75	11.09	517.2	514.9	512.8	-0.75	-0.33	-0.15	10.10	-23.2	-34.7	-44.0	0.00	0.26	-88.1	-111.5	-131.8	-150.4	100.0	-131.97
3.00	11.23	520.0	517.6	515.6	-0.73	-0.32	-0.14	10.10	-23.1	-34.6	-43.8	0.02	0.29	-89.1	-112.2	-132.0	-151.2	148.1	-135.15
3.25	11.32	522.9	520.4	518.3	-0.72	-0.32	-0.14	10.10	-23.1	-34.6	-43.3	0.04	0.32	-88.9	-111.0	-131.8	-150.3	177.0	-136.77
3.50	11.37	525.7	523.3	521.1	-0.71	-0.32	-0.13	10.10	-23.3	-34.4	-43.1	0.06	0.34	-89.8	-111.1	-131.6	-151.5	211.6	-138.50
3.75	11.37	528.6	526.1	524.0	-0.72	-0.32	-0.13	10.10	-23.5	-34.2	-42.8	0.08	0.37	-90.7	-111.2	-131.7	-150.9	302.4	-141.52
4.00	11.32	531.4	529.0	526.8	-0.73	-0.33	-0.13	10.10	-23.8	-34.1	-42.7	0.10	0.40	-90.4	-111.2	-131.5	-150.7	361.5	-143.10
4.25	11.22	534.3	531.8	529.6	-0.74	-0.34	-0.14	10.10	-24.0	-34.1	-42.2	0.11	0.42	-89.4	-111.1	-131.5	-150.0	507.5	-145.45
4.50	11.09	537.1	534.6	532.4	-0.77	-0.36	-0.15	10.09	-24.1	-34.0	-41.8	0.12	0.44	-88.4	-111.0	-131.3	-149.7	600.0	-147.52
4.75	10.91	539.9	537.4	535.1	-0.79	-0.38	-0.16	10.09	-24.2	-34.0	-41.2	0.12	0.45	-87.8	-111.2	-131.1	-150.1	851.6	-149.64
5.00	10.72	542.7	540.1	537.8	-0.82	-0.40	-0.17	10.10	-24.2	-34.0	-41.2	0.13	0.46	-88.8	-110.6	-131.1	-150.2	1000.0	-150.69

\*at 25°C unless mentioned otherwise



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

