

Voltage Controlled Oscillator

ZX95-730+

5V Tuning for PLL IC's 695 to 730 MHz

Features

- linear tuning characteristics
- low phase noise
- low pushing
- low pulling
- 0.5-5V tuning voltage range
- protected by US patent 6,790,049



CASE STYLE: GB956

Connectors	Model
SMA	ZX95-730-S+

Applications

- r & d
- lab
- instrumentation
- PLL circuitry
- wireless microphones

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, KHz				TUNING					NON HARMONIC SPURIOUS (dBc)	HARMONICS (dBc)		PULLING pk-pk @ 12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER			
	Min.	Max.		Typ.	1	10	100	1000	VOLTAGE RANGE (V)	SENSI- TIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)		Typ.	Typ.			Typ.	Typ.	Vcc (volts)	Current (mA)
ZX95-730+	695	730	0	-90	-114	-134	-153	0.5	5	11-12	40	90	-90	-21	-13	0.5	0.2	5	18		

Maximum Ratings


Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	7V
Absolute Max. Tuning Voltage (Vtune)	7V
All specifications	50 ohm system

Permanent damage may occur if any of these limits are exceeded.



NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note AN-40-10.

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
1.20	.75	.46	1.18	.04	.38	.38	.57	.18	.33	.21	.22	.18	1.00	.50	.35	.18	.106	grams
30.48	19.05	11.68	29.97	1.02	9.65	9.65	14.48	4.57	8.38	5.33	5.59	4.57	25.40	12.70	8.89	4.57	2.69	35.0

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp









Performance Data & Curves*

ZX95-730+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (KHz)	PHASE NOISE at 710 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F2	F3	F4			1kHz	10kHz	100kHz	1MHz		
0.00	13.45	684.2	681.6	679.4	-0.54	-0.24	-0.15	12.88	-20.0	-29.3	-30.5	0.30	0.26	-87.9	-112.6	-133.5	-152.6	1.0	-90.74
0.50	11.76	690.5	688.1	686.0	-0.51	-0.15	-0.04	12.94	-20.1	-29.4	-30.0	0.18	0.28	-87.7	-112.4	-133.8	-153.2	2.0	-99.96
0.75	11.45	693.5	691.0	688.9	-0.49	-0.11	0.01	12.97	-20.2	-29.6	-29.9	0.16	0.29	-90.0	-113.5	-133.8	-154.2	3.5	-103.61
1.00	11.32	696.4	693.9	691.7	-0.46	-0.06	0.06	12.99	-20.4	-29.6	-29.8	0.14	0.30	-88.7	-114.0	-134.2	-153.2	6.0	-107.94
1.25	11.30	699.2	696.7	694.6	-0.44	-0.02	0.11	13.01	-20.5	-29.9	-29.8	0.13	0.31	-90.2	-113.6	-134.2	-153.3	8.5	-112.96
1.50	11.37	702.1	699.5	697.4	-0.41	0.02	0.15	13.05	-20.6	-30.0	-29.9	0.12	0.32	-90.1	-113.5	-134.1	-150.1	10.0	-113.97
1.75	11.49	705.0	702.4	700.2	-0.38	0.05	0.20	13.07	-20.7	-30.2	-29.9	0.12	0.33	-89.4	-113.9	-134.2	-153.1	20.8	-120.12
2.00	11.65	707.9	705.2	703.0	-0.35	0.09	0.24	13.10	-20.8	-30.5	-29.6	0.12	0.34	-89.7	-112.9	-134.3	-153.0	35.5	-124.95
2.25	11.81	710.8	708.1	705.9	-0.31	0.12	0.28	13.12	-20.9	-30.6	-29.3	0.12	0.35	-89.8	-114.2	-134.6	-153.4	60.7	-129.69
2.50	11.96	713.8	711.1	708.8	-0.27	0.16	0.32	13.15	-21.1	-30.6	-29.2	0.13	0.37	-89.6	-114.6	-134.0	-153.4	86.7	-132.78
2.75	12.10	716.8	714.1	711.7	-0.23	0.19	0.36	13.17	-21.2	-30.8	-29.3	0.13	0.39	-91.1	-114.1	-134.2	-153.2	100.0	-134.55
3.00	12.20	719.9	717.1	714.7	-0.19	0.22	0.40	13.20	-21.4	-30.9	-29.4	0.14	0.41	-90.7	-114.1	-134.4	-153.9	148.1	-137.81
3.25	12.26	723.0	720.2	717.7	-0.16	0.25	0.44	13.23	-21.4	-31.2	-29.2	0.16	0.43	-89.3	-113.4	-134.1	-153.5	177.0	-139.43
3.50	12.26	726.1	723.2	720.7	-0.14	0.28	0.48	13.25	-21.4	-31.4	-28.9	0.17	0.45	-89.3	-114.0	-134.3	-153.8	211.6	-141.73
3.75	12.23	729.2	726.3	723.8	-0.12	0.32	0.52	13.28	-21.4	-31.7	-28.8	0.19	0.47	-87.3	-113.7	-134.3	-154.1	302.4	-142.96
4.00	12.15	732.3	729.3	726.8	-0.10	0.36	0.56	13.31	-21.4	-32.0	-28.8	0.21	0.48	-88.1	-114.2	-134.0	-153.1	361.5	-145.14
4.25	12.03	735.4	732.4	729.8	-0.08	0.41	0.61	13.34	-21.5	-32.3	-28.7	0.22	0.50	-88.4	-114.1	-134.3	-153.7	507.5	-148.56
4.50	11.88	738.4	735.4	732.8	-0.06	0.45	0.65	13.36	-21.6	-32.9	-28.6	0.24	0.50	-89.6	-112.8	-134.4	-154.1	600.0	-149.45
4.75	11.70	741.4	738.4	735.7	-0.04	0.48	0.69	13.39	-21.8	-33.4	-29.0	0.25	0.51	-88.2	-113.9	-134.1	-153.5	851.6	-151.83
5.00	11.50	744.4	741.3	738.6	-0.01	0.52	0.73	13.42	-21.8	-33.8	-29.0	0.26	0.51	-90.4	-113.5	-134.1	-153.6	1000.0	-153.72

*at 25°C unless mentioned otherwise



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

