

## Non-Catalog Model

# Frequency Mixer

# TUF-11AHSM

Level 17 (LO Power +17 dBm)

### Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

**CASE STYLE : NNN150**


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	1400		1900	MHz
	RF (fL to fU)	1400		1900	MHz
	IF	40		500	MHz
Conversion Loss			7.3	9.0	dB
LO-RF Isolation		25	35		dB
LO-IF Isolation		15	30		dB
1 dB Comp. Input Power			+14		dBm

**Note:** Non-hermetic.

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA

PIN CONNECTIONS	
LO	4
RF	1
IF	2
GROUND	3

### Electrical Schematics



# Frequency Mixer

# TUF-11AHSM

## Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)			LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
		@LO (dBm)				@LO (dBm)			@LO (dBm)		
		+14	+17	+20		+14	+17	+20	+14	+17	+20
1400.0	1350.0	7.85	7.77	7.80	1400.0	30.5	31.3	32.2	32.0	32.1	30.0
1439.5	1359.5	7.83	7.67	7.61	1439.5	29.7	30.8	31.8	30.9	31.9	30.1
1479.0	1429.0	7.66	7.43	7.34	1479.0	29.2	30.4	31.6	29.9	32.0	30.7
1492.1	1442.1	7.60	7.32	7.23	1492.1	29.1	30.4	31.7	29.6	32.1	30.9
1505.3	1455.3	7.47	7.19	7.08	1505.3	29.1	30.4	31.8	29.2	32.2	31.1
1544.7	1494.7	7.31	7.04	6.91	1544.7	29.0	30.6	32.2	28.2	31.4	31.1
1571.1	1521.1	7.31	6.98	6.82	1571.1	29.0	30.8	32.4	27.8	30.9	31.0
1584.2	1534.2	7.26	6.93	6.79	1584.2	29.0	30.8	32.4	27.6	30.4	30.9
1623.7	1573.7	7.07	6.83	6.72	1623.7	28.8	30.7	32.4	26.7	29.5	30.6
1663.2	1613.2	7.05	6.76	6.68	1663.2	28.8	30.9	32.8	25.8	28.4	29.9
1676.3	1626.3	6.93	6.70	6.65	1676.3	28.8	31.0	32.9	25.6	28.0	29.5
1702.6	1652.6	6.93	6.67	6.63	1702.6	28.7	30.9	32.7	24.8	27.3	28.8
1742.1	1692.1	6.86	6.61	6.58	1742.1	28.5	31.0	32.9	24.1	26.5	28.2
1768.4	1718.4	6.92	6.63	6.58	1768.4	28.6	31.2	33.3	23.6	26.0	27.6
1781.6	1731.6	6.86	6.59	6.52	1781.6	28.6	31.2	33.5	23.3	25.8	27.3
1821.1	1771.1	6.90	6.59	6.52	1821.1	28.6	30.9	33.0	22.7	25.1	26.6
1860.5	1810.5	6.94	6.68	6.63	1860.5	28.6	30.7	32.3	22.1	24.6	26.4
1873.7	1823.7	6.89	6.67	6.63	1873.7	28.6	30.6	32.3	21.9	24.4	26.3
1886.8	1836.8	7.00	6.74	6.72	1886.8	28.6	30.6	32.3	21.7	24.2	26.1
1900.0	1850.0	7.00	6.79	6.75	1900.0	28.7	30.6	32.2	21.6	24.1	26.0

REV. X1  
TUF-11AHSM  
060615  
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Frequency Mixer


# TUF-11AHSM

## Typical Performance Data


RF/LO (MHz)	RF VSWR (:1)			LO VSWR (:1)			IF (MHz)	IF VSWR (:1)		
	@LO (dBm)			@LO (dBm)				@LO (dBm)		
	+14	+17	+20	+14	+17	+20		+14	+17	+20
1400.0	2.21	2.14	2.04	2.07	2.49	3.00	40.0	1.30	1.24	1.25
1437.5	2.03	1.96	1.87	2.02	2.36	2.93	50.0	1.27	1.21	1.21
1477.5	1.85	1.78	1.70	2.05	2.40	2.96	75.0	1.20	1.13	1.14
1490.0	1.80	1.73	1.65	2.05	2.42	2.99	100.0	1.16	1.08	1.09
1515.0	1.69	1.63	1.56	2.03	2.40	2.98	110.0	1.15	1.07	1.08
1555.0	1.53	1.47	1.43	2.03	2.41	2.92	145.0	1.14	1.04	1.06
1580.0	1.41	1.37	1.35	2.04	2.43	2.95	182.5	1.13	1.03	1.05
1592.5	1.37	1.35	1.35	2.02	2.40	2.94	200.0	1.13	1.02	1.05
1630.0	1.30	1.30	1.32	2.03	2.39	2.92	227.5	1.13	1.02	1.06
1670.0	1.21	1.25	1.30	2.04	2.39	2.87	250.0	1.13	1.02	1.06
1682.5	1.18	1.24	1.29	2.03	2.39	2.85	275.0	1.13	1.03	1.07
1707.5	1.14	1.22	1.30	2.01	2.37	2.84	287.5	1.13	1.03	1.08
1745.0	1.10	1.20	1.29	2.02	2.38	2.87	312.5	1.13	1.04	1.10
1772.5	1.08	1.19	1.28	2.02	2.38	2.88	347.5	1.13	1.06	1.12
1785.0	1.08	1.19	1.29	2.02	2.37	2.85	382.5	1.13	1.09	1.14
1822.5	1.09	1.21	1.32	2.01	2.36	2.85	400.0	1.14	1.10	1.16
1862.5	1.14	1.25	1.36	2.00	2.37	2.98	430.0	1.14	1.12	1.18
1875.0	1.16	1.27	1.38	2.00	2.35	2.93	465.0	1.16	1.15	1.21
1887.5	1.19	1.29	1.40	2.00	2.33	2.86	487.5	1.17	1.17	1.23
1900.0	1.22	1.31	1.41	2.00	2.31	2.81	500.0	1.18	1.18	1.24

## Typical Performance Curves


Conversion Loss




LO-RF Isolation




LO-IF Isolation




RF VSWR



LO VSWR




IF VSWR




## Outline Dimensions

### NNN150

NOTE: BLUE BEAD INDICATES PIN #1.  
PIN NUMBERS DO NOT APPEAR  
ON UNIT.FOR REFERENCE ONLY.



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT, GRAM
NNN150	.50 (12.70)	.48 (12.19)	.255 (6.48)	.240 (6.10)	.23 (5.84)	.21 (5.33)	.06 (1.52)	.100 (2.54)	.09 (2.29)	.16 (4.06)	.020 (0.51)	.09 (2.29)	.005 (0.13)	1.9

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

#### Notes:

- Header material C.R.S. Pin material #52 alloy.
- Finish: Electro-Tin, hot-oil flowed or electro-Tin-Silver.
- Cover material: Cupro-Nickel.
- Pin's meniscus 0.015 inch max.
- Special Tolerances: Pin diameter  $\pm .005$  inch.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F9



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M86549	NEW RELEASE	04/15/03	GF	DJ
A	M102713	UPDATED NOTES & DISCRPTION	01/14/06	GF	IL

SUGGESTED MOUNTING CONFIGURATION  
FOR NNN150 CASE STYLE, "z"/"cm" PIN CONNECTIONS.



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	GF	04/11/03
	CHECKED	AV	04/15/03
	APPROVED	DJ	04/15/03


**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

PL, z/cm NNN150, TUF/TFAS-SM, TB-201


Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-081	REV: A
FILE: 98PL081	SCALE: 6:1	SHEET: 1 OF 1	

# Evaluation Board and Circuit




TB-201



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
---------------	---------------------------	----------------

Barometric Pressure

100,000 Feet

MIL-STD-202, Method 105, Condition D