

# Surface Mount Frequency Mixer

Level 7 (LO Power +7 dBm) 5 to 1500 MHz

## ADE-5+



Generic photo used for illustration purposes only  
CASE STYLE: CD542

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost	
Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

Permanent damage may occur if any of these limits are exceeded.


### Pin Connections

LO	6
RF	3
IF	2
GROUND	1,4,5

### Outline Drawing




### PCB Land Pattern



### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.272	.310	.220	.100	.112	.055	.100
6.91	7.87	5.59	2.54	2.84	1.40	2.54
H	J	K	L			wt
.030	.026	.065	.300			grams
0.76	0.66	1.65	7.62			0.20

### Demo Board MCL P/N: TB-03 Suggested PCB Layout (PL-052)



- NOTES:
- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- low conversion loss, 6.6 dB typ.
- excellent L-R isolation, 40 dB typ.
- excellent IP3, 15 dBm
- aqueous washable
- protected by U.S. Patent 6,133,525

### Applications

- cellular
- PCS

### Electrical Specifications

FREQUENCY (MHz)	CONVERSION LOSS (dB)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)			IP3 at center band (dBm)						
		L	M	U	L	M	U							
5-1500	DC-1000	50	40	40	25	33	23	50	40	30	20	20	10	15


1 dB COMP.: +1 dBm typ.  
Phase detection, positive polarity







L = low range [ $f_L$  to  $10 f_L$ ] M = mid range [ $10 f_L$  to  $f_U/2$ ] U = upper range [ $f_U/2$  to  $f_U$ ]  
m = mid band [ $2f_L$  to  $f_U/2$ ]

### Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm
5.0	35.0	7.0	63.9	53.6	1.59	1.91
10.0	40.0	6.6	63.2	52.2	1.51	1.94
50.0	80.0	6.5	56.7	46.6	1.39	1.91
100.0	130.0	6.6	52.7	41.7	1.38	1.91
197.1	227.1	6.7	49.0	36.3	1.41	1.94
295.6	325.6	6.6	47.3	33.5	1.40	2.01
394.1	424.1	6.7	43.7	32.0	1.39	2.20
492.6	522.6	6.5	42.4	30.7	1.35	2.40
500.0	530.0	6.6	41.9	30.5	1.34	2.37
591.1	621.1	6.6	39.7	29.9	1.35	2.40
689.6	719.6	6.6	36.8	28.5	1.28	2.32
788.1	818.1	6.6	35.2	26.0	1.23	2.30
886.6	916.6	6.5	33.4	23.5	1.14	2.32
985.1	1015.1	6.4	33.2	21.8	1.09	2.49
1000.0	1030.0	6.5	33.5	21.5	1.11	2.58
1182.0	1212.0	6.6	35.6	20.4	1.50	2.88
1280.5	1310.5	7.1	36.3	19.2	1.81	2.92
1379.0	1409.0	7.6	34.3	17.9	2.10	2.92
1477.5	1507.5	8.2	31.2	17.1	2.37	2.88
1500.0	1530.0	8.2	30.5	16.8	2.46	2.96

### Electrical Schematic





**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Frequency Mixer

# ADE-5+

## Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)			RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)			RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+1dBm (dB)		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+4	+7	+10			+4	+7	+10			+4	+7	+10
5.0	35.0	7.48	6.98	6.78	10.1	40.1	15.58	20.51	23.05	10.1	40.1	0.45	0.31	0.25
10.0	40.0	7.24	6.64	6.44	49.9	79.9	15.26	20.08	20.07	49.9	79.9	0.53	0.33	0.28
49.9	79.9	7.37	6.84	6.60	89.7	119.7	14.88	18.96	20.00	89.7	119.7	0.50	0.41	0.28
89.7	119.7	7.41	6.89	6.65	129.5	159.5	15.49	15.95	20.95	129.5	159.5	0.49	0.40	0.23
129.5	159.5	7.42	6.87	6.66	169.3	199.3	14.96	17.56	20.45	169.3	199.3	0.49	0.41	0.26
169.3	199.3	7.36	6.88	6.66	209.0	239.0	14.80	17.96	19.47	209.0	239.0	0.57	0.38	0.24
209.0	239.0	7.33	6.87	6.69	248.8	278.8	14.87	18.74	23.99	248.8	278.8	0.55	0.34	0.32
248.8	278.8	7.31	6.89	6.69	308.5	338.5	14.65	18.93	17.31	308.5	338.5	0.47	0.39	0.23
308.5	338.5	7.34	6.94	6.75	348.3	378.3	17.66	18.72	17.98	348.3	378.3	0.60	0.37	0.28
348.3	378.3	7.33	6.95	6.74	408.0	438.0	15.65	17.13	18.08	408.0	438.0	0.62	0.36	0.27
408.0	438.0	7.37	6.98	6.78	447.8	477.8	16.68	20.38	17.17	447.8	477.8	0.50	0.39	0.28
447.8	477.8	7.40	7.00	6.80	507.5	537.5	17.82	17.23	17.43	507.5	537.5	0.49	0.38	0.29
507.5	537.5	7.44	7.04	6.87	547.3	577.3	16.90	17.00	16.06	547.3	577.3	0.46	0.50	0.29
547.3	577.3	7.49	7.08	6.89	606.9	636.9	15.01	15.88	15.85	606.9	636.9	0.52	0.51	0.34
606.9	636.9	7.55	7.10	6.83	646.7	676.7	15.61	15.91	15.01	646.7	676.7	0.70	0.65	0.55
646.7	676.7	7.58	7.17	6.89	706.4	736.4	16.16	16.86	17.45	706.4	736.4	0.63	0.54	0.46
706.4	736.4	7.66	7.24	6.99	746.2	776.2	16.41	17.01	16.57	746.2	776.2	0.70	0.57	0.52
805.9	835.9	7.68	7.24	6.94	805.9	835.9	15.03	15.52	14.82	805.9	835.9	0.83	0.73	0.58
845.7	875.7	7.67	7.17	6.89	845.7	875.7	13.72	14.23	14.92	845.7	875.7	1.08	0.93	0.76
905.4	935.4	7.73	7.18	6.86	905.4	935.4	12.88	12.10	13.20	905.4	935.4	1.15	1.07	0.93
945.2	975.2	7.80	7.19	6.85	945.2	975.2	12.26	11.50	12.30	945.2	975.2	1.17	1.16	0.96
1004.8	1034.8	7.88	7.26	6.89	1004.8	1034.8	11.09	11.31	11.03	1004.8	1034.8	1.27	1.16	0.97
1044.6	1074.6	7.91	7.28	6.89	1044.6	1074.6	10.10	10.80	12.00	1044.6	1074.6	1.10	1.01	0.97
1104.3	1134.3	7.96	7.36	6.94	1104.3	1134.3	8.96	9.96	11.18	1104.3	1134.3	1.18	1.08	0.96
1144.1	1174.1	8.00	7.42	7.00	1144.1	1174.1	8.35	9.98	10.73	1144.1	1174.1	1.19	1.09	1.04
1203.8	1233.8	8.02	7.51	7.12	1203.8	1233.8	7.74	9.22	9.32	1203.8	1233.8	1.30	1.07	0.99
1243.6	1273.6	8.04	7.54	7.22	1243.6	1273.6	7.33	8.33	10.20	1243.6	1273.6	1.33	1.05	0.96
1303.3	1333.3	7.97	7.50	7.16	1303.3	1333.3	8.15	10.60	12.48	1303.3	1333.3	1.48	1.16	1.00
1343.0	1373.0	7.97	7.52	7.21	1343.0	1373.0	8.92	11.15	12.65	1343.0	1373.0	1.47	1.22	1.01
1402.7	1432.7	8.00	7.56	7.29	1402.7	1432.7	9.92	12.80	13.65	1402.7	1432.7	1.38	1.11	0.88
1442.5	1472.5	8.03	7.63	7.37	1442.5	1472.5	10.21	13.09	14.38	1442.5	1472.5	1.32	1.08	0.91
1502.2	1532.2	8.21	7.84	7.66	1502.2	1532.2	10.87	12.83	14.40	1502.2	1532.2	1.28	0.94	0.90
1542.0	1572.0	8.36	8.07	7.88	1542.0	1572.0	11.83	14.09	15.96	1542.0	1572.0	1.19	0.89	0.74
1601.7	1631.7	8.69	8.43	8.29	1601.7	1631.7	11.25	13.16	16.08	1601.7	1631.7	0.95	0.71	0.81
1641.5	1671.5	8.84	8.68	8.59	1641.5	1671.5	11.08	13.06	15.88	1641.5	1671.5	0.74	0.70	0.66
1701.2	1731.2	9.06	8.89	8.82	1701.2	1731.2	11.38	13.94	15.06	1701.2	1731.2	0.72	0.58	0.45
1740.9	1770.9	9.19	9.03	8.97	1740.9	1770.9	12.51	13.39	15.86	1740.9	1770.9	0.87	0.55	0.46
1800.6	1830.6	9.49	9.31	9.24	1800.6	1830.6	13.91	16.85	18.66	1800.6	1830.6	0.69	0.44	0.31
1840.4	1870.4	9.78	9.54	9.44	1840.4	1870.4	15.41	16.40	18.41	1840.4	1870.4	0.51	0.40	0.42
1900.1	1930.1	10.18	9.93	9.87	1900.1	1930.1	14.49	18.96	17.05	1900.1	1930.1	0.61	0.37	0.29

REV. X2  
ADE-5+  
100817  
Page 1 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Frequency Mixer

# ADE-5+

## Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=750.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=10.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1500.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+7			+7			+7
740.0	10.1	7.47	10.0	20.1	6.66	1000.0	500.1	8.51
721.3	28.8	7.48	30.0	40.1	6.24	979.8	520.3	8.33
702.6	47.5	7.46	50.0	60.1	6.16	959.6	540.5	8.26
683.8	66.3	7.47	70.0	80.1	6.24	939.4	560.7	8.20
665.1	85.0	7.40	90.0	100.1	6.22	919.2	580.9	8.15
646.4	103.7	7.37	110.0	120.1	6.12	899.0	601.1	8.06
627.7	122.4	7.32	130.0	140.1	6.16	878.8	621.3	8.03
609.0	141.1	7.25	150.0	160.1	6.20	858.6	641.5	7.97
590.3	159.8	7.23	170.0	180.1	6.18	838.4	661.7	7.95
571.5	178.6	7.19	190.0	200.1	6.21	818.2	681.9	7.95
552.8	197.3	7.18	210.0	220.1	6.20	798.0	702.1	7.92
534.1	216.0	7.14	230.0	240.1	6.28	777.8	722.3	7.90
515.4	234.7	7.12	250.0	260.1	6.22	757.6	742.5	7.87
496.7	253.4	7.10	270.0	280.1	6.27	737.3	762.8	7.88
477.9	272.2	7.09	290.0	300.1	6.36	717.1	783.0	7.84
459.2	290.9	7.08	310.0	320.1	6.35	696.9	803.2	7.79
440.5	309.6	7.11	330.0	340.1	6.37	676.7	823.4	7.73
421.8	328.3	7.09	350.0	360.1	6.44	656.5	843.6	7.72
403.1	347.0	7.05	370.0	380.1	6.41	636.3	863.8	7.66
384.4	365.7	7.04	390.0	400.1	6.46	616.1	884.0	7.63
365.6	384.5	7.01	430.0	440.1	6.86	575.7	924.4	7.53
346.9	403.2	7.04	450.0	460.1	6.63	555.5	944.6	7.54
328.2	421.9	7.04	490.0	500.1	6.59	515.1	985.0	7.50
309.5	440.6	7.02	510.0	520.1	6.64	494.9	1005.2	7.50
290.8	459.3	7.01	550.0	560.1	6.73	454.5	1045.6	7.52
272.1	478.0	7.03	570.0	580.1	6.79	434.3	1065.8	7.59
253.3	496.8	7.04	610.0	620.1	6.77	393.9	1106.2	7.55
234.6	515.5	6.98	630.0	640.1	6.97	373.7	1126.4	7.63
215.9	534.2	7.06	670.0	680.1	6.98	333.3	1166.8	7.69
197.2	552.9	7.04	690.0	700.1	7.05	313.1	1187.0	7.74
178.5	571.6	7.04	730.0	740.1	7.19	272.7	1227.4	7.84
159.7	590.4	7.03	750.0	760.1	7.28	252.4	1247.7	7.89
141.0	609.1	7.04	790.0	800.1	7.24	212.0	1288.1	7.96
122.3	627.8	7.06	810.0	820.1	7.24	191.8	1308.3	8.01
103.6	646.5	7.10	850.0	860.1	7.23	151.4	1348.7	7.99
84.9	665.2	7.12	870.0	880.1	7.13	131.2	1368.9	7.96
66.2	683.9	7.14	910.0	920.1	7.17	90.8	1409.3	7.94
47.4	702.7	7.15	930.0	940.1	7.24	70.6	1429.5	7.91
28.7	721.4	7.26	970.0	980.1	7.30	30.2	1469.9	7.81
10.0	740.1	7.14	990.0	1000.1	7.30	10.0	1490.1	7.77

REV. X2  
ADE-5+  
100817  
Page 2 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



## Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+4	+7	+10	+4	+7	+10
5.0	62.6	63.9	64.4	55.9	53.6	52.4
10.0	61.4	63.2	63.6	54.7	52.2	51.4
49.9	61.08	60.98	60.65	55.75	54.61	55.38
89.7	55.41	55.60	55.58	49.88	49.37	48.68
129.5	52.30	52.23	52.56	45.64	44.95	44.63
169.3	50.10	50.23	50.70	42.62	41.75	42.08
209.0	48.36	48.80	49.12	39.72	39.51	40.26
248.8	46.94	47.56	47.90	37.50	37.92	38.88
308.5	45.40	45.98	46.35	35.25	36.14	37.21
348.3	44.61	45.30	45.71	34.05	35.20	36.31
408.0	43.15	43.93	44.43	32.74	34.07	35.15
447.8	42.36	43.14	43.68	31.86	33.18	34.18
507.5	41.41	42.42	43.10	31.08	32.51	33.50
547.3	40.59	41.65	42.39	30.48	31.87	32.81
606.9	39.04	40.18	41.02	29.97	31.20	31.87
646.7	37.90	39.08	39.97	29.70	30.95	31.53
706.4	36.33	37.46	38.35	29.10	30.30	30.82
805.9	34.21	35.20	35.96	27.33	28.08	28.44
845.7	33.70	34.62	35.33	26.53	27.07	27.37
905.4	32.94	33.74	34.36	25.59	25.92	26.07
945.2	32.65	33.39	33.90	25.15	25.36	25.35
1004.8	32.39	33.13	33.57	24.57	24.64	24.35
1044.6	32.16	32.91	33.36	24.12	24.17	23.78
1104.3	31.89	32.59	33.03	23.70	23.66	23.09
1144.1	31.75	32.41	32.84	23.44	23.43	22.85
1203.8	31.60	32.15	32.52	23.00	23.05	22.62
1243.6	31.58	32.03	32.35	22.53	22.58	22.33
1303.3	31.59	31.90	32.06	21.45	21.18	20.92
1343.0	31.54	31.72	31.81	20.63	20.08	19.65
1402.7	31.40	31.41	31.44	19.80	19.00	18.49
1442.5	31.29	31.16	31.14	19.40	18.56	18.04
1502.2	31.18	30.82	30.62	19.01	18.10	17.49
1542.0	31.23	30.67	30.33	18.96	17.97	17.30
1601.7	30.92	29.97	29.37	18.78	17.63	16.91
1641.5	30.61	29.34	28.56	18.67	17.39	16.57
1701.2	30.08	28.40	27.40	18.55	17.18	16.28
1740.9	29.78	27.83	26.70	18.45	17.03	16.09
1800.6	29.22	26.97	25.70	18.31	16.86	15.89
1840.4	28.86	26.56	25.26	18.20	16.76	15.78
1900.1	28.30	25.88	24.49	18.09	16.67	15.65

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+4	+7	+10
10.1	40.1	42.19	49.31	48.33
49.9	79.9	34.91	34.84	34.69
89.7	119.7	29.97	30.08	30.18
129.5	159.5	27.31	27.39	27.37
169.3	199.3	25.29	25.46	25.52
209.0	239.0	23.91	24.05	24.11
248.8	278.8	22.84	23.01	23.11
308.5	338.5	21.72	21.97	22.10
348.3	378.3	21.20	21.49	21.67
408.0	438.0	20.59	20.97	21.21
447.8	477.8	20.20	20.60	20.87
507.5	537.5	19.52	19.96	20.26
547.3	577.3	19.12	19.65	20.03
606.9	636.9	18.85	19.54	20.02
646.7	676.7	18.66	19.33	19.84
706.4	736.4	18.13	18.63	18.98
746.2	776.2	17.48	17.80	18.00
805.9	835.9	16.34	16.43	16.46
845.7	875.7	15.62	15.64	15.63
905.4	935.4	14.66	14.61	14.58
945.2	975.2	14.18	14.11	14.07
1004.8	1034.8	13.67	13.60	13.54
1044.6	1074.6	13.44	13.37	13.33
1104.3	1134.3	13.21	13.16	13.14
1144.1	1174.1	13.06	13.02	12.98
1203.8	1233.8	12.89	12.84	12.81
1243.6	1273.6	12.75	12.69	12.67
1303.3	1333.3	12.56	12.43	12.33
1343.0	1373.0	12.35	12.16	12.02
1402.7	1432.7	11.86	11.63	11.47
1442.5	1472.5	11.46	11.21	11.03
1502.2	1532.2	10.86	10.57	10.36
1542.0	1572.0	10.38	10.08	9.86
1601.7	1631.7	9.70	9.37	9.14
1641.5	1671.5	9.22	8.87	8.65
1701.2	1731.2	8.54	8.15	7.87
1740.9	1770.9	8.13	7.73	7.48
1800.6	1830.6	7.51	7.11	6.86
1840.4	1870.4	7.17	6.78	6.53
1900.1	1930.1	6.56	6.20	5.98

## Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=1500.1MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+4	+7	+10		+4	+7	+10		+4	+7	+10
5.0	35.0	1.68	1.59	1.54	5.0	1.11	1.91	2.80	0.1	1.32	1.10	1.02
10.0	40.0	1.64	1.51	1.45	10.0	1.11	1.94	2.76	5.0	1.39	1.16	1.06
49.9	79.9	1.41	1.30	1.24	49.9	1.12	1.69	2.45	10.0	1.39	1.15	1.05
89.7	119.7	1.49	1.38	1.32	89.7	1.12	1.69	2.42	30.3	1.80	1.54	1.43
129.5	159.5	1.42	1.33	1.28	129.5	1.14	1.68	2.39	50.5	1.64	1.44	1.24
169.3	199.3	1.47	1.38	1.32	169.3	1.17	1.71	2.43	70.7	1.59	1.38	1.25
209.0	239.0	1.44	1.35	1.32	209.0	1.17	1.69	2.37	90.9	1.69	1.47	1.32
248.8	278.8	1.41	1.34	1.30	248.8	1.21	1.73	2.44	111.1	1.74	1.50	1.37
308.5	338.5	1.43	1.37	1.34	308.5	1.22	1.75	2.46	131.3	1.68	1.46	1.33
348.3	378.3	1.41	1.35	1.32	348.3	1.25	1.82	2.55	151.5	1.63	1.42	1.30
408.0	438.0	1.40	1.35	1.33	408.0	1.26	1.83	2.55	171.7	1.66	1.43	1.31
447.8	477.8	1.45	1.40	1.37	447.8	1.30	1.88	2.63	191.9	1.71	1.48	1.36
507.5	537.5	1.48	1.43	1.40	507.5	1.32	1.92	2.67	212.1	1.70	1.48	1.35
547.3	577.3	1.47	1.43	1.41	547.3	1.36	1.99	2.75	232.3	1.65	1.43	1.31
606.9	636.9	1.49	1.45	1.43	606.9	1.39	2.01	2.76	252.5	1.61	1.41	1.29
646.7	676.7	1.43	1.40	1.39	646.7	1.45	2.09	2.87	272.8	1.61	1.42	1.30
706.4	736.4	1.42	1.40	1.39	706.4	1.49	2.12	2.88	293.0	1.64	1.44	1.32
746.2	776.2	1.33	1.31	1.30	746.2	1.54	2.20	2.99	313.2	1.63	1.43	1.31
805.9	835.9	1.30	1.28	1.28	805.9	1.58	2.22	2.98	333.4	1.58	1.39	1.29
845.7	875.7	1.27	1.23	1.22	845.7	1.64	2.29	3.06	353.6	1.56	1.38	1.29
905.4	935.4	1.24	1.20	1.19	905.4	1.71	2.37	3.14	394.0	1.59	1.42	1.33
945.2	975.2	1.26	1.21	1.19	945.2	1.79	2.46	3.23	434.4	1.55	1.39	1.31
1004.8	1034.8	1.16	1.12	1.12	1004.8	1.88	2.57	3.35	454.6	1.55	1.40	1.33
1044.6	1074.6	1.15	1.11	1.11	1044.6	1.95	2.64	3.43	495.0	1.57	1.43	1.36
1104.3	1134.3	1.06	1.05	1.10	1104.3	2.03	2.73	3.52	515.2	1.55	1.42	1.36
1144.1	1174.1	1.08	1.09	1.13	1144.1	2.10	2.81	3.61	555.6	1.56	1.44	1.39
1203.8	1233.8	1.25	1.25	1.26	1203.8	2.15	2.84	3.62	575.8	1.57	1.46	1.41
1243.6	1273.6	1.29	1.30	1.32	1243.6	2.23	2.93	3.73	616.2	1.56	1.47	1.43
1303.3	1333.3	1.37	1.37	1.38	1303.3	2.22	2.86	3.62	636.4	1.57	1.48	1.45
1343.0	1373.0	1.44	1.45	1.47	1343.0	2.29	2.94	3.70	676.8	1.59	1.51	1.48
1402.7	1432.7	1.50	1.52	1.54	1402.7	2.29	2.90	3.63	697.0	1.57	1.50	1.47
1442.5	1472.5	1.60	1.63	1.64	1442.5	2.36	2.97	3.71	737.4	1.58	1.53	1.52
1502.2	1532.2	1.80	1.83	1.84	1502.2	2.44	3.03	3.76	757.7	1.60	1.55	1.53
1542.0	1572.0	1.90	1.93	1.94	1542.0	2.55	3.12	3.83	798.1	1.56	1.51	1.50
1601.7	1631.7	2.08	2.11	2.12	1601.7	2.71	3.26	3.94	818.3	1.55	1.52	1.52
1641.5	1671.5	1.99	2.03	2.04	1641.5	2.84	3.35	4.01	858.7	1.58	1.56	1.55
1701.2	1731.2	2.02	2.05	2.06	1701.2	3.03	3.48	4.10	878.9	1.56	1.53	1.53
1740.9	1770.9	1.88	1.91	1.93	1740.9	3.20	3.62	4.21	919.3	1.51	1.50	1.51
1800.6	1830.6	1.92	1.93	1.94	1800.6	3.36	3.70	4.21	939.5	1.52	1.51	1.53
1840.4	1870.4	2.03	2.04	2.07	1840.4	3.56	3.84	4.33	979.9	1.49	1.47	1.48
1900.1	1930.1	2.09	2.09	2.10	1900.1	3.69	3.88	4.29	1000.1	1.44	1.44	1.45

## Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	+0	20	8	36	18	27	34	38	58	44
1	-	10	+0	27	14	39	33	41	47	38	59	48
2	124	63	48	59	50	59	51	62	63	61	69	64
3	117	68	79	67	67	68	65	86	79	77	81	82
4	118	96	90	91	83	81	83	91	90	92	92	94
5	116	107	103	130	110	95	86	104	100	99	102	105
6	119	102	109	100	99	119	104	83	119	102	114	112
7	114	101	103	114	115	125	100	95	102	109	109	109
8	109	99	103	114	110	97	110	101	97	91	101	106
9	117	95	106	112	107	106	102	109	108	95	97	98
10	114	99	98	102	122	111	107	102	104	110	104	96
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 750.1 MHz; -14.00 dBm.  
 LO IN: 780.01 MHz; +7.00 dBm  
 IF OUT: 29.91 MHz; -21.11 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	10	31	18	42	28	39	48	53	63	66
1	-	10	+0	28	14	42	33	46	56	43	67	54
2	89	51	37	47	39	48	42	57	71	54	67	60
3	116	47	60	49	50	50	47	65	61	60	63	59
4	115	78	71	69	58	61	58	77	61	70	64	64
5	114	73	76	73	66	66	62	72	64	73	71	75
6	111	91	87	91	88	78	70	71	70	72	72	78
7	122	92	97	94	107	87	78	78	78	79	85	89
8	106	110	104	99	102	116	92	91	83	82	82	93
9	113	121	111	116	109	104	105	103	107	105	94	97
10	105	111	113	111	130	111	114	116	106	99	99	98
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 750.1 MHz; -4.00 dBm.  
 LO IN: 780.01 MHz; +7.00 dBm  
 IF OUT: 29.91 MHz; -11.16 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.  
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.  
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2  
 ADE-5+  
 100817

Page 5 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=750.1MHz




Conversion Loss vs. IF @ RF=10.1MHz




Conversion Loss vs. IF @ RF=1500.1MHz



IP3 Input




Compression @ RF IN=+1dBm






## Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



## Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	+0	20	8	36	18	27	34	38	58	44
1	-	10	+0	27	14	39	33	41	47	38	59	48
2	124	63	48	59	50	59	51	62	63	61	69	64
3	117	68	79	67	67	68	65	86	79	77	81	82
4	118	96	90	91	83	81	83	91	90	92	92	94
5	116	107	103	130	110	95	86	104	100	99	102	105
6	119	102	109	100	99	119	104	83	119	102	114	112
7	114	101	103	114	115	125	100	95	102	109	109	109
8	109	99	103	114	110	97	110	101	97	91	101	106
9	117	95	106	112	107	106	102	109	108	95	97	98
10	114	99	98	102	122	111	107	102	104	110	104	96
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 750.1 MHz; -14.00 dBm.  
 LO IN: 780.01 MHz; +7.00 dBm  
 IF OUT: 29.91 MHz; -21.11 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	10	31	18	42	28	39	48	53	63	66
1	-	10	+0	28	14	42	33	46	56	43	67	54
2	89	51	37	47	39	48	42	57	71	54	67	60
3	116	47	60	49	50	50	47	65	61	60	63	59
4	115	78	71	69	58	61	58	77	61	70	64	64
5	114	73	76	73	66	66	62	72	64	73	71	75
6	111	91	87	91	88	78	70	71	70	72	72	78
7	122	92	97	94	107	87	78	78	78	79	85	89
8	106	110	104	99	102	116	92	91	83	82	82	93
9	113	121	111	116	109	104	105	103	107	105	94	97
10	105	111	113	111	130	111	114	116	106	99	99	98
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

### LO HARMONICS ORDER

Test conditions: RF IN: 750.1 MHz; -4.00 dBm.  
 LO IN: 780.01 MHz; +7.00 dBm  
 IF OUT: 29.91 MHz; -11.16 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.  
 2. + entry denotes harmonics are in (dBc) above IF OUTPUT.  
 3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2  
 ADE-5+  
 100817

Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see





# Case Style


# CD

CD541  
CD542  
CD636  
CD637

## Outline Dimensions



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
CD541					.082 (2.08)							.15
CD542	.272 (6.91)	.310 (7.87)	.220 (5.58)	.100 (2.54)	.112 (2.84)	.055 (1.40)	.100 (2.54)	.030 (0.76)	.026 (0.66)	.065 (1.65)	.300 (7.62)	.20
CD636					.162 (4.11)							.25
CD637					.206 (5.23)							.40

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:
  - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

**Mini-Circuits®**

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
1000				

Note: Availability of small reel quantity varies by model.  
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M101143	ADDED "gk" PIN CONNECTION, TT100 CASE STYLE & NOTE 2	10/10/05	MMG	DJ
B	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL
C	M108637	REMOVED "PIN 1", ADDED INDEX ON UNIT	12/01/06	MYG	FL

SUGGESTED MOUNTING CONFIGURATION  
FOR BH292, CD541/542/636/637, TT100/240 CASE  
STYLES, "gk", "ht", "hu", "nd", "w" PIN CONNECTIONS



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	MMG	07/17/02
TOLERANCES ON:	WL	08/02/02
2 PL DECIMALS ±	DJ	08/05/02
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		

**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

PL, gk/ht/hu/nd/w, BH292,  
CD541/542/636/637, TT100/240, TB-03

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-052	REV: C
FILE: 98PL052	SCALE: 8:1	SHEET: 1 OF 1	

Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

# Evaluation Board and Circuit

For Pin Connections and DUT Orientation Refer to  
Data Sheet of the DUT




TB-03



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215