

Surface Mount Power Splitter/Combiner

ADP-2-122-75+

2 Way-0° 75Ω 5 to 1250 MHz

Features

- wideband, 5 to 1250 MHz
- low insertion loss, 0.9 dB typ.
- aqueous washable
- protected under U.S. Patent 6,133,525



Generic photo used for illustration purposes only

CASE STYLE: CD636

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost	
Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000

Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		5		1250	MHz
Insertion Loss, above 3.0 dB	5-50	—	0.25	0.5	dB
	50-1000	—	0.75	1.2	
	1000-1250	—	1.00	1.6	
Isolation	5-50	17	20	—	dB
	50-1000	18	22	—	
	1000-1250	17	19	—	
Phase Unbalance	5-50	—	0.5	1.0	Degree
	50-1000	—	1.5	3.5	
	1000-1250	—	2.0	4.0	
Amplitude Unbalance	5-50	—	0.1	0.2	dB
	50-1000	—	0.15	0.3	
	1000-1250	—	0.2	0.4	
VSWR (Port S)	5-1000	—	1.15	1.30	:1
	1000-1250	—	1.25	1.35	
VSWR (Port 1 and Port 2)	5-1000	—	1.25	1.4	:1
	1000-1250	—	1.2	1.4	

Maximum Ratings


Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	0.5W max.
Internal Dissipation	0.125 W max.

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

Function	Pin Number
SUM PORT	1
PORT 1	3
PORT 2	4
GROUND	6
NOT USED	2,5


Electrical Schematic



Outline Drawing




PCB Land Pattern



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
272	.310	.220	.100	.162	.055	.100
3.91	7.87	5.59	2.54	4.11	1.40	2.54
H	J	K	L	wt		
030	.026	.065	.300	grams		
1.76	0.66	1.65	7.62	0.25		

Demo Board MCL P/N: TB-243 Suggested PCB Layout (PL-141)






- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
5	3.23	3.23	0.00	18.60	0.03	1.08	1.32	1.32
50	3.21	3.21	0.00	21.49	0.17	1.06	1.20	1.20
100	3.23	3.23	0.01	21.23	0.33	1.06	1.20	1.20
200	3.26	3.27	0.01	20.87	0.66	1.08	1.20	1.19
300	3.30	3.30	0.00	20.64	0.93	1.10	1.20	1.18
400	3.35	3.35	0.00	20.43	1.21	1.11	1.19	1.17
500	3.40	3.42	0.01	20.26	1.43	1.13	1.19	1.16
600	3.42	3.42	0.00	20.07	1.56	1.11	1.19	1.14
700	3.47	3.47	0.00	20.19	1.68	1.10	1.19	1.13
800	3.54	3.52	0.01	20.52	1.80	1.08	1.19	1.11
900	3.65	3.61	0.03	21.24	1.76	1.06	1.21	1.11
1000	3.71	3.66	0.05	22.22	1.84	1.04	1.22	1.11
1100	3.81	3.72	0.09	23.50	1.90	1.07	1.24	1.13
1200	3.93	3.82	0.11	24.89	1.96	1.13	1.27	1.15
1300	4.10	3.97	0.13	26.28	1.92	1.19	1.29	1.17

1. Total Loss = Insertion Loss + 3dB splitter loss.



Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

2 Way-0° Power Splitter/Combiner

ADP-2-122-75+

Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (deg.)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
4	3.25	3.25	0.00	17.60	0.03	4	1.08	1.37	1.37
5	3.23	3.23	0.00	18.60	0.03	5	1.08	1.32	1.32
6	3.22	3.22	0.00	19.36	0.01	6	1.07	1.29	1.29
7	3.21	3.21	0.00	19.95	0.03	7	1.07	1.26	1.26
8	3.21	3.21	0.00	20.40	0.04	8	1.07	1.25	1.25
9	3.21	3.21	0.00	20.69	0.04	9	1.06	1.24	1.24
10	3.20	3.21	0.00	20.96	0.05	10	1.06	1.23	1.23
15	3.20	3.20	0.00	21.49	0.07	15	1.06	1.21	1.21
20	3.20	3.20	0.00	21.72	0.07	20	1.06	1.20	1.20
30	3.20	3.21	0.00	21.69	0.10	30	1.06	1.20	1.20
40	3.20	3.21	0.00	21.57	0.13	40	1.06	1.20	1.20
50	3.21	3.21	0.00	21.49	0.17	50	1.06	1.20	1.20
60	3.21	3.22	0.00	21.41	0.20	60	1.06	1.20	1.20
70	3.22	3.22	0.01	21.36	0.24	70	1.06	1.20	1.20
80	3.22	3.23	0.01	21.32	0.27	80	1.06	1.20	1.20
90	3.22	3.23	0.01	21.28	0.30	90	1.06	1.20	1.20
100	3.23	3.23	0.01	21.23	0.33	100	1.06	1.20	1.20
200	3.26	3.27	0.01	20.87	0.66	200	1.08	1.20	1.19
300	3.30	3.30	0.00	20.64	0.93	300	1.10	1.20	1.18
400	3.35	3.35	0.00	20.43	1.21	400	1.11	1.19	1.17
500	3.40	3.42	0.01	20.26	1.43	500	1.13	1.19	1.16
600	3.42	3.42	0.00	20.07	1.56	600	1.11	1.19	1.14
700	3.47	3.47	0.00	20.19	1.68	700	1.10	1.19	1.13
800	3.54	3.52	0.01	20.52	1.80	800	1.08	1.19	1.11
900	3.65	3.61	0.03	21.24	1.76	900	1.06	1.21	1.11
1000	3.71	3.66	0.05	22.22	1.84	1000	1.04	1.22	1.11
1100	3.81	3.72	0.09	23.50	1.90	1100	1.07	1.24	1.13
1200	3.93	3.82	0.11	24.89	1.96	1200	1.13	1.27	1.15
1300	4.10	3.97	0.13	26.28	1.92	1300	1.19	1.29	1.17

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site www.minicircuits.com



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com






IF/RF MICROWAVE COMPONENTS

REV. OR
ADP-2-122-75+
6/29/2015
Page 1 of 1

2 Way-0° Power Splitter/Combiner

ADP-2-122-75+

Typical Performance Curves





Case Style


CD

CD541
CD542
CD636
CD637

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
CD541					.082 (2.08)							.15
CD542	.272 (6.91)	.310 (7.87)	.220 (5.58)	.100 (2.54)	.112 (2.84)	.055 (1.40)	.100 (2.54)	.030 (0.76)	.026 (0.66)	.065 (1.65)	.300 (7.62)	.20
CD636					.162 (4.11)							.25
CD637					.206 (5.23)							.40

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M88803	NEW RELEASE	10/20/03	GF	HY
A	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR CD542 CASE STYLE, "hv" PIN CONNECTION



- NOTES:**
- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $.030" \pm .002"$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN GF	09/18/03
TOLERANCES ON:	CHECKED IL	10/20/03
2 PL DECIMALS \pm	APPROVED HY	10/20/03
3 PL DECIMALS $\pm .005$		
ANGLES \pm		
FRACTIONS \pm		

Mini-Circuits[®] 13 Neptune Avenue
Brooklyn NY 11235



PL, hv, 75, CD542, ADP, TB-243

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-141	REV: A
FILE: 98PL141	SCALE: 8:1	SHEET: 1 OF 1	

Mini-Circuits[®]
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. BNC Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215