



## MMIC SURFACE MOUNT

# Fixed Attenuator

# BAT-0+

50Ω DC to 60 GHz 2 W 0 dB

### THE BIG DEAL

- Wideband, DC to 60 GHz
- High Power Handling, 2 W
- Excellent Return Loss, Typ. 20 dB
- 1.5x1.5 mm, 6-Lead QFN-Style Package




Generic photo used for illustration purposes only

### APPLICATIONS

- Test & Measurement Equipment
- Satellite Communications
- Radar, EW, and ECM Defense Systems
- Telecom Infrastructure
- 5G sub-6 GHz and mmW

### FUNCTIONAL DIAGRAM



### PRODUCT OVERVIEW

BAT-0+ is a wideband, bidirectional, 0 dB fixed attenuator fabricated using a highly reliable and repeatable GaAs semiconductor process. Operating from DC to 60 GHz, this model is suitable for use as a through line and can be interchanged on a PCB with any other BAT attenuation value. The model can handle input power up to 2 W, making it an ideal choice for a wide range of applications such as Test & Measurement, Satellite Communications, Radar, EW, ECM Defense Systems, Telecom Infrastructure, and 5G.

### KEY FEATURES

| Features                            | Advantages  |
|-------------------------------------|---|
| Wideband Operation, DC to 60 GHz    | Flat attenuation response from DC to 60 GHz supports a wide array of applications including Test & Measurement Equipment, Satellite Communications, Radar, EW, ECM Defense Systems, & 5G applications.                |
| Excellent Return Loss               | Low Return Loss minimizes reflections and enables flexibility to implement anywhere within wideband signal chains.  |
| 1.5x1.5 mm 6-Lead QFN-Style Package | Small footprint saves space in dense layouts while providing low inductance and excellent thermal contact to the PCB. Industry-standard packaging allows for ease of assembly in high-volume manufacturing processes. |

REV. OR  
ECO-023830  
BAT-0+  
MCL NY  
241203





MMIC SURFACE MOUNT

# Fixed Attenuator

**BAT-0+**

50Ω DC to 60 GHz 2 W 0 dB

## ELECTRICAL SPECIFICATIONS<sup>1,2</sup> AT +25°C, 50Ω, UNLESS NOTED OTHERWISE


| Parameter          | Condition (GHz) | Min. | Typ. | Max. | Units |
|--------------------|-----------------|------|------|------|-------|
| Frequency Range    |                 | DC   |      | 60   | GHz   |
| Attenuation        | 0.01 - 10       |      | 0.05 | 0.6  | dB    |
|                    | 10 - 20         |      | 0.13 | 0.9  |       |
|                    | 20 - 30         |      | 0.28 | 1.1  |       |
|                    | 30 - 40         |      | 0.32 | 1.3  |       |
|                    | 40 - 50         |      | 0.42 |      |       |
|                    | 50 - 60         |      | 0.52 |      |       |
| Input Return Loss  | 0.01 - 10       |      | 34   |      | dB    |
|                    | 10 - 20         |      | 26   |      |       |
|                    | 20 - 30         |      | 20   |      |       |
|                    | 30 - 40         |      | 21   |      |       |
|                    | 40 - 50         |      | 22   |      |       |
|                    | 50 - 60         |      | 24   |      |       |
| Output Return Loss | 0.01 - 10       |      | 34   |      | dB    |
|                    | 10 - 20         |      | 26   |      |       |
|                    | 20 - 30         |      | 20   |      |       |
|                    | 30 - 40         |      | 21   |      |       |
|                    | 40 - 50         |      | 22   |      |       |
|                    | 50 - 60         |      | 24   |      |       |

1. Tested on Mini-Circuits Characterization Test/Evaluation Board TB-BAT-0C+. See Figure 2. Board loss de-embedded to the device.  
 2. Bi-directional RF-IN and RF-OUT ports can be interchanged.




### TYPICAL PERFORMANCE GRAPHS


**INSERTION LOSS vs. TEMPERATURE (LOW FREQUENCY)**




**INSERTION LOSS vs. TEMPERATURE (WIDEBAND)**




**INPUT RETURN LOSS vs. TEMPERATURE (LOW FREQUENCY)**




**INPUT RETURN LOSS vs. TEMPERATURE (WIDEBAND)**



**OUTPUT RETURN LOSS vs. TEMPERATURE (LOW FREQUENCY)**



**OUTPUT RETURN LOSS vs. TEMPERATURE (WIDEBAND)**





MMIC SURFACE MOUNT

# Fixed Attenuator

**BAT-0+**

50Ω DC to 60 GHz 2 W 0 dB

## ABSOLUTE MAXIMUM RATINGS<sup>3</sup>

| Parameter                   | Ratings         |
|-----------------------------|-----------------|
| Operating Temperature       | -45°C to +105°C |
| Storage Temperature         | -65°C to +150°C |
| RF Input Power <sup>4</sup> | 2 W             |

3. Permanent damage may occur if any of these limits are exceeded. Maximum ratings are not intended for continuous normal operation.

4. Power derated to 1 W at +105°C.

## ESD RATING

|     | Class | Voltage Range | Reference Standard          |
|-----|-------|---------------|-----------------------------|
| HBM | 2     | > 2000 V      | ANSI/ESD STM 5.1 - 2001     |
| CDM | C3    | > 1000 V      | ANSI/ESDA/JEDEC JS-002-2022 |



ESD HANDLING PRECAUTION: This device is designed to be Class 2 for HBM. Static charges may easily produce potentials higher than this with improper handling and can discharge into DUT and damage it. As a preventive measure Industry standard ESD handling precautions should be used at all times to protect the device from ESD damage.

## MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020E /JEDEC J-STD-033C





### FUNCTIONAL DIAGRAM




Figure 1. BAT-0+ Functional Diagram

### PAD DESCRIPTION

| Function | Pad #               | Description (Refer to Figure 2)        |
|----------|---------------------|--|
| RF-IN    | 2                   | RF-IN Pad connects to RF Input port.   |
| RF-OUT   | 5                   | RF-OUT Pad connects to RF Output port. |
| GND      | 1, 3, 4, 6 & Paddle | Connects to ground.                    |

### CHARACTERIZATION TEST BOARD




Figure 2. BAT-0+ Characterization and Application Circuit.

#### Electrical Parameters and Conditions



Insertion Loss and Return Loss are measured using N5247B PNA-X microwave network analyzer.

Conditions:

1. Insertion Loss and Return Loss:  $P_{IN} = -5 \text{ dBm}$



### CASE STYLE DRAWING



Suggested Layout,  
Tolerance to be within ±0.050 mm


### NOTES:

1. DENOTES METALLIZATION

Weight: .0036 grams

Dimensions are in mm [inches]. Tolerances: 2 Pl.± 0.05 mm

### PRODUCT MARKING



Marking may contain other features or characters for internal lot control



MMIC SURFACE MOUNT

# Fixed Attenuator

**BAT-0+**

50Ω DC to 60 GHz 2 W 0 dB

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD [CLICK HERE](#)

|  |  |
|--|--|
| Performance Data                                     | Data<br>Graphs<br>S-Parameter (S2P Files) Data Set (.zip file)             |
| Case Style   | KC3009 Plastic package, exposed paddle, lead finish: Nickel-Palladium-Gold |
| RoHS Status  | Compliant  |
| Tape & Reel<br>Standard quantities available on reel | F66<br>7" reels with 20, 50, 100, 200, 500, 1000, 2000, or 3000 devices    |
| Suggested Layout for PCB Design                      | PL-801   |
| Evaluation Board                                     | TB-BAT-0C+<br>Gerber File  |
| Environmental Ratings                                | ENV08T1  |

**NOTES**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



*Typical Performance Data*

**Definitions:**

Input Return Loss = -S11 (dB)







Attenuation = -S21 (dB)

Output Return Loss = -S22 (dB)

| FREQ  | Attenuation |       |       |        | Input Return Loss |       |       |        | Output Return Loss |       |       |        |
|-------|-------------|-------|-------|--------|-------------------|-------|-------|--------|--------------------|-------|-------|--------|
|       | -45°C       | +25°C | +85°C | +105°C | -45°C             | +25°C | +85°C | +105°C | -45°C              | +25°C | +85°C | +105°C |
| (MHz) | (dB)        | (dB)  | (dB)  | (dB)   | (dB)              | (dB)  | (dB)  | (dB)   | (dB)               | (dB)  | (dB)  | (dB)   |
| 0.009 | 0.002       | 0.004 | 0.011 | 0.013  | 31.47             | 31.44 | 31.51 | 31.43  | 29.96              | 29.92 | 29.97 | 30.00  |
| 0.5   | 0.002       | 0.004 | 0.011 | 0.013  | 43.34             | 43.64 | 43.21 | 43.03  | 43.17              | 43.55 | 43.11 | 42.93  |
| 1     | 0.002       | 0.004 | 0.011 | 0.013  | 44.03             | 44.23 | 43.82 | 43.56  | 43.05              | 43.35 | 42.87 | 42.68  |
| 5     | 0.002       | 0.004 | 0.011 | 0.013  | 42.44             | 42.50 | 41.95 | 41.69  | 42.72              | 42.82 | 42.31 | 42.00  |
| 10    | 0.002       | 0.004 | 0.011 | 0.013  | 42.93             | 42.74 | 42.08 | 41.78  | 42.52              | 42.44 | 41.81 | 41.57  |
| 100   | 0.002       | 0.004 | 0.011 | 0.013  | 45.35             | 42.79 | 41.01 | 40.39  | 44.96              | 42.33 | 40.54 | 39.96  |
| 200   | 0.003       | 0.006 | 0.015 | 0.017  | 40.21             | 39.52 | 38.73 | 38.42  | 40.21              | 39.41 | 38.35 | 38.08  |
| 400   | 0.006       | 0.007 | 0.018 | 0.021  | 36.78             | 36.70 | 36.14 | 35.89  | 37.15              | 36.85 | 36.07 | 35.83  |
| 600   | 0.008       | 0.010 | 0.020 | 0.023  | 35.21             | 35.05 | 34.45 | 34.25  | 35.77              | 35.57 | 34.97 | 34.76  |
| 800   | 0.009       | 0.012 | 0.023 | 0.025  | 34.54             | 34.36 | 33.85 | 33.73  | 35.21              | 34.91 | 34.34 | 34.16  |
| 1000  | 0.012       | 0.014 | 0.026 | 0.029  | 34.05             | 33.69 | 33.22 | 33.15  | 34.73              | 34.63 | 34.12 | 34.04  |
| 2000  | 0.034       | 0.037 | 0.048 | 0.049  | 32.23             | 32.04 | 32.48 | 32.88  | 36.51              | 36.59 | 37.00 | 37.58  |
| 4000  | 0.052       | 0.047 | 0.053 | 0.059  | 34.79             | 39.49 | 44.55 | 45.56  | 33.92              | 36.40 | 37.52 | 37.75  |
| 6000  | 0.042       | 0.038 | 0.063 | 0.076  | 31.62             | 32.13 | 34.05 | 34.71  | 30.33              | 31.12 | 31.97 | 32.21  |
| 8000  | 0.028       | 0.036 | 0.074 | 0.090  | 33.57             | 33.35 | 33.20 | 33.22  | 37.05              | 34.94 | 34.03 | 33.99  |
| 10000 | 0.032       | 0.046 | 0.092 | 0.112  | 31.10             | 32.44 | 33.30 | 33.34  | 29.47              | 30.52 | 30.93 | 30.98  |
| 12000 | 0.015       | 0.035 | 0.090 | 0.114  | 29.15             | 29.83 | 30.95 | 31.19  | 29.89              | 30.70 | 32.33 | 32.45  |
| 14000 | 0.148       | 0.136 | 0.172 | 0.192  | 16.19             | 17.90 | 19.47 | 20.01  | 16.58              | 18.22 | 19.86 | 20.42  |
| 16000 | -0.012      | 0.031 | 0.113 | 0.148  | 31.72             | 30.25 | 31.10 | 31.91  | 38.91              | 31.00 | 32.29 | 34.98  |
| 18000 | 0.052       | 0.078 | 0.150 | 0.184  | 34.14             | 33.82 | 32.77 | 30.21  | 30.22              | 33.63 | 31.20 | 28.87  |
| 20000 | 0.186       | 0.242 | 0.334 | 0.367  | 15.53             | 14.61 | 14.79 | 14.95  | 15.50              | 14.87 | 14.98 | 15.12  |
| 22000 | 0.259       | 0.230 | 0.255 | 0.266  | 14.16             | 16.26 | 18.25 | 19.16  | 14.46              | 16.35 | 18.28 | 19.22  |
| 24000 | 0.074       | 0.107 | 0.195 | 0.232  | 29.60             | 27.94 | 28.25 | 28.95  | 26.98              | 26.23 | 26.87 | 27.63  |
| 26000 | 0.158       | 0.207 | 0.316 | 0.363  | 18.48             | 18.34 | 17.27 | 16.74  | 18.90              | 18.63 | 17.56 | 16.96  |
| 28000 | 0.229       | 0.243 | 0.324 | 0.351  | 16.14             | 17.27 | 17.91 | 18.46  | 16.16              | 17.35 | 17.82 | 18.28  |
| 30000 | 0.220       | 0.288 | 0.348 | 0.366  | 18.99             | 17.72 | 19.03 | 20.17  | 18.49              | 17.71 | 18.91 | 20.02  |
| 32000 | 0.202       | 0.238 | 0.283 | 0.317  | 22.11             | 26.24 | 25.98 | 25.61  | 23.04              | 26.73 | 26.63 | 26.43  |
| 34000 | 0.382       | 0.360 | 0.401 | 0.420  | 16.36             | 16.87 | 17.02 | 17.18  | 20.30              | 19.03 | 17.90 | 17.67  |
| 36000 | 0.209       | 0.209 | 0.343 | 0.350  | 15.36             | 17.77 | 20.03 | 21.95  | 16.49              | 17.75 | 20.25 | 21.94  |
| 38000 | 0.211       | 0.226 | 0.393 | 0.441  | 19.20             | 18.67 | 17.79 | 17.23  | 17.76              | 18.23 | 17.97 | 17.54  |
| 40000 | 0.084       | 0.138 | 0.307 | 0.377  | 22.66             | 26.94 | 27.44 | 26.89  | 21.23              | 26.62 | 26.07 | 25.25  |
| 42000 | 0.215       | 0.228 | 0.351 | 0.405  | 17.86             | 21.47 | 22.36 | 22.93  | 19.03              | 21.01 | 21.41 | 21.93  |
| 44000 | 0.214       | 0.253 | 0.390 | 0.473  | 28.78             | 29.87 | 23.81 | 21.67  | 29.48              | 30.71 | 22.76 | 20.94  |
| 46000 | 0.126       | 0.311 | 0.477 | 0.545  | 21.34             | 18.42 | 19.18 | 19.46  | 19.63              | 18.14 | 18.81 | 18.92  |
| 48000 | 0.236       | 0.361 | 0.450 | 0.503  | 14.72             | 17.40 | 21.17 | 22.52  | 15.98              | 17.40 | 21.00 | 22.56  |
| 50000 | 0.077       | 0.230 | 0.400 | 0.482  | 22.23             | 24.95 | 25.58 | 24.51  | 18.42              | 24.47 | 24.74 | 23.53  |
| 52000 | 0.194       | 0.301 | 0.472 | 0.553  | 23.07             | 26.16 | 22.71 | 21.40  | 22.67              | 27.96 | 24.94 | 23.83  |
| 54000 | 0.261       | 0.327 | 0.475 | 0.544  | 25.93             | 27.33 | 25.31 | 24.84  | 19.90              | 30.20 | 29.57 | 27.74  |
| 56000 | 0.417       | 0.422 | 0.603 | 0.685  | 17.26             | 19.74 | 18.96 | 18.35  | 16.16              | 19.13 | 18.28 | 17.50  |
| 58000 | 0.316       | 0.313 | 0.478 | 0.535  | 24.10             | 25.44 | 22.78 | 21.32  | 25.33              | 22.80 | 21.85 | 20.93  |
| 60000 | 0.308       | 0.425 | 0.675 | 0.749  | 25.76             | 20.41 | 18.32 | 17.55  | 23.52              | 19.34 | 18.30 | 18.35  |
| 62000 | 1.276       | 1.160 | 1.471 | 1.628  | 8.70              | 10.08 | 9.75  | 9.41   | 8.43               | 9.57  | 9.21  | 8.93   |
| 64000 | 1.258       | 1.553 | 1.704 | 1.746  | 10.55             | 8.79  | 9.67  | 10.06  | 9.56               | 8.77  | 9.59  | 10.00  |
| 66000 | 2.234       | 1.908 | 2.068 | 2.164  | 5.58              | 8.78  | 10.06 | 10.32  | 6.56               | 9.26  | 10.39 | 10.68  |
| 67000 | 1.492       | 1.949 | 2.196 | 2.303  | 10.89             | 10.18 | 10.87 | 11.05  | 12.36              | 10.92 | 11.72 | 12.04  |



## Typical Performance Curves




# Case Style


# KC

## Outline Dimensions


## KC3009




TOP VIEW



SIDE VIEW



BOTTOM VIEW



Suggested Layout,  
Tolerance to be within  $\pm 0.050$  mm

### NOTES:

1.  DENOTES METALLIZATION

Weight: .0036 grams

Dimensions are in mm [inches]. Tolerances: 2 Pl.  $\pm 0.05$  mm

### Notes:

1. Case material: Plastic.
2. Termination finish: NiPdAu ( $3\mu\text{m}/0.080\mu\text{m}/0.080\mu\text{m}$ ).

 **Mini-Circuits**<sup>®</sup>  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
  



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No.    | DESCRIPTION | DATE     | DR  | AUTH |
|-----|------------|-------------|----------|-----|------|
| OR  | ECO-023573 | NEW RELEASE | 11/08/24 | ITG | IL   |
|     |            |             |          |     |      |
|     |            |             |          |     |      |

SUGGESTED MOUNTING CONFIGURATION FOR  
KC3009 CASE STYLE




NOTES:

1. LINE WIDTH AND GAP ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .0066"; COPPER: 1 OZ. EACH SIDE.  
FOR OTHER MATERIALS LINE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.




DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

| UNLESS OTHERWISE SPECIFIED | INITIALS    | DATE     |
|----------------------------|-------------|----------|
| DIMENSIONS ARE IN INCHES   | DRAWN ITG   | 11/08/24 |
| TOLERANCES ON:             | CHECKED GF  | 11/08/24 |
| 2 PL DECIMALS ±            | APPROVED IL | 11/08/24 |
| 3 PL DECIMALS ± .005       |             |          |
| ANGLES ±                   |             |          |
| FRACTIONS ±                |             |          |



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.





Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235


PL,KC3009,TB-BAT-#+/TB-BAT-#C+

| SIZE  | CODE IDENT | DRAWING NO: | REV:          |
|-------|------------|-------------|---------------|
| A     | 15542      | 98-PL-801   | OR            |
| FILE: | 98PL801    | SCALE: 15:1 | SHEET: 1 OF 1 |

# Evaluation Board and Circuit



DETAIL "A"  
(SCALE 5:1)




Schematic Diagram  
(Scale 5:1)

| Function | Pad     |
|----------|---------|
| RF-IN    | 2       |
| RF-OUT   | 5       |
| GND      | 1,3,4,6 |

## NOTES:

1. 1.85mm Female Connectors.
2. PCB Material: Roger RO4350B or equivalent,  
Dielectric constant=3.5, Thickness=0.0066 inch

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition  | Reference/Spec  |
|--------------------------------|--|---|
| Operating Temperature          | -40° to 85° C or -45° to 85° C or -55° to 105° C or -40° to 105° C or -40° to 95° C<br>Ambient Environment | Individual Model Data Sheet                                     |
| Storage Temperature            | -55° to 100° C or -65° to 150°<br>Ambient Environment  | Individual Model Data Sheet                                     |
| HTOL                           | 1000 hours at 125°C  | MIL-STD-883, Method 1005, Condition B                           |
| Thermal Shock                  | -55° to 100°C, 100 cycles  | MIL-STD-202, Method 107, Condition A-3, except +100°C           |
| Mechanical Shock               | 1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only   | MIL-STD-883, Method 2002, Condition B, except Y1 direction only |
| Vibration (Variable Frequency) | 50g peak   | MIL-STD-883, Method 2007, Condition B                           |
| Autoclave                      | 15 psig, 100% RH, 121°C, 96 hours  | JESD22-A102, Condition C  |
| HAST                           | 130°C, 85% RH, 96 hours  | JESD22-A110   |
| Solderability                  | 10X Magnification  | J-STD-002, Para 4.2.5, Test S, 95% Coverage                     |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 240°C peak<br>Pb-Free Process: 260°C peak   | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1                   |
| Moisture Sensitivity: Level 1  | Bake at 125°C for 24 hours<br>Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak             | J-STD-020   |

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition   | Reference/Spec          |
|--------------------------------|---|-------------------------|
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |