

Surface Mount

RF Transformer

ADT3-1T-75+

75Ω 1 to 500 MHz

The Big Deal

- Low insertion loss, 1.2 dB
- Excellent return loss, 25 dB in 1 dB bandwidth
- Low unbalance, 0.2 dB, 1°
- Small size, 0.27 x 0.31 x 0.22"



CASE STYLE: CD542

Product Overview

Mini-Circuits' ADT3-1T-75+ is a 75Ω DC isolated surface-mount transformer with a secondary/primary impedance ratio of 3:1 and a center tap on the secondary winding. This model covers the 1 to 500 MHz band with low insertion loss (1.2 dB), excellent return loss (25 dB within the 1 dB bandwidth, low phase unbalance (1°) and low amplitude unbalance (0.2 dB). The unit comes enclosed in a miniature, 6-lead plastic package measuring just 0.27 x 0.31 x 0.22", ideal for dense circuit board layouts.

Key Features

| Feature | Advantages |
|---|---|
| DC Isolation | Provides DC isolation between circuits and efficient AC transmission, eliminating the need for external DC biasing components. |
| Secondary center tap | Allows DC feed up to 30 mA and DC bias without adding bias tees into the signal chain. |
| Low insertion loss, 1.2 dB | Excellent transmission of signal power from input to output. |
| Excellent return loss, 25 dB within 1 dB bandwidth. | Provides excellent matching for 75Ω systems with low signal reflection. |
| Low phase and amplitude unbalance, 1°, 0.2 dB | Low phase and amplitude unbalance can improve a system's electromagnetic compatibility by rejecting unwanted common-mode noise. |
| Small footprint, 0.27 x 0.31 x 0.22" | Accommodates tight space requirements for dense PCB layouts. |

Surface Mount RF Transformer

75Ω 1 to 500 MHz

ADT3-1T-75+



Generic photo used for illustration purposes only

CASE STYLE: CD542

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Features

- excellent return loss, 25 dB typ. in 1 dB bandwidth
- excellent amplitude unbalance, 0.2 dB typ. and phase unbalance, 1 deg. typ. in 1dB bandwidth
- aqueous washable
- protected under US patent 6,133,525

Applications

- balun
- impedance matching
- DOCSIS 3.1



Available Tape and Reel at no extra cost

| Reel Size | Devices/Reel |
|-----------|----------------------|
| 7" | 10, 20, 50, 100, 200 |
| 13" | 500, 1000 |

Electrical Specifications at 25°C

| Parameter | Frequency (MHz) | Min. | Typ. | Max. | Unit |
|--------------------------------------|-----------------|------|------|------|--------|
| Impedance Ratio (secondary/ primary) | | | 3 | | Ohm |
| Frequency Range | | 1 | — | 500 | MHz |
| Insertion Loss* | 2-300 | — | — | 0.8 | dB |
| | 1-500 | — | — | 1.2 | |
| Amplitude Unbalance | 1-300 | — | 0.2 | 0.6 | dB |
| | 300-500 | — | 0.4 | 1.20 | |
| Phase Unbalance | 1-300 | — | 1 | 4 | Degree |
| | 300-500 | — | 4 | 8 | |
| Return Loss | 1-2 | 13 | 19 | — | dB |
| | 2-300 | 17 | 25 | — | |
| | 300-500 | 14 | 22 | — | |

* Insertion Loss is referenced to mid-band loss, 0.5 dB typ.

Maximum Ratings


| Parameter | Ratings |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C |
| Storage Temperature | -55°C to 100°C |
| RF Power | 0.25W |
| DC Current | 30mA |

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

| Function | Pin Number |
|---------------|------------|
| PRIMARY DOT | 3 |
| PRIMARY | 1 |
| SECONDARY DOT | 6 |
| SECONDARY | 4 |
| SECONDARY CT | 5 |
| NOT USED | 2 |

Config. A




Outline Drawing



Outline Dimensions (inch/mm)





| A | B | C | D | E | F | G |
|------|------|------|------|-------|------|------|
| .272 | .310 | .220 | .100 | .112 | .055 | .100 |
| 6.91 | 7.87 | 5.59 | 2.54 | 2.84 | 1.40 | 2.54 |
| H | J | K | L | wt | | |
| .030 | .026 | .065 | .300 | grams | | |
| 0.76 | 0.66 | 1.65 | 7.62 | 0.20 | | |

PCB Land Pattern



Typical Performance Data

| FREQUENCY (MHz) | INSERTION LOSS (dB) | INPUT R. LOSS (dB) | AMPLITUDE UNBALANCE (dB) | PHASE UNBALANCE (Deg.) |
|-----------------|---------------------|--------------------|--------------------------|------------------------|
| 1.0 | 1.02 | 18.88 | 0.03 | 0.26 |
| 2.0 | 0.79 | 23.05 | 0.02 | 0.18 |
| 10.0 | 0.57 | 30.52 | 0.01 | 0.22 |
| 50.0 | 0.58 | 32.09 | 0.04 | 0.16 |
| 150.0 | 0.64 | 31.42 | 0.06 | 0.04 |
| 200.0 | 0.64 | 31.03 | 0.12 | 0.13 |
| 250.0 | 0.66 | 30.66 | 0.22 | 0.27 |
| 300.0 | 0.67 | 29.74 | 0.28 | 0.61 |
| 400.0 | 0.73 | 28.00 | 0.48 | 0.82 |
| 500.0 | 0.81 | 25.24 | 0.72 | 2.00 |



Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

RF Transformer





ADT3-1T-75+

Typical Performance Data

| FREQUENCY (MHz) | AVERAGE INSERTION LOSS (dB) | INPUT RETURN LOSS (dB) | AMPLITUDE UNBALANCE (dB) | PHASE UNBALANCE (deg.) |
|-----------------|-----------------------------|------------------------|--------------------------|------------------------|
| 0.5 | 1.31 | 14.79 | 0.03 | 0.48 |
| 1.0 | 1.02 | 18.88 | 0.03 | 0.26 |
| 2.0 | 0.79 | 23.05 | 0.02 | 0.18 |
| 5.0 | 0.62 | 28.15 | 0.02 | 0.16 |
| 8.0 | 0.58 | 29.96 | 0.02 | 0.18 |
| 10 | 0.57 | 30.52 | 0.01 | 0.22 |
| 15 | 0.56 | 31.46 | 0.01 | 0.12 |
| 20 | 0.56 | 31.35 | 0.01 | 0.04 |
| 30 | 0.57 | 31.29 | 0.01 | 0.07 |
| 50 | 0.58 | 32.09 | 0.04 | 0.16 |
| 70 | 0.60 | 32.38 | 0.05 | 0.10 |
| 100 | 0.61 | 30.99 | 0.03 | 0.21 |
| 125 | 0.62 | 32.06 | 0.09 | 0.06 |
| 150 | 0.64 | 31.42 | 0.06 | 0.04 |
| 175 | 0.63 | 31.21 | 0.11 | 0.16 |
| 200 | 0.64 | 31.03 | 0.12 | 0.13 |
| 225 | 0.65 | 31.04 | 0.14 | 0.10 |
| 250 | 0.66 | 30.66 | 0.22 | 0.27 |
| 275 | 0.67 | 30.19 | 0.25 | 0.50 |
| 300 | 0.67 | 29.74 | 0.28 | 0.61 |
| 325 | 0.69 | 29.31 | 0.30 | 0.64 |
| 350 | 0.69 | 28.89 | 0.34 | 0.62 |
| 400 | 0.73 | 28.00 | 0.48 | 0.82 |
| 450 | 0.76 | 26.33 | 0.61 | 1.35 |
| 475 | 0.78 | 25.69 | 0.67 | 1.69 |
| 500 | 0.81 | 25.24 | 0.72 | 2.00 |
| 525 | 0.84 | 24.66 | 0.77 | 2.32 |
| 550 | 0.86 | 24.15 | 0.84 | 2.60 |
| 600 | 0.94 | 23.27 | 1.04 | 3.28 |
| 700 | 1.14 | 21.60 | 1.44 | 5.68 |
| 800 | 1.46 | 21.13 | 1.96 | 8.94 |



Typical Performance Data





Case Style


CD

CD541
CD542
CD636
CD637

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE# | A | B | C | D | E | F | G | H | J | K | L | WT, GRAM |
|-------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| CD541 | | | | | .082 (2.08) | | | | | | | .15 |
| CD542 | .272 (6.91) | .310 (7.87) | .220 (5.58) | .100 (2.54) | .112 (2.84) | .055 (1.40) | .100 (2.54) | .030 (0.76) | .026 (0.66) | .065 (1.65) | .300 (7.62) | .20 |
| CD636 | | | | | .162 (4.11) | | | | | | | .25 |
| CD637 | | | | | .206 (5.23) | | | | | | | .40 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F34



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel see note | |
|----------------|-------------------------|-------------------|------------------------------------|------|
| 16 | 12 | 7 | Small quantity standard (see note) | 20 |
| | | | | 50 |
| | | | 100 | |
| | | | 200 | |
| | | 13 | Standard | 500 |
| | | | | 1000 |

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Evaluation Board and Circuit


For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.
3. Must use ENA/PNA type agilent's network analyzers with impedance conversion option to convert ports to appropriate impedances.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|--|
| Operating Temperature | -40° to 85°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |