

# Coaxial Bandpass Filter

## BBP-100+

50Ω 87 to 117 MHz



Generic photo used for illustration purposes only  
CASE STYLE: FF55

### The Big Deal

- Very good rejection
- Good VSWR 1.3:1 typ in passband
- Connectorized package

### Product Overview

BBP-100+ is a 50Ω bandpass filter in a connectorized package. The bandpass filter covers from 87 to 117 MHz, offering good matching within the passband. It uses miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across production lots and consistent performance across temperature.

### Key Features

Feature	Advantages
Very good rejection	Rejects unwanted spurious signals.
Good VSWR, 1.3:1 typical in passband	This provides well matched input and output ports.
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Coaxial Bandpass Filter

# BBP-100+

50Ω 87 to 117 MHz



Generic photo used for illustration purposes only

CASE STYLE: FF55

Connectors	Model
BNC	BBP-100+

## Features

- Very good rejection, 40 dB typ.
- Good VSWR, 1.3:1 typical in passband
- Connectorized package

## Applications

- Transmitters / Receivers
- Harmonic rejection
- Test equipment
- Military Radio

## Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Insertion Loss	F1-F2	87 - 117	-	2.2	3.0	dB
	VSWR	F1-F2	87 - 117	-	1.3	1.7	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 55	40	49	-	dB
	VSWR	F3-F4	55 - 66	20	29	-	dB
		DC-F4	DC - 66	-	20	-	:1
Stop Band, Upper	Insertion Loss	F5-F6	143 - 175	20	28	-	dB
	VSWR	F6-F7	175 - 1500	40	50	-	dB
		F5-F7	143 - 1500	-	20	-	:1

## Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.25 W max.

Permanent damage may occur if any of these limits are exceeded.

## Functional Schematic



## Typical Frequency Response







## Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	108.00	76258.91	87	32.32
20	101.38	7169.24	88	31.12
30	99.20	2804.52	89	30.05
40	74.21	1019.16	90	29.09
55	49.59	230.34	91	28.26
66	30.48	63.05	92	27.55
71	20.10	26.82	93	26.94
79	3.40	1.94	94	26.44
87	1.58	1.14	95	26.04
100	1.51	1.12	96	25.71
117	2.17	1.23	97	25.42
122	3.11	1.30	98	25.19
137	21.15	15.65	99	24.98
143	27.76	22.07	100	24.79
175	49.76	47.26	111	25.18
200	59.27	61.00	112	25.47
300	76.14	81.76	113	25.80
500	89.85	67.83	115	26.68
1000	64.51	31.26	116	27.29
1500	51.03	21.92	117	28.10

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



**Coaxial Connections**

PORT - 1	BNC-Male
PORT - 2	BNC-Female

**Outline Drawing**



**Outline Dimensions ( inch / mm )**

A	B	C	D	E	Wt.
--	0.57	--	2.59	--	grams
--	14.47	--	65.79	--	40

*Note: Please refer to case style drawing for details*

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



*Typical Performance Data*


FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	106.30	108.00	101.96	0.00	0.00	0.00	0.00	0.00	0.00
2	107.94	111.36	111.42	0.00	0.00	0.00	0.00	0.00	0.00
3	104.76	102.00	105.28	0.00	0.00	0.00	0.00	0.00	0.00
4	102.15	106.53	98.33	0.00	0.00	0.00	0.00	0.00	0.00
10	98.03	106.79	108.03	0.00	0.00	0.00	0.00	0.00	0.00
20	108.34	101.38	113.33	0.00	0.00	0.00	0.00	0.00	0.00
25	99.90	108.18	120.57	0.00	0.00	0.00	0.00	0.00	0.00
30	94.07	99.20	99.11	0.00	0.01	0.01	0.00	0.00	0.00
35	83.08	82.90	83.33	0.01	0.01	0.01	0.00	0.00	0.00
40	74.32	74.21	73.53	0.01	0.02	0.02	0.00	0.01	0.01
45	65.80	65.60	65.34	0.02	0.03	0.03	0.01	0.02	0.02
50	57.81	57.62	57.33	0.04	0.05	0.05	0.02	0.03	0.03
55	49.83	49.59	49.33	0.07	0.08	0.08	0.05	0.05	0.06
56	48.22	47.97	47.71	0.07	0.08	0.09	0.05	0.06	0.07
57	46.59	46.33	46.06	0.08	0.09	0.10	0.06	0.07	0.08
59	43.30	43.01	42.73	0.10	0.12	0.12	0.08	0.09	0.10
60	41.61	41.31	41.03	0.11	0.13	0.14	0.09	0.10	0.12
61	39.90	39.60	39.31	0.13	0.15	0.16	0.10	0.12	0.13
65	32.74	32.39	32.07	0.21	0.24	0.26	0.18	0.21	0.23
66	30.84	30.48	30.16	0.24	0.28	0.30	0.21	0.24	0.27
70	22.71	22.31	21.96	0.46	0.53	0.57	0.43	0.49	0.55
71	20.51	20.10	19.74	0.57	0.65	0.71	0.53	0.61	0.68
79	3.36	3.40	3.43	8.94	9.91	10.72	8.92	9.78	10.56
80	2.53	2.65	2.74	13.50	14.76	15.77	13.45	14.44	15.32
82	1.83	1.99	2.11	28.18	29.06	28.53	27.36	26.42	25.94
87	1.44	1.58	1.69	24.79	23.59	22.99	35.09	34.29	32.96
100	1.40	1.51	1.59	24.85	24.90	24.64	17.98	18.40	18.63
110	1.60	1.73	1.82	21.76	21.38	21.06	20.59	21.05	21.28
117	2.02	2.17	2.30	19.12	19.60	19.98	18.42	18.41	18.31
120	2.34	2.55	2.72	26.85	28.96	28.29	19.05	18.51	17.83
122	2.81	3.11	3.36	20.14	17.62	16.11	15.56	14.22	13.30
130	11.07	11.70	12.16	2.53	2.46	2.38	2.45	2.37	2.32
137	20.69	21.15	21.50	1.10	1.11	1.11	1.10	1.11	1.11
140	24.21	24.61	24.93	0.90	0.92	0.92	0.90	0.92	0.93
143	27.41	27.76	28.05	0.77	0.79	0.79	0.78	0.79	0.81
146	30.33	30.64	30.89	0.67	0.70	0.70	0.69	0.70	0.72
175	49.60	49.76	49.84	0.34	0.37	0.38	0.35	0.37	0.39
180	51.92	52.02	52.10	0.32	0.34	0.36	0.33	0.35	0.36
200	59.25	59.27	59.34	0.26	0.28	0.30	0.26	0.29	0.30
250	69.90	70.09	70.06	0.20	0.23	0.25	0.19	0.22	0.24
300	75.76	76.14	76.19	0.18	0.21	0.24	0.16	0.19	0.21
350	79.88	80.02	80.26	0.18	0.21	0.24	0.15	0.18	0.20
400	84.60	85.14	85.45	0.18	0.22	0.25	0.14	0.18	0.20
450	89.90	89.88	89.31	0.19	0.24	0.27	0.14	0.18	0.20
500	90.98	89.85	90.58	0.21	0.26	0.29	0.14	0.18	0.21
550	91.81	92.00	89.40	0.22	0.28	0.32	0.14	0.19	0.21
600	89.97	88.67	86.49	0.25	0.31	0.35	0.14	0.20	0.23
650	86.08	84.36	84.49	0.28	0.34	0.38	0.15	0.21	0.24
700	81.11	79.94	79.93	0.30	0.36	0.42	0.16	0.22	0.26
750	79.14	77.54	76.97	0.33	0.40	0.46	0.17	0.24	0.28
800	75.59	74.55	74.35	0.36	0.43	0.50	0.19	0.26	0.30
850	72.04	71.18	70.63	0.40	0.46	0.53	0.20	0.28	0.32
900	70.19	69.45	69.02	0.43	0.49	0.57	0.22	0.30	0.35
950	68.16	67.38	66.96	0.46	0.52	0.61	0.24	0.33	0.38
1000	65.53	64.51	64.19	0.49	0.56	0.65	0.26	0.35	0.41
1050	63.86	63.14	62.77	0.53	0.59	0.68	0.29	0.38	0.44
1200	58.75	58.24	57.85	0.62	0.67	0.78	0.38	0.48	0.54
1300	56.59	55.95	55.65	0.67	0.72	0.84	0.44	0.55	0.62
1400	54.03	53.50	53.15	0.71	0.76	0.89	0.51	0.63	0.70
1500	51.54	51.03	50.63	0.74	0.79	0.93	0.59	0.71	0.79

*Typical Performance Data*


FREQ.  (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
87.0	32.63	32.32	32.07
87.2	32.37	32.07	31.84
88.0	31.38	31.12	30.90
88.2	31.14	30.89	30.68
89.0	30.27	30.05	29.85
89.2	30.06	29.84	29.66
90.0	29.27	29.09	28.94
90.4	28.91	28.74	28.60
91.0	28.41	28.26	28.15
91.2	28.24	28.10	28.00
91.4	28.09	27.97	27.85
92.0	27.64	27.55	27.46
92.4	27.38	27.30	27.22
93.0	27.01	26.94	26.89
93.2	26.90	26.84	26.78
94.0	26.50	26.44	26.41
94.2	26.40	26.36	26.32
95.0	26.07	26.04	26.02
95.6	25.86	25.83	25.82
96.0	25.73	25.71	25.70
96.2	25.68	25.67	25.65
97.0	25.44	25.42	25.42
97.2	25.38	25.38	25.36
98.0	25.19	25.19	25.17
98.6	25.07	25.06	25.04
99.0	24.99	24.98	24.97
99.8	24.83	24.82	24.82
100.0	24.80	24.79	24.78
100.4	24.72	24.70	24.70
101.0	24.62	24.61	24.60
101.8	24.50	24.50	24.49
102.0	24.48	24.48	24.47
102.4	24.42	24.43	24.42
103.0	24.36	24.37	24.37
103.4	24.33	24.35	24.34
104.0	24.28	24.30	24.31
104.8	24.26	24.30	24.31
105.0	24.27	24.30	24.31
105.2	24.25	24.29	24.32
106.4	24.31	24.36	24.39
107.0	24.36	24.41	24.45
107.8	24.45	24.52	24.57
108.0	24.48	24.55	24.60
109.0	24.64	24.71	24.79
110.0	24.85	24.94	25.02
111.0	25.08	25.18	25.27
112.0	25.35	25.47	25.57
113.0	25.66	25.80	25.91
114.0	26.02	26.19	26.32
115.0	26.47	26.68	26.84
117.0	27.76	28.10	28.35

## Typical Performance Curves


**INSERTION LOSS vs. TEMPERATURE**  
INPUT POWER = 0 dBm




**INSERTION LOSS vs. TEMPERATURE (Zoomed)**  
INPUT POWER = 0 dBm




**INPUT RETURN LOSS vs. TEMPERATURE**  
INPUT POWER = 0 dBm




**OUTPUT RETURN LOSS vs. TEMPERATURE**  
INPUT POWER = 0 dBm



**GROUP DELAY vs. TEMPERATURE**  
INPUT POWER = 0 dBm



### Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF55	--	.57 (14.47)	--	2.59 (65.79)	--	40.0

Dimensions are in inches (mm). Tolerances: 2Pl. +.03/-.04; 3Pl. ± .015

#### Note:

1. Case material: Stainless steel.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C