

Coaxial Bandpass Filter

BBP-101+

50Ω

94 to 108 MHz



The Big Deal

- Flat group delay over passband
- Narrow bandwidth
- Good VSWR (1.2:1 typical)
- Fast roll-off
- High rejection

Generic photo used for illustration purposes only
CASE STYLE: FF55

Product Overview

BBP-101+ is a 50Ω bandpass filter in a connectorized package. The bandpass filter covers from 94 to 108 MHz, and offers good matching within the passband with high out of band rejection. The filter uses miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
Flat group delay over passband	The model has group delay over passband around 45 ns
Good VSWR, 1.2:1 typical over passband	This provides well matched input and output ports.
High rejection	This enables the filter to attenuate spurious signals and reject harmonics for broad frequency band.
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Bandpass Filter

50Ω 94 to 108 MHz

BBP-101+




Features

- Flat group delay over passband
- Good VSWR, 1.2:1 typical in passband
- High rejection, 60 dB typ
- Rugged shielded case
- Connectorized package
- Fast roll-off


Applications

- Test equipment
- Harmonic rejection
- Transmitters / Receivers
- Military

Functional Schematic



Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Generic photo used for illustration purposes only

CASE STYLE: FF55

Connectors	BNC	Model	BBP-101+
------------	-----	-------	----------

Electrical Specifications at 25°C

	Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center frequency	-	-	-	101	-	MHz
	Insertion Loss	F1-F2	94 - 108	-	2.3	3.5	dB
	VSWR	F1-F2	94 - 108	-	1.2	1.6	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 50	50	65	-	dB
		F3-F4	50 - 80	20	29	-	dB
	VSWR	DC-F4	DC - 80	-	20	-	:1
Stop Band, Upper	Insertion Loss	F5-F6	130 - 200	20	28	-	dB
		F6-F7	200 - 680	50	60	-	dB
		F7-F8	680 - 2000	-	40	-	dB
	VSWR	F5-F8	130 - 2000	-	20	-	:1





Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.25 W max.

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	88.85	84.83	94.0	51.17
10	71.57	64.16	94.5	49.18
30	65.06	47.20	95.0	47.44
50	65.99	47.41	95.5	45.94
79	31.55	36.76	96.0	44.65
80	29.37	34.02	96.5	43.55
83	22.30	24.16	97.0	42.60
91	3.31	1.65	97.5	41.76
94	2.19	1.19	98.0	41.03
101	1.80	1.05	98.5	40.39
108	1.98	1.12	99.0	39.82
124	20.71	16.97	99.5	39.32
130	27.84	23.53	100.0	38.88
133	30.83	26.35	100.5	38.49
145	40.41	35.58	101.0	38.18
200	70.25	69.12	101.5	37.91
680	93.18	198.49	102.0	37.69
1000	70.76	104.09	106.0	37.67
1500	68.61	51.28	107.0	38.36
2000	58.15	41.32	108.0	39.51



Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Coaxial Connections

PORT - 1	BNC-Male
PORT - 2	BNC-Female

Outline Drawing**Outline Dimensions (inch)**

A	B	C	D	E	Wt.
--	0.57	--	2.59	--	grams
--	14.47	--	65.79	--	40

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Band Pass Filter

BBP-101+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1.0	90.02	88.85	88.68	0.15	0.20	0.23	0.15	0.20	0.23
5.0	77.46	76.11	75.89	0.18	0.23	0.26	0.18	0.23	0.26
10.0	71.99	71.57	71.33	0.22	0.27	0.30	0.22	0.26	0.29
12.0	70.77	70.39	69.79	0.23	0.28	0.30	0.23	0.28	0.31
14.0	69.78	69.20	68.74	0.25	0.30	0.32	0.24	0.29	0.32
18.0	68.10	67.49	67.50	0.27	0.32	0.34	0.27	0.31	0.34
20.0	67.68	66.80	66.64	0.28	0.33	0.35	0.28	0.32	0.35
30.0	65.66	65.06	64.95	0.32	0.37	0.39	0.32	0.36	0.38
32.0	65.29	65.01	64.65	0.33	0.37	0.39	0.32	0.36	0.39
34.0	65.12	64.77	64.45	0.33	0.38	0.39	0.32	0.37	0.39
36.0	65.03	64.79	64.30	0.33	0.38	0.39	0.33	0.37	0.39
40.0	65.05	64.49	64.23	0.34	0.38	0.39	0.33	0.37	0.39
42.0	65.02	64.97	64.50	0.34	0.38	0.39	0.33	0.37	0.39
50.0	66.62	65.99	66.00	0.33	0.37	0.38	0.32	0.36	0.38
52.0	67.41	66.79	66.90	0.33	0.36	0.38	0.32	0.36	0.38
60.0	79.78	80.46	81.36	0.31	0.35	0.37	0.31	0.35	0.37
70.0	49.43	49.31	49.15	0.31	0.36	0.38	0.31	0.36	0.38
79.5	30.75	30.47	30.26	0.42	0.49	0.53	0.43	0.50	0.54
80.0	29.66	29.37	29.15	0.43	0.51	0.55	0.44	0.52	0.56
83.5	21.39	21.04	20.77	0.66	0.78	0.85	0.68	0.81	0.89
91.0	3.12	3.31	3.39	11.11	12.20	13.06	12.02	13.42	14.61
94.0	1.94	2.19	2.33	20.66	21.23	21.25	22.28	22.66	22.40
100.0	1.58	1.81	1.94	33.07	32.15	30.75	29.86	29.44	28.90
101.0	1.57	1.80	1.93	32.85	32.86	31.72	31.22	31.26	30.72
108.0	1.71	1.98	2.13	26.38	25.21	25.29	26.72	25.84	26.17
113.0	3.24	3.77	4.11	8.96	8.57	8.27	9.10	8.73	8.45
123.5	19.49	20.03	20.37	0.98	1.06	1.10	0.97	1.06	1.10
130.0	27.42	27.84	28.12	0.67	0.74	0.76	0.66	0.73	0.77
133.0	30.45	30.83	31.08	0.60	0.66	0.68	0.59	0.65	0.69
140.0	36.47	36.78	37.00	0.49	0.54	0.56	0.48	0.54	0.56
145.0	40.15	40.41	40.63	0.44	0.49	0.50	0.43	0.48	0.51
146.0	40.83	41.09	41.29	0.43	0.48	0.50	0.42	0.48	0.50
150.0	43.44	43.69	43.90	0.40	0.45	0.46	0.39	0.44	0.46
200.0	70.47	70.25	70.46	0.21	0.25	0.26	0.21	0.25	0.27
221.0	81.64	79.69	77.80	0.17	0.22	0.23	0.18	0.22	0.23
231.0	78.32	76.54	76.36	0.16	0.20	0.21	0.16	0.20	0.22
241.0	75.52	75.03	73.98	0.15	0.19	0.20	0.15	0.19	0.20
251.0	74.34	72.96	73.44	0.14	0.18	0.19	0.14	0.18	0.19
301.0	71.77	71.87	72.01	0.10	0.13	0.14	0.10	0.14	0.15
421.0	74.59	74.90	74.53	0.05	0.09	0.10	0.05	0.09	0.10
501.0	77.29	78.01	78.15	0.04	0.08	0.09	0.03	0.07	0.08
510.0	77.18	78.06	78.58	0.04	0.08	0.09	0.03	0.07	0.08
520.0	78.04	78.23	78.78	0.04	0.08	0.09	0.03	0.07	0.08
530.0	79.63	79.20	79.29	0.04	0.08	0.09	0.03	0.07	0.08
600.0	82.12	84.83	83.39	0.03	0.08	0.09	0.02	0.06	0.07
650.0	85.01	88.59	86.99	0.04	0.08	0.10	0.01	0.06	0.07
680.0	90.11	93.18	91.88	0.04	0.09	0.10	0.01	0.06	0.07
700.0	89.44	94.11	99.46	0.04	0.09	0.11	0.01	0.06	0.08
750.0	82.55	81.22	81.62	0.05	0.10	0.12	0.01	0.06	0.08
800.0	56.21	55.30	54.58	0.06	0.12	0.15	0.03	0.08	0.10
850.0	43.20	44.72	45.92	0.12	0.17	0.19	0.06	0.11	0.12
900.0	64.43	64.80	64.89	0.08	0.14	0.17	0.03	0.09	0.11
950.0	69.19	69.12	69.50	0.09	0.15	0.18	0.03	0.09	0.12
1000.0	69.66	70.76	70.82	0.10	0.17	0.20	0.04	0.10	0.13
1100.0	68.44	68.60	68.94	0.13	0.20	0.23	0.06	0.13	0.16
1200.0	47.93	47.77	47.66	0.19	0.27	0.31	0.12	0.19	0.22
1300.0	67.16	67.38	67.16	0.20	0.27	0.31	0.12	0.19	0.22
1500.0	68.98	68.61	67.88	0.26	0.34	0.38	0.19	0.27	0.30
1800.0	63.11	62.51	62.16	0.31	0.40	0.45	0.29	0.38	0.41
2000.0	58.75	58.15	57.78	0.32	0.42	0.46	0.33	0.43	0.47



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR
BBP-101+
190920
Page 1 of 2

Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
90.0	61.86	61.62	61.63
90.5	63.06	62.43	62.14
91.0	63.33	62.35	61.83
91.5	62.71	61.48	60.76
92.0	61.32	59.96	59.11
92.5	59.34	57.93	57.05
93.0	57.00	55.67	54.82
93.5	54.54	53.36	52.58
94.0	52.16	51.17	50.48
94.5	50.01	49.18	48.62
95.0	48.10	47.44	46.98
95.5	46.48	45.94	45.56
96.0	45.09	44.65	44.35
96.5	43.92	43.55	43.29
97.0	42.90	42.60	42.37
97.5	42.02	41.76	41.56
98.0	41.27	41.03	40.87
98.5	40.59	40.39	40.25
99.0	39.98	39.82	39.69
99.5	39.46	39.32	39.21
100.0	39.00	38.88	38.79
100.5	38.59	38.49	38.43
101.0	38.25	38.18	38.13
101.5	37.95	37.91	37.88
102.0	37.71	37.69	37.68
102.5	37.52	37.51	37.51
103.0	37.37	37.38	37.39
103.5	37.28	37.30	37.33
104.0	37.21	37.25	37.31
104.5	37.21	37.28	37.33
105.0	37.26	37.34	37.42
105.5	37.36	37.47	37.56
106.0	37.54	37.67	37.79
106.5	37.80	37.96	38.11
107.0	38.14	38.36	38.54
107.5	38.62	38.88	39.09
108.0	39.21	39.51	39.75
108.5	39.94	40.28	40.54
109.0	40.78	41.16	41.44
109.5	41.74	42.14	42.42
110.0	42.78	43.16	43.43



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
BBP-101+






190920

Page 2 of 2

Coaxial Band Pass Filter

BBP-101+

Typical Performance Curves




Case Style

FF

FF55

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF55	--	.57 (14.47)	--	2.59 (65.79)	--	40.0

Dimensions are in inches (mm). Tolerances: 2Pl. +.03/.04; 3Pl. ± .015

Note:

1. Case material: Stainless steel.

 **Mini-Circuits®**
ISO 9001 ISO 14001 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

ALL NEW

minicircuits.com



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C