


High Power Bi-Directional Coupler

BDCN-14-342+

50Ω 14 dB Coupling DC Pass 1700 to 3400 MHz



Generic photo used for illustration purposes only

CASE STYLE: FV1206-1

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost

Reel Size Devices/Reel
7" 20, 50, 100, 200, 500, 1000, 3000

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	0.5A
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

INPUT	1
OUTPUT	4
COUPLED (forward)	6
COUPLED (reverse)	3
GROUND	2,5

Features

- four-port coupler
- wideband, 1700 to 3400 MHz
- excellent return loss, all ports
- ultra small size, hermetically sealed
- minimal variation with temperature variation
- protected by US Patent 7,049,905
- DC current through input to output 0.5A Max. at 1.0 watt RF input power

Applications

- UMTS • CDMA
- PCS • ISM
- GPS • DCS
- TDMA

Electrical Specifications at 25°C


Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		1700	—	3400	MHz
Mainline Loss	1700-2100	—	0.4	0.55	dB
	2100-2700	—	0.45	0.6	
	2700-3400	—	0.4	0.55	
Nominal Coupling	1700-2100	—	14	—	dB
	2100-2700	—	13	—	
	2700-3400	—	15.5	—	
Coupling Flatness(±)	1700-2100	—	0.4	—	dB
	2100-2700	—	0.4	—	
	2700-3400	—	2.1	—	
Directivity	1700-2100	8	15	—	dB
	2100-2700	8	20	—	
	2700-3400	6	15	—	
Return Loss (Input)	1700-3400	—	20	—	dB
Return Loss (Output)	1700-3400	—	20	—	dB
Return Loss (Coupling)	1700-3400	—	20	—	dB
Input Power ¹	1700-3400	—	—	16	W

1. Derate linearly 8W at 100°C


Typical Performance Data

Frequency (MHz)	Mainline Loss (dB)		Coupling (dB)		Directivity (dB)		Return Loss (dB)		
	In-Out	In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd	Cpl Rev
1700.0	0.38	14.0	14.0	31.7	31.6	26.5	26.8	33.6	31.9
1900.0	0.41	13.6	13.6	33.4	33.1	26.9	27.8	35.4	33.5
2100.0	0.42	13.4	13.4	36.0	35.1	27.8	29.3	39.0	37.0
2300.0	0.43	13.3	13.3	40.2	37.9	28.4	30.6	41.2	45.0
2500.0	0.43	13.4	13.4	48.1	41.7	28.3	31.1	37.1	47.7
2700.0	0.42	13.7	13.7	52.6	46.1	27.7	30.6	34.7	41.8
2900.0	0.41	14.2	14.2	41.1	43.3	26.5	29.4	35.6	42.5
3100.0	0.40	14.9	14.9	36.1	37.9	25.2	27.7	38.9	43.7
3300.0	0.39	15.9	15.9	32.5	33.8	23.7	25.7	41.1	37.9
3400.0	0.38	16.6	16.6	31.1	32.2	23.0	24.8	36.5	34.0

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch/mm)

A	B	C	D	E	F
.126	.063	.035	.024	.022	.011
3.20	1.60	0.89	0.61	0.56	0.28
G	H	J	K	wt	
.039	.024	.042	.123	grams	
0.99	0.61	1.07	3.12	.020	

Demo Board MCL P/N: TB-1127+ Suggested PCB Layout (PL-669)






NOTES:


1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR BI-DIRECTIONAL COUPLER WITHOUT INTERNAL TRANSFORMERS AND RESISTORS.



Bi-Directional Coupler

BDCN-14-342+

Typical Performance Data




FREQ. (MHz)	INSERTION LOSS (dB) IN-OUT	COUPLING (dB)		DIRECTIVITY (dB)		RETURN LOSS (dB)				
		IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD		REV
								FWD	REV	
1700	0.38	14.00	14.00	17.63	17.66	26.54	26.78	33.60	31.87	
1725	0.39	13.94	13.94	17.79	17.90	26.53	26.88	33.78	31.94	
1750	0.39	13.88	13.88	18.01	18.08	26.58	26.95	34.01	32.08	
1775	0.39	13.83	13.83	18.25	18.32	26.61	27.02	34.08	32.39	
1800	0.40	13.78	13.78	18.44	18.60	26.65	27.23	34.38	32.41	
1825	0.40	13.73	13.73	18.72	18.84	26.74	27.36	34.40	32.59	
1850	0.40	13.69	13.69	18.93	19.17	26.82	27.49	34.84	32.87	
1875	0.41	13.64	13.65	19.17	19.39	26.89	27.59	35.22	33.18	
1900	0.41	13.60	13.61	19.49	19.75	26.88	27.77	35.45	33.45	
1925	0.41	13.57	13.57	19.74	20.04	27.04	27.88	35.83	33.72	
1950	0.41	13.54	13.54	19.97	20.34	27.04	28.11	36.20	34.04	
1975	0.41	13.50	13.51	20.24	20.68	27.19	28.27	36.64	34.42	
2000	0.41	13.47	13.48	20.52	21.00	27.29	28.36	36.92	34.74	
2025	0.42	13.45	13.45	20.79	21.36	27.34	28.48	37.28	35.15	
2050	0.42	13.42	13.43	21.13	21.73	27.43	28.71	37.86	35.53	
2075	0.42	13.40	13.41	21.45	22.12	27.63	29.02	38.26	36.24	
2100	0.42	13.39	13.39	21.69	22.57	27.77	29.27	38.97	36.97	
2125	0.42	13.37	13.37	22.09	23.04	27.87	29.42	39.73	37.57	
2150	0.42	13.36	13.36	22.35	23.45	27.89	29.53	40.15	38.29	
2175	0.42	13.34	13.35	22.69	23.91	27.97	29.64	40.58	39.01	
2200	0.42	13.34	13.34	23.03	24.43	28.09	29.90	41.07	40.17	
2225	0.43	13.33	13.33	23.45	24.92	28.24	30.16	41.00	40.78	
2250	0.43	13.33	13.33	23.80	25.49	28.28	30.32	41.37	42.09	
2275	0.43	13.33	13.33	24.18	26.09	28.32	30.38	41.07	43.10	
2300	0.43	13.33	13.33	24.56	26.84	28.40	30.64	41.25	45.03	
2325	0.43	13.33	13.33	24.97	27.57	28.43	30.72	41.08	47.39	
2350	0.43	13.34	13.34	25.43	28.26	28.44	30.65	40.42	49.59	
2375	0.43	13.35	13.35	25.90	29.08	28.36	30.88	39.61	52.00	
2400	0.43	13.37	13.36	26.32	30.12	28.52	31.14	39.09	52.64	
2425	0.43	13.38	13.38	26.91	30.93	28.61	31.35	38.40	53.22	
2450	0.43	13.40	13.39	27.39	32.07	28.66	31.31	38.01	51.06	
2475	0.43	13.42	13.42	27.70	33.06	28.37	31.10	37.27	49.63	
2500	0.43	13.44	13.43	28.23	34.61	28.29	31.07	37.09	47.71	
2525	0.42	13.47	13.46	28.90	36.63	28.29	31.15	36.50	45.93	
2550	0.43	13.50	13.49	29.40	38.26	28.23	31.15	35.99	44.58	
2575	0.42	13.53	13.52	30.06	40.66	28.20	31.04	35.79	44.05	
2600	0.42	13.57	13.56	30.57	43.83	27.95	30.99	35.45	43.09	
2625	0.42	13.60	13.59	31.45	44.89	27.87	30.95	34.99	41.96	
2650	0.42	13.64	13.63	32.00	43.25	27.90	30.90	34.79	41.43	
2675	0.42	13.69	13.67	32.35	40.48	27.84	30.89	34.82	41.54	
2700	0.42	13.73	13.72	32.39	38.83	27.68	30.63	34.72	41.76	
2725	0.42	13.78	13.77	32.63	36.37	27.50	30.60	34.75	41.27	
2750	0.42	13.84	13.82	32.59	34.46	27.36	30.31	34.70	41.43	
2775	0.42	13.89	13.88	32.19	32.91	27.20	30.25	34.83	41.65	
2800	0.42	13.95	13.93	31.62	31.38	27.02	29.96	35.10	42.09	
2825	0.41	14.01	14.00	30.99	30.15	26.92	29.77	35.01	41.98	
2850	0.41	14.08	14.06	30.40	28.90	26.81	29.69	35.29	41.69	
2875	0.41	14.15	14.13	29.87	27.87	26.64	29.65	35.32	41.88	
2900	0.41	14.23	14.20	29.03	26.92	26.45	29.37	35.60	42.52	
2925	0.41	14.30	14.27	28.23	25.99	26.26	29.07	36.06	42.63	
2950	0.41	14.38	14.35	27.40	25.22	26.16	28.95	36.07	42.38	
2975	0.40	14.46	14.43	26.70	24.56	26.03	28.79	36.15	42.17	
3000	0.40	14.55	14.52	25.81	23.80	25.91	28.58	36.73	42.96	
3025	0.40	14.65	14.61	25.06	23.09	25.69	28.30	37.12	43.15	
3050	0.40	14.74	14.70	24.33	22.44	25.51	28.12	37.75	43.27	
3075	0.40	14.84	14.80	23.67	21.71	25.42	27.95	38.34	43.36	
3100	0.40	14.95	14.90	22.94	21.14	25.18	27.72	38.87	43.73	
3150	0.39	15.17	15.11	21.56	19.90	24.68	27.04	40.01	42.56	
3200	0.39	15.41	15.34	20.28	18.77	24.48	26.74	41.39	41.36	
3250	0.39	15.67	15.59	19.08	17.70	24.06	26.22	41.59	39.41	
3300	0.39	15.95	15.86	17.87	16.60	23.74	25.74	41.10	37.88	
3350	0.38	16.25	16.15	16.74	15.61	23.32	25.33	38.92	35.73	
3400	0.38	16.57	16.45	15.62	14.57	23.01	24.82	36.51	33.99	



Bi-Directional Coupler

Typical Performance Curves


BDCN-14-342+



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAM
FV1206-1	.126 (3.20)	.063 (1.60)	.035 (0.89)	.024 (0.61)	.022 (0.56)	.011 (0.28)	.039 (0.99)	.024 (0.61)	.042 (1.07)	.123 (3.12)	--	--	--	--	.020

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles
FV1206-1
FV1206-3




ILLUSTRATION 2

Applicable Case Styles
FV1206-4
FV1206-5
FV1206-6
FV1206-7
FV1206-9




ILLUSTRATION 3

Applicable Case Styles
FV1206-12
GE0805C-18
NL1008C-6
NL1008C-7
NL1008C-9
NL1008C-10

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits ISO 9001 & ISO 14001 Certified

Mini-Circuits[®]


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS



REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-002173	NEW RELEASE	03/19/20	ITG	SL

SUGGESTED MOUNTING CONFIGURATION
FOR FV1206-1 CASE STYLE



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.020" \pm .0015"$.
COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN ITG	03/18/20
TOLERANCES ON:	CHECKED GF	03/18/20
2 PL DECIMALS \pm	APPROVED SL	03/19/20
3 PL DECIMALS \pm .005		
ANGLES \pm		
FRACTIONS \pm		



Mini-Circuits®


13 Neptune Avenue
Brooklyn NY 11235

PL, FV1206-1, TB-1127+


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-669	REV: OR
FILE: 98PL669	SCALE: 10:1	SHEET: 1 OF 1	

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit




TB-1127+



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A