


High Power Bi-Directional Coupler

BDCN-14-22+

50Ω 14dB Coupling DC Pass 1930 to 2170 MHz



Generic photo used for illustration purposes only

CASE STYLE: FV1206-1

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost

| Reel Size | Devices/Reel |
|-----------|-----------------------------------|
| 7" | 20, 50, 100, 200, 500, 1000, 3000 |

Maximum Ratings


| | |
|-----------------------|----------------|
| Operating Temperature | -55°C to 100°C |
| Storage Temperature | -55°C to 100°C |
| DC Current | 0.5A |

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

| | |
|-------------------|-----|
| INPUT | 1 |
| OUTPUT | 4 |
| COUPLED (forward) | 6 |
| COUPLED (reverse) | 3 |
| GROUND | 2,5 |

Outline Drawing



PCB Land Pattern




Suggested Layout, Tolerance to be within ±.002

Outline Dimensions (inch/mm)

| A | B | C | D | E | F | G | H | J | K | wt |
|------|------|------|------|------|------|------|------|------|------|-------|
| .126 | .063 | .035 | .024 | .022 | .011 | .039 | .024 | .042 | .123 | grams |
| 3.20 | 1.60 | 0.89 | 0.61 | 0.56 | 0.28 | 0.99 | 0.61 | 1.07 | 3.12 | .020 |

Demo Board MCL P/N: TB-255+ Suggested PCB Layout (PL-131)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. DEMOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
4. DEMOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- four-port coupler
- wideband, 1930 to 2170 MHz
- excellent return loss, all ports
- ultra small size, hermetically sealed
- minimal variation with temperature variation
- protected by US Patent 7,049,905
- DC current through input to output 0.5A Max. at 1.0 watt RF input power

Applications

- UMTS
- PCS

Electrical Specifications


| Parameter | Frequency (MHz) | Min. | Typ. | Max. | Units |
|----------------------------|-----------------|------|----------|------|-------|
| Frequency Range | | 1930 | | 2170 | MHz |
| Coupling | 1930 - 2170 | — | 13.8±1.0 | — | dB |
| Coupling Flatness(±) | 1930 - 2170 | — | 0.15 | — | dB |
| Mainline Loss ¹ | 1930 - 1990 | — | 0.5 | 0.9 | dB |
| | 2110 - 2170 | — | 0.5 | 0.9 | dB |
| Directivity | 1930 - 1990 | 17 | 22 | — | dB |
| | 2110 - 2170 | 18 | 25 | — | dB |
| Return Loss | 1930 - 2170 | — | 19 | — | dB |
| Input Power ¹ | 1930 - 2170 | — | 16 | — | W |

1. Derate linearly 8W at 100°C


Typical Performance Data

| Frequency (MHz) | Mainline Loss (dB) | | Coupling (dB) | | Directivity (dB) | | Return Loss (dB) | | |
|-----------------|--------------------|------------|---------------|-------------|------------------|-------|------------------|---------|---------|
| | In-Out | In-Cpl Fwd | Out-Cpl Rev | Out-Cpl Fwd | In-Cpl Rev | In | Out | Cpl Fwd | Cpl Rev |
| 1920.00 | 0.49 | 14.23 | 14.24 | 25.80 | 25.24 | 23.29 | 23.14 | 28.62 | 26.21 |
| 1955.00 | 0.49 | 14.22 | 14.23 | 26.88 | 26.34 | 23.91 | 23.07 | 27.94 | 27.00 |
| 1980.00 | 0.50 | 14.22 | 14.23 | 27.42 | 26.89 | 23.65 | 22.78 | 28.32 | 26.92 |
| 2000.00 | 0.50 | 14.22 | 14.23 | 27.94 | 27.40 | 23.63 | 23.17 | 29.06 | 26.72 |
| 2020.00 | 0.50 | 14.22 | 14.23 | 28.29 | 27.76 | 24.05 | 23.66 | 29.13 | 26.91 |
| 2060.00 | 0.50 | 14.24 | 14.24 | 28.51 | 27.99 | 23.96 | 23.09 | 28.50 | 27.10 |
| 2080.00 | 0.50 | 14.25 | 14.25 | 28.49 | 28.01 | 23.90 | 23.40 | 28.97 | 26.80 |
| 2100.00 | 0.50 | 14.26 | 14.26 | 28.30 | 27.88 | 24.33 | 23.91 | 29.31 | 27.02 |
| 2140.00 | 0.50 | 14.30 | 14.30 | 27.21 | 27.01 | 24.32 | 23.29 | 28.51 | 27.63 |
| 2160.00 | 0.51 | 14.32 | 14.32 | 26.57 | 26.45 | 24.23 | 23.60 | 28.57 | 27.36 |


BDCN-14-22+
MAINLINE LOSS




BDCN-14-22+
COUPLING & DIRECTIVITY



BDCN-14-22+
RETURN LOSS



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR BI-DIRECTIONAL COUPLER WITHOUT INTERNAL TRANSFORMERS AND RESISTORS.



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M151107
ED-10885/1
BDCN-14-22+
AD/CP/AM
231117

Bi-Directional Coupler

BDCN-14-22+


Typical Performance Data

| FREQ. (MHz) | INSERTION LOSS (dB) IN-OUT | COUPLING (dB) | | DIRECTIVITY (dB) | | RETURN LOSS (dB) | | | |
|----------------|-------------------------------------|------------------|---------|---------------------|---------|---------------------|-------|-------|-------|
| | | IN-FWD | OUT-REV | IN-REV | OUT-FWD | IN | OUT | FWD | REV |
| 1500.0 | 0.42 | 14.87 | 14.88 | 17.63 | 17.67 | 23.35 | 23.34 | 25.52 | 25.99 |
| 1550.0 | 0.43 | 14.75 | 14.75 | 18.23 | 18.33 | 23.79 | 22.95 | 25.58 | 26.74 |
| 1600.0 | 0.44 | 14.63 | 14.65 | 18.91 | 19.07 | 23.34 | 23.58 | 25.98 | 26.07 |
| 1650.0 | 0.45 | 14.53 | 14.54 | 19.59 | 19.81 | 23.33 | 22.75 | 26.38 | 26.18 |
| 1700.0 | 0.46 | 14.45 | 14.46 | 20.43 | 20.65 | 23.72 | 23.26 | 26.46 | 26.58 |
| 1720.0 | 0.46 | 14.42 | 14.43 | 20.78 | 21.01 | 23.62 | 22.75 | 26.68 | 26.71 |
| 1740.0 | 0.47 | 14.39 | 14.40 | 21.18 | 21.40 | 23.21 | 22.77 | 27.05 | 26.28 |
| 1780.0 | 0.47 | 14.34 | 14.35 | 21.97 | 22.28 | 23.47 | 23.26 | 27.19 | 26.48 |
| 1800.0 | 0.48 | 14.32 | 14.33 | 22.36 | 22.72 | 23.44 | 22.72 | 27.48 | 26.58 |
| 1820.0 | 0.48 | 14.30 | 14.31 | 22.76 | 23.19 | 23.16 | 22.60 | 27.94 | 26.24 |
| 1840.0 | 0.48 | 14.28 | 14.29 | 23.20 | 23.68 | 23.27 | 23.11 | 27.99 | 26.14 |
| 1880.0 | 0.48 | 14.25 | 14.26 | 24.13 | 24.64 | 23.72 | 22.87 | 27.72 | 26.82 |
| 1900.0 | 0.49 | 14.24 | 14.25 | 24.64 | 25.18 | 23.31 | 22.68 | 28.26 | 26.46 |
| 1920.0 | 0.49 | 14.23 | 14.24 | 25.24 | 25.80 | 23.29 | 23.14 | 28.62 | 26.21 |
| 1955.0 | 0.49 | 14.22 | 14.23 | 26.34 | 26.88 | 23.91 | 23.07 | 27.94 | 27.00 |
| 1980.0 | 0.50 | 14.22 | 14.23 | 26.89 | 27.42 | 23.65 | 22.78 | 28.32 | 26.92 |
| 2000.0 | 0.50 | 14.22 | 14.23 | 27.40 | 27.94 | 23.63 | 23.17 | 29.06 | 26.72 |
| 2020.0 | 0.50 | 14.22 | 14.23 | 27.76 | 28.29 | 24.05 | 23.66 | 29.13 | 26.91 |
| 2060.0 | 0.50 | 14.24 | 14.24 | 27.99 | 28.51 | 23.96 | 23.09 | 28.50 | 27.10 |
| 2080.0 | 0.50 | 14.25 | 14.25 | 28.01 | 28.49 | 23.90 | 23.40 | 28.97 | 26.80 |
| 2100.0 | 0.50 | 14.26 | 14.26 | 27.88 | 28.30 | 24.33 | 23.91 | 29.31 | 27.02 |
| 2140.0 | 0.50 | 14.30 | 14.30 | 27.01 | 27.21 | 24.32 | 23.29 | 28.51 | 27.63 |
| 2160.0 | 0.51 | 14.32 | 14.32 | 26.45 | 26.57 | 24.23 | 23.60 | 28.57 | 27.36 |
| 2200.0 | 0.50 | 14.36 | 14.36 | 25.10 | 25.16 | 24.93 | 24.26 | 28.76 | 27.98 |
| 2300.0 | 0.51 | 14.54 | 14.53 | 21.71 | 21.69 | 25.09 | 24.22 | 28.13 | 28.67 |




Typical Performance Curves


Insertion Loss




Coupling



Directivity




Return Loss



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm.002$

| CASE # | A | B | C | D | E | F | G | H | J | K | L | M | N | P | WT. GRAM |
|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----|----|----|----|----------|
| FV1206-1 | .126 (3.20) | .063 (1.60) | .035 (0.89) | .024 (0.61) | .022 (0.56) | .011 (0.28) | .039 (0.99) | .024 (0.61) | .042 (1.07) | .123 (3.12) | -- | -- | -- | -- | .020 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm.01$; 3 Pl. $\pm.005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
 For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
 For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles

FV1206-1
FV1206-3




ILLUSTRATION 2

Applicable Case Styles

FV1206-4
FV1206-5
FV1206-6
FV1206-7
FV1206-9




ILLUSTRATION 3

Applicable Case Styles

FV1206-12
GE0805C-18
NL1008C-6
NL1008C-7
NL1008C-9
NL1008C-10

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel | |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8 | 4 | 7 | Small quantity standards (see note) | 20 |
| | | | | 50 |
| | | | | 100 |
| | | | | 200 |
| | | | | 500 |
| | | | 1000 | |
| | | | Standard | 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits ISO 9001 & ISO 14001 Certified

Mini-Circuits[®]


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|---------|---------------------------|----------|-----|------|
| OR | M87001 | NEW RELEASE | 05/20/03 | MMG | ABD |
| A | M87231 | CORRECTED DWG. | 05/28/03 | MMG | ABD |
| B | M91636 | ADDED "pn" PIN CONNECTION | 04/07/04 | AV | ABD |
| C | M102713 | ADDED "...WITH SMOBC" | 01/16/06 | GF | IL |

**SUGGESTED MOUNTING CONFIGURATION
FOR FV1206-1 CASE STYLE, "pb/pn" PIN CONNECTIONS**




NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|--|----------|--------------|
| DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ± | DRAWN | MMG 05/14/03 |
| | CHECKED | AV 05/19/03 |
| | APPROVED | ABD 05/20/03 |



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235



PL, pb/pn, FV1206-1, QCN/BDCN, TB-255

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

| | | | |
|------------------|---------------------|--------------------------|-----------|
| SIZE A | CODE IDENT 15542 | DRAWING NO: 98-PL-131 | REV: C |
| FILE: 98PL131 | SCALE: 10:1 | SHEET: 1 OF 1 | |

Evaluation Board and Circuit


For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|----------------------------|---|--|
| Operating Temperature | -55° to 100°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |