

Ceramic


Bandpass Filter

BFCN-5540+

50Ω 4620 to 6640 MHz

The Big Deal

- LTCC construction
- Temperature stable from -55 to +100°C
- Small size (0.12 x .06 X .03")



CASE STYLE: FV1206-4

Product Overview

The BFCN-5540+ LTCC bandpass filter covers the 4620 to 6640 MHz passband with 1.2 dB passband insertion loss, 22 dB lower stopband rejection, and 30 dB upper stopband rejection. This model handles up to 1W RF input power and provides a wide operating temperature range from -55 to +100°C. Utilizing LTCC construction, the filter achieves excellent repeatability of performance and comes in a tiny 1206 ceramic package with wraparound terminations, minimizing performance variations due to parasitics and saving space in dense PCB layouts.

Key Features


Feature	Advantages
LTCC Construction	Provides a rugged package well suited for tough environments such as high humidity and temperature extremes.
Tiny size (0.12 x .06 x .03")	Saves space in dense circuit boards and minimizes the effects of parasitics.
Wrap-around terminations	Provides excellent solderability and easy visual inspection
Wide operating temperature range, -55 to +100°C	Enables reliable performance in extreme environments

Ceramic

Bandpass Filter

50Ω 4620 to 6640 MHz

BFCN-5540+



Generic photo used for illustration purposes only

CASE STYLE: FV1206-4

Features

- Small size
- Temperature stable
- LTCC construction

Applications

- Harmonic Rejection
- Transmitters / Receivers
- Aviation
- Communications
- W-LAN

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500, 1000, 3000

Electrical Specifications^(1,2) at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Center Frequency	—	—	5540	—	MHz	
	Insertion Loss	F1-F2	4620-6640	—	1.2	4	dB
	VSWR	F1-F2	4620-6640	—	2.1	—	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-3470	17	22	—	dB
	VSWR	DC-F3	DC-3470	—	25	—	:1
Stop Band, Upper	Insertion Loss	F4-F5	8060-8820	13	30	—	dB
		F5-F6	8820-10990	—	17	—	dB
	VSWR	F4-F6	8060-10990	—	25	—	:1

1. Measured on Mini-Circuits Characterization Test Board TB-824+.

2. This filter is not intended for use as a DC Blocking circuit element. In Application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port.

Maximum Ratings


Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
RF Power Input*	1W at 25°C

*Passband rating, derate linearly to 0.25W at 100°C ambient
Permanent damage may occur if any of these limits are exceeded.


Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1000	36.33	65.08
2000	25.57	46.87
3400	37.28	39.50
4600	1.39	1.58
5000	1.48	1.95
6600	2.33	2.10
7000	3.54	1.62
7500	16.69	9.78
8000	38.25	15.07
8600	45.83	14.11
9000	35.68	14.34
9500	30.89	17.30
10000	29.47	22.09
10900	40.64	27.46
11000	38.85	26.92


Specification Definition



Functional Schematic




Top View




Pad Connections

Input	1
Output	3
Ground	2,4

BFCN-5540+
INSERTION LOSS



BFCN-5540+
VSWR



Mini-Circuits


www.minicircuits.com P.O. Box 250189, Broomfield, NY 11238-0089 (718) 954-8900 sales@minicircuits.com

REV. B
ECO-023234
BFCN-5540+
241004

Bandpass Filter

BFCN-5540+

Outline Drawing



Pad Connections


Input	1
Output	3
Ground	2,4

Product Marking: F6


Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J
.126	.063	.037	.026	.075	.012	.182	.104	.069
3.20	1.60	0.94	0.66	1.91	0.30	4.62	2.64	1.75
K	L	M	N	P	Q	R	wt	
.119	.041	.039	.013	.024	.020	.039	grams	
3.02	1.04	0.99	0.33	0.61	0.51	0.99	.020	

PCB Land Pattern



Demo Board MCL P/N: TB-824+ Suggested PCB Layout (PL-454)



NOTES:




- TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .0066"±.0007"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- Legend:
- Light blue shaded area: DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
 - Dark blue shaded area: DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

- NOTES:
- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 - The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html


Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
1000	36.33	0.27
1500	29.96	0.33
2000	25.57	0.37
2500	22.86	0.40
3000	23.40	0.42
3470	38.96	0.45
3500	32.97	0.47
4000	9.64	1.41
4000	9.64	1.41
4200	5.16	3.20
4400	2.40	7.38
4600	1.39	13.00
4620	1.39	13.00
4700	1.30	13.15
4800	1.32	11.88
4900	1.40	10.68
5000	1.48	9.87
5100	1.55	9.37
5200	1.61	9.14
5300	1.64	9.06
5400	1.67	9.07
5500	1.69	9.13
5540	1.70	9.14
5600	1.73	9.14
5700	1.76	9.08
5800	1.82	8.91
5900	1.88	8.68
6000	1.96	8.41
6100	2.05	8.15
6200	2.13	7.96
6300	2.20	7.87
6400	2.26	7.97
6500	2.30	8.31
6600	2.33	9.01
6640	2.34	9.26
6700	2.38	10.31
6800	2.50	12.51
6900	2.81	14.94
7000	3.54	12.55
7200	7.09	5.00
7400	13.17	2.31
7600	20.42	1.49
7800	28.58	1.23
7900	33.17	1.18
8000	38.25	1.15
8060	38.25	1.15
8200	49.77	1.16
8400	58.63	1.20
8600	45.83	1.23
8800	39.18	1.24
8900	37.13	1.23
9000	35.68	1.21
9100	34.47	1.18
9200	33.37	1.14
9300	32.43	1.10
9400	31.58	1.05
9500	30.89	1.01
9700	29.99	0.91
9800	29.73	0.87
9900	29.54	0.83
10000	29.47	0.79
10100	29.50	0.75
10200	29.66	0.71
10300	29.94	0.69
10400	30.39	0.66
10500	31.07	0.64
10600	32.14	0.63
10700	33.79	0.63
10800	36.53	0.62
10900	40.64	0.63
11000	38.85	0.65


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	L	M
FV1206-4	.126 (3.20)	.063 (1.60)	.037 (0.94)	.026 (0.66)	.075 (1.91)	.012 (0.30)	.182 (4.62)	.104 (2.64)	.069 (1.75)	.119 (3.02)	.041 (1.04)	.039 (0.99)

CASE #	N	P	Q	R	WT. GRAM
FV1206-4	.013 (0.33)	.024 (0.61)	.020 (0.51)	.039 (0.99)	.020

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
 For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
 For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles
FV1206-1 FV1206-3




ILLUSTRATION 2

Applicable Case Styles
FV1206-4 FV1206-5 FV1206-6 FV1206-7 FV1206-9




ILLUSTRATION 3

Applicable Case Styles
FV1206-12 GE0805C-18 NL1008C-6 NL1008C-7 NL1008C-9 NL1008C-10

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
			1000	
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits ISO 9001 & ISO 14001 Certified

Mini-Circuits[®]


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M152168	NEW RELEASE	07/31/15	ITG	AVB

SUGGESTED MOUNTING CONFIGURATION
FOR FV1206-4 CASE STYLE, "04FL01" PIN CODE



NOTES:

- TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.0066 \pm .0007$ ". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	ITG	07/30/15
	CHECKED	GF	07/31/15
	APPROVED	AVB	07/31/15



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 04FL01, FV1206-4, TB-824+

Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-454	REV: OR
FILE: 98PL454	SCALE: 16:1	SHEET: 1 OF 1	

Evaluation Board and Circuit



Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.0066 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A