

Ceramic

Bandpass Filter

BFHK-2582+

50Ω 24.25 to 27.50 GHz

The Big Deal

- 5G n258 bandpass filter
- Low Insertion Loss – Mid band 2.0dB typical
- Pick and place standard case style
- Small size 4.5mm x 3.2mm
- High quality distributed filter topology



CASE STYLE: NM1812C-2

Product Overview

The BFHK-2582+ LTCC Bandpass Filter covers the 5G n258 band. This corresponds to a passband of 24.25 to 27.5 GHz, with as low as 2dB passband loss, and up to 58dB stopband rejection. This model handles up to 1W RF input power and provides a wide operating temperature range from -55 to +125°C. Utilizing a proprietary LTCC material system and a distributed filter topology, this filter is able to achieve repeatable performance on a lot to lot basis, up to mmWave frequencies.

Key Features

Feature	Advantages
5G n258 band	Designed for 5G Telecommunications, n258 band, 24.25 - 27.50 GHz
Proprietary mmWave compatible LTCC material system	Low loss and repeatable performance on a lot to lot basis up to mmWave frequencies.
Cost effective	LTCC is scalable technology that is cost effective due to ease of production in high quantities.
Small size (4.5mm x 3.2mm)	Allows for high layout density of circuit boards, while minimizing effects of parasitics.



Ceramic

Bandpass Filter

50Ω 24.25 to 27.50 GHz

Features

- Small size
- Temperature stable
- Hermetically sealed
- LTCC construction

Applications

- 5G Telecommunications

BFHK-2582+



Generic photo used for illustration purposes only

CASE STYLE: NM1812C-2


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
RF Power Input	1W at 25°C


Permanent damage may occur if any of these limits are exceeded.



Pad Connections

Input	1
Output	2
Ground	3

Functional Schematic



Electrical Specifications¹ at 25°C





Parameter	F#	Frequency (GHz)	Min.	Typ.	Max.	Unit
Center Frequency	—			25.8		MHz
Pass Band	F1-F2	24.25 - 24.56	—	4	—	
		24.56 - 26.45	—	2	4.5	dB
		26.45 - 27.5	—	4	—	
Stop Band, Lower	DC-F3	DC - 9	45	58	—	
		9 - 21	34	40	—	dB
		21 - 21.7	—	40	—	
Stop Band, Upper	F4-F5	29.43 - 33	—	30	—	
		33 - 35.4	21	30	—	dB
		35.4 - 46	—	25	—	

1. Measured on Mini-Circuits Characterization Test Board TB-BFHK-2582C+ with feedline losses removed by normalization of S12 and S21 traces to measurement of TB thru-line.

Typical Performance Data at 25°C

Frequency (GHz)	Insertion Loss (dB)	Return Loss (dB)
1	76.49	0.38
5	63.57	1.12
10	56.27	1.26
15	47.15	1.51
20	39.84	1.86
23	14.86	2.70
24	2.32	12.94
25	1.46	26.07
26	1.64	14.78
27	2.54	11.86
28	8.70	5.33
30	38.18	2.42
35	40.95	2.58
40	39.07	2.56
45	41.01	2.57
50	10.66	4.74

Specification Definition




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
ECO-005291
BFHK-2582+
WY/CP/AM
201209
Page 2 of 3

Bandpass Filter

BFHK-2582+

Outline Drawing




Product Marking: F415

Pad Connections

Input	1
Output	2
Ground	3

Demo Board MCL P/N: TB-BFHK-2582C+ Suggested PCB Layout (PL-677)



- NOTES:**
- TRACE WIDTH AND GAP ARE SHOWN FOR MEGTRON7 WITH DIELECTRIC THICKNESS: .0079±.001"; COPPER: HVLP/HVLP.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Additional Notes




- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data


FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	53.79	0.01
500	82.01	0.29
1000	76.49	0.38
2000	72.06	0.33
4000	63.57	0.50
6000	60.71	0.88
8000	60.85	0.90
10000	56.27	1.26
12000	51.65	1.39
14000	49.14	1.29
16000	43.63	1.87
18000	41.98	1.52
20000	39.84	1.86
21700	53.55	2.26
22000	42.83	2.30
24000	2.32	12.94
24100	2.28	11.68
24200	2.21	11.39
24250	2.17	11.47
24300	2.12	11.80
24350	2.06	12.10
24400	2.00	12.53
24450	1.94	13.23
24500	1.86	13.94
24550	1.81	14.78
24560	1.79	14.97
25000	1.46	26.07
25200	1.43	21.47
25400	1.42	19.49
25600	1.44	18.64
25800	1.49	17.15
26000	1.64	14.78
26050	1.68	14.32
26100	1.74	13.64
26150	1.80	13.02
26200	1.85	12.67
26250	1.92	12.16
26300	1.98	11.66
26350	2.05	11.47
26400	2.11	11.08
26450	2.18	10.73
26500	2.23	10.68
26600	2.34	10.30
26700	2.42	10.43
26800	2.48	10.58
26900	2.52	10.88
27000	2.54	11.86
27100	2.55	12.82
27200	2.57	14.40
27300	2.66	16.25
27400	2.87	16.29
27500	3.24	14.47
28000	8.70	5.33
29000	26.16	3.12
29430	32.68	2.86
30000	38.18	2.42
31000	38.68	2.46
32000	44.43	2.67
33000	38.27	3.08
34000	38.11	2.86
35000	40.95	2.58
35400	43.16	2.51
36000	44.59	2.49
38000	32.82	2.99
40000	39.07	2.56
42000	37.50	2.67
44000	38.74	3.60
46000	49.95	2.87
48000	25.72	4.29
50000	10.66	4.74

Typical Performance Curves



Outline Dimensions

NM1812C-2



Weight: .064 grams.

Dimensions are in inches (mm). Tolerances: 2 Pl.±.01; 3 Pl. ±.005

Notes:

1. Case material: Ceramic.
2. Termination Finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin Plate over Nickel plate. All models, (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-003081	NEW RELEASE	06/24/20	ITG	WY
A	ECO-003526	UPDATED PATTERN	08/03/20	GF	WY

SUGGESTED MOUNTING CONFIGURATION FOR NM1812C-2 CASE STYLE




NOTES:

- TRACE WIDTH AND GAP ARE SHOWN FOR MEGTRON7 WITH DIELECTRIC THICKNESS: $.0079 \pm .001$ "; COPPER: HVLP/HVLP.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS \pm 3 PL DECIMALS \pm .005ANGLES \pm FRACTIONS \pm

DRAWN

ITG

06/24/20

CHECKED

GF

06/24/20

APPROVED

WY

06/24/20

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, NM1812C-2, TB-1135+

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-677


REV:
A

FILE: 98PL677



SCALE: 10:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-BFHK-2582+



Schematic Diagram

1. 50 Ohm 1.85 mm Female end launch connectors.
2. PCB Material: Megtron 7 R5785(N) or equivalent, Dielectric Constant=3.6 Thickness=.008 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Thermal Cycling	-55 to 125°C, 100 cycles, Dwell Time 15 minutes.	MIL-STD-202, Method 107, Condition A-3
Mechanical Shock	50g, 11ms half-sine, 18 shocks applied each to 3 axes	MIL-STD-202 Method 213, Condition A
Vibration	10-2000Hz sine, 20g, 12 cycles applied each to 3 axes	MIL-STD-202, Method 204, Condition D
Constant Acceleration	30Kg, Y1 Direction	MIL-STD-883, Method 2001, Condition E
Humidity	85°C, 90-95% Relative Humidity, 250hours	
Solderability	10X / 30X Magnification	J-STD-002C Test S, J-STD-002C Test S1
High Temp Storage	125°C, 250 hours	