LTCC SURFACE MOUNT

Band Pass Filter

BFHK-1432+

50Ω 14 to 14.5 GHz

THE BIG DEAL

- Ultra-High Stopband Rejection, 65 dB Typ.
- Surface mountable pick and place standard case style
- Standard small 1812 (4.5x3.2 mm) case style
- High quality distributed filter topology
- Wide rejection band
- Shielded construction preventing filter from de-tuning
- Reduced footprint area by employing LGA (Land Grid Array)
- Suited for very high-volume production




Generic photo used for illustration purposes only

APPLICATIONS

- Test & Measurement Equipment
- Satellite Communications
- Aerospace and Defense Signal Conditioning

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' BFHK-1432+ Band Pass Filter delivers precision filtering for Ku-band uplinks in a compact, rugged ceramic package. Leveraging proprietary materials science and a distributed design topology ensures highly repeatable performance for mission-critical operation. The filter provides a typical passband loss of 3.0 dB from 14 to 14.5 GHz with exceptional stopband rejection of 60 dB from 0.1 to 5 GHz and 65 dB through 27.5 GHz, greatly suppressing interference and harmonics. The BFHK-1432+ is rated for 6.3 W of RF input power and operates over a wide temperature range of -55°C to +125°C, combining reliability and high performance for demanding SATCOM (VSAT), defense and test environments.

ELECTRICAL SPECIFICATIONS[1,2,3] AT +25°C, Z_0 = 50Ω

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency[4]	—	—	—	14.3	—	GHz
	Insertion Loss	F4-F5	14 – 14.5	—	3	4.5	dB
	Return Loss	F4-F5	14 – 14.5	—	9	—	dB
Stopband, Lower	Rejection	DC-F1	0.1 – 5	53	60	—	dB
		F1-F2	5 – 10	41	50	—	
		F2-F3	10 – 12.75	33	40	—	
Stopband, Upper	Rejection	F6-F7	15.7 – 16	30	35	—	dB
		F7-F8	16 – 18.5	45	50	—	
		F8-F9	18.5 – 27.5	55	65	—	
		F9-F10	27.5 – 31	50	60	—	


1. Tested in Evaluation Board P/N TB-BFHK-1432C+.
2. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.
3. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.
4. Typical variation ± 1.5%

ABSOLUTE MAXIMUM RATINGS[5]

Operating Temperature	-55 °C to +125 °C
Storage Temperature	-55 °C to +125 °C
Input Power[6]	6.3 W

5. Permanent damage may occur if any of these limits are exceeded.
6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 1.9 W at +125°C.

TYPICAL FREQUENCY RESPONSE



REV. OR
ECO-027828
BFHK-1432+
MCL NY
251201


Band Pass Filter

BFHK-1432+


50Ω 14 to 14.5 GHz

TYPICAL PERFORMANCE GRAPHS


INSERTION LOSS




RETURN LOSS



INSERTION LOSS (PASSBAND)



RETURN LOSS (PASSBAND)



LTCC SURFACE MOUNT

Band Pass Filter

BFHK-1432+

50Ω 14 to 14.5 GHz

FUNCTIONAL DIAGRAM





Figure 1. BFHK-1432+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1[2]	1	Connects to RF Input Port
RF2[2]	2	Connects to RF Output Port
GROUND	3	Connects to Ground on PCB, (See drawing PL-730)

CASE STYLE DRAWING




Weight: .126 grams
Dimensions are in inches [mm]. Tolerances: 2 Pl.±.01; 3 Pl. ±.005

PRODUCT MARKING*: F605

*Marking may contain other features or characters for internal lot control.

SUGGESTED PCB LAYOUT: PL-730



NOTES:
1. PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
2. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
3. COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK




Figure 2. Suggested PCB Layout

Band Pass Filter

BFHK-1432+

50Ω 14 to 14.5 GHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD CLICK HERE

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	NM1812C-3 Lead Finish: Tin over Nickel Plating
RoHS/REACH Status	Compliant
Tape and Reel	F77
Suggested Layout for PCB Design	PL-730
Evaluation Board	TB-BFHK-1432C+ Gerber File
Environmental Rating	ENV06T12

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

LTCC Bandpass Filter BFHK-1432+


Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)			RETURN LOSS (dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
0.1	100.03	98.14	88.47	0.04	0.04	0.07
0.5	84.19	84.07	84.74	0.12	0.12	0.17
1.0	78.62	78.24	77.79	0.12	0.13	0.17
1.5	74.47	74.27	74.53	0.08	0.07	0.12
2.0	71.67	71.37	71.75	-0.01	-0.01	0.02
2.5	69.99	70.12	69.39	-0.07	-0.08	-0.05
3.0	68.00	68.25	68.18	-0.09	-0.10	-0.06
3.5	66.76	66.75	66.72	-0.05	-0.06	-0.01
4.0	65.56	65.69	65.61	0.03	0.03	0.08
4.5	64.47	64.49	64.42	0.13	0.13	0.17
5.0	63.47	63.45	63.38	0.18	0.18	0.23
5.5	62.39	62.14	62.20	0.18	0.17	0.25
6.0	61.03	60.96	61.01	0.14	0.13	0.22
6.5	59.94	59.84	59.82	0.09	0.07	0.14
7.0	58.82	58.61	58.55	0.05	0.03	0.09
7.5	57.59	57.56	57.41	0.01	-0.01	0.08
8.0	56.51	56.40	56.31	-0.03	-0.05	0.08
8.5	55.37	55.14	55.17	-0.05	-0.06	0.05
9.0	54.07	53.97	53.94	-0.03	-0.05	0.03
9.5	52.89	52.72	52.69	-0.04	-0.04	0.03
10.0	51.53	51.34	51.31	-0.08	-0.05	0.04
10.5	50.13	49.90	49.79	-0.06	-0.02	0.12
11.0	48.63	48.37	48.14	0.06	0.09	0.19
11.5	47.00	46.74	46.42	0.18	0.20	0.20
12.0	45.34	45.08	44.78	0.18	0.17	0.17
12.5	44.32	44.39	44.87	0.07	0.07	0.17
13.0	55.14	53.93	41.02	0.09	0.14	0.26
13.2	41.00	34.68	27.52	0.18	0.27	0.41
13.4	27.60	22.40	15.39	0.35	0.55	1.01
13.6	15.43	10.03	4.77	0.85	1.88	5.60
13.8	4.21	2.91	2.64	5.24	8.33	9.63
14.0	2.13	1.99	1.91	9.19	11.66	19.03
14.1	1.75	1.67	1.79	11.72	16.82	24.68
14.2	1.45	1.53	1.78	17.29	23.59	23.02
14.3	1.34	1.51	1.82	24.09	23.40	27.29
14.4	1.33	1.53	1.96	23.04	26.75	21.75
14.5	1.34	1.62	2.24	27.13	24.77	15.73
14.6	1.43	1.85	2.67	25.08	17.02	13.92
14.8	1.94	2.98	7.96	14.84	11.29	3.62
15.0	5.96	11.76	19.82	4.27	1.93	1.09
15.2	17.84	23.43	30.62	0.97	0.77	0.70
15.4	28.77	33.82	40.87	0.53	0.50	0.56
15.5	33.85	38.91	46.40	0.44	0.43	0.51
16.0	70.60	62.84	58.47	0.27	0.28	0.31
16.5	56.72	56.66	56.94	0.14	0.16	0.13
17.0	57.91	58.41	59.14	-0.08	-0.07	-0.02
17.5	60.44	60.93	61.64	-0.26	-0.24	-0.10
18.0	62.99	63.57	64.37	-0.23	-0.22	-0.08
18.5	65.76	65.98	66.90	-0.05	-0.05	0.03
19.0	68.10	68.98	69.24	0.10	0.10	0.15
19.5	70.32	70.34	71.54	0.18	0.18	0.30
20.0	72.47	72.38	72.89	0.17	0.18	0.39
20.5	72.62	74.03	74.39	0.18	0.21	0.45
21.0	74.89	74.93	75.25	0.22	0.27	0.46
21.5	75.19	74.51	75.91	0.28	0.31	0.43
22.0	75.17	75.67	75.34	0.28	0.28	0.39
22.5	75.32	74.11	75.90	0.21	0.18	0.32
23.0	76.26	75.39	74.20	0.09	0.05	0.23
23.5	75.13	75.16	74.44	-0.02	-0.02	0.17
24.0	74.85	75.18	75.00	-0.06	-0.05	0.14
24.5	75.33	75.74	75.69	-0.04	-0.03	0.13
25.0	74.47	74.47	75.11	-0.01	-0.03	0.12
25.5	74.75	74.15	74.24	0.03	-0.01	0.12
26.0	74.46	74.13	73.66	0.07	0.03	0.14
26.5	73.65	74.04	73.69	0.10	0.08	0.13
27.0	74.59	72.65	73.56	0.16	0.18	0.18
27.5	74.50	72.64	73.64	0.17	0.23	0.26
28.0	75.78	72.46	71.55	0.17	0.21	0.37
28.5	70.68	72.81	71.27	0.14	0.16	0.39
29.0	71.12	74.40	71.41	0.09	0.09	0.31
29.5	70.30	69.33	70.93	0.04	0.04	0.24
30.0	69.59	69.03	69.53	0.02	0.02	0.23
30.5	69.16	67.48	66.18	0.03	0.07	0.27
31.0	66.38	65.75	63.75	0.11	0.16	0.22


LTCC Bandpass Filter BFHK-1432+

Typical Performance Data


INSERTION LOSS




RETURN LOSS



INSERTION LOSS (PASSBAND)




RETURN LOSS (PASSBAND)



Case Style NM

Outline Dimensions

NM1812C-3



Weight: .126 grams.

Dimensions are in inches [mm]. Tolerances: 2 Pl.±.01; 3 Pl. ±.005 Inches


Notes:

1. Case material: Ceramic.
2. Termination Finish: **as shown below or indicated on Data Sheet.**
   For RoHS Case Styles: Tin Plate over Nickel plate. All models, (+) suffix.


Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED
ALL NEW minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com
RF/IF MICROWAVE COMPONENTS

This document and its contents are the property of Mini-Circuits

Tape & Reel Packaging TR-F77



Note: The shape of the pocket may differ



Note: The location and shape of the metallization may differ

Applicable Case Styles
GU1604, GU1804, GU2644, TT1618-2

Applicable Case Styles
MZ4532C, NM1812C, NM1812C-1, NM1812C-2, NM1812C-3, NM1812C-5, NM1812C-6, NM3237 NM1812C-9

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
		13	Standard	2000

Note: Please Consult individual model data sheet to determine device per reel availability.


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.


THIRD ANGLE PROJECTION




REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-013254	NEW RELEASE	05/16/22	ITG	IL
A	ECO-015587	UPDATED STACK-UP DIAGRAM	11/01/22	ITG	IL
B	ECO-020890	ADDED DIMENSIONS	02/16/24	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR NM1812C-3 CASE STYLE

TOP VIEW



STACK-UP DIAGRAM



1. TOTAL FINISHED THICKNESS 0.0228±.004.
2. B-VIA PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 2.
3. PTH PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 4.
4. INDICATED PLUGGED PTH's ARE PLUGGED WITH EPOXY AND CAPPED WITH COPPER FROM TOP SIDE.
5. LAYER 4 IS CONTINUOUS GROUND PLANE.

NOTES:

1. PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
2. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
3. COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	05/16/22
TOLERANCES ON:	CHECKED	GF	05/16/22
2 PL DECIMALS ±	APPROVED	IL	05/16/22
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, NM1812C-3, TB-1239


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-730	B

FILE:	SCALE:	SHEET:
98PL730	8:1	1 OF 2

LAYER 2, B-VIA & PTH



LAYER 3 & PTH



Mini-Circuits

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA2.DWG REV:A DATE: 01/12/94

ALL DIMENSIONS ARE IN INCHES EXCEPT OTHERWISE SPECIFIED


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-730	B

FILE:	SCALE:	SHEET:
98PL730	8:1	2 OF 2


Evaluation Board and Circuit



TB-BFHK-1432C+



Schematic Diagram



STACK-UP DIAGRAM

Notes:

1. 1.85 mm Female End Launch Connector.
2. PCB Material: Megtron 6 R5775(N).
   Dielectric Constant=3.6.
3. Total finished thickness .023".

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV06T12

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Thermal Cycling	-55 to 125°C, 100 cycles, Dwell Time 15 minutes.	MIL-STD-202, Method 107, Condition A-3
Humidity	85°C, 90-95% Relative Humidity, 250hours	
Solderability	10X / 30X Magnification	J-STD-002C Test S, J-STD-002C Test S1
High Temp Storage	125°C, 250 hours	
Bend Test	1mm, deflection for 5 seconds Span of bending: 2.75"	--

This document and its contents are the property of Mini-Circuits.