

Ceramic Bandpass Filter

BFHK-2582+

50Ω 24.25 to 27.50 GHz

The Big Deal

- 5G n258 bandpass filter
- Low Insertion Loss – Mid band 2.0dB typical
- Pick and place standard case style
- Small size 4.5mm x 3.2mm
- High quality distributed filter topology



CASE STYLE: NM1812C-2

Product Overview

The BFHK-2582+ LTCC Bandpass Filter covers the 5G n258 band. This corresponds to a passband of 24.25 to 27.5 GHz, with as low as 2dB passband loss, and up to 58dB stopband rejection. This model handles up to 1W RF input power and provides a wide operating temperature range from -55 to +125°C. Utilizing a proprietary LTCC material system and a distributed filter topology, this filter is able to achieve repeatable performance on a lot to lot basis, up to mmWave frequencies.

Key Features

| Feature | Advantages |
|--|--|
| 5G n258 band | Designed for 5G Telecommunications, n258 band, 24.25 - 27.50 GHz |
| Proprietary mmWave compatible LTCC material system | Low loss and repeatable performance on a lot to lot basis up to mmWave frequencies. |
| Cost effective | LTCC is scalable technology that is cost effective due to ease of production in high quantities. |
| Small size (4.5mm x 3.2mm) | Allows for high layout density of circuit boards, while minimizing effects of parasitics. |



Ceramic Bandpass Filter

50Ω 24.25 to 27.50 GHz

Features

- Small size
- Temperature stable
- Hermetically sealed
- LTCC construction

Applications

- 5G Telecommunications

BFHK-2582+



Generic photo used for illustration purposes only

CASE STYLE: NM1812C-2

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Available Tape and Reel at no extra cost

| Reel Size | Devices/Reel |
|-----------|-----------------------------------|
| 7" | 20, 50, 100, 200, 500, 1000, 3000 |

Maximum Ratings

| | |
|-----------------------|-----------------|
| Operating Temperature | -55°C to +125°C |
| Storage Temperature | -55°C to +125°C |
| RF Power Input | 1W at 25°C |


Permanent damage may occur if any of these limits are exceeded.



Pad Connections

| | |
|--------|---|
| Input | 1 |
| Output | 2 |
| Ground | 3 |

Functional Schematic



Electrical Specifications¹ at 25°C





| Parameter | F# | Frequency (GHz) | Min. | Typ. | Max. | Unit |
|------------------|----------------|-----------------|---------------|------|------|------|
| Center Frequency | — | | | 25.8 | | MHz |
| Pass Band | Insertion Loss | F1-F2 | 24.25 - 24.56 | — | 4 | — |
| | | | 24.56 - 26.45 | — | 2 | 4.5 |
| | | | 26.45 - 27.5 | — | 4 | — |
| | Return Loss | F1-F2 | 24.25 - 27.5 | — | 10 | — |
| Stop Band, Lower | Insertion Loss | DC - 9 | 45 | 58 | — | — |
| | | | 9 - 21 | 34 | 40 | — |
| | | | 21 - 21.7 | — | 40 | — |
| Stop Band, Upper | Insertion Loss | F4-F5 | 29.43 - 33 | — | 30 | — |
| | | | 33 - 35.4 | 21 | 30 | — |
| | | | 35.4 - 46 | — | 25 | — |

1. Measured on Mini-Circuits Characterization Test Board TB-BFHK-2582C+ with feedline losses removed by normalization of S12 and S21 traces to measurement of TB thru-line.


Typical Performance Data at 25°C

| Frequency (GHz) | Insertion Loss (dB) | Return Loss (dB) |
|-----------------|---------------------|------------------|
| 1 | 76.49 | 0.38 |
| 5 | 63.57 | 1.12 |
| 10 | 56.27 | 1.26 |
| 15 | 47.15 | 1.51 |
| 20 | 39.84 | 1.86 |
| 23 | 14.86 | 2.70 |
| 24 | 2.32 | 12.94 |
| 25 | 1.46 | 26.07 |
| 26 | 1.64 | 14.78 |
| 27 | 2.54 | 11.86 |
| 28 | 8.70 | 5.33 |
| 30 | 38.18 | 2.42 |
| 35 | 40.95 | 2.58 |
| 40 | 39.07 | 2.56 |
| 45 | 41.01 | 2.57 |
| 50 | 10.66 | 4.74 |

Specification Definition



Outline Drawing



METALLIZATION


Weight: .064 grams.
Dimensions are in inches [mm]

Product Marking: F415

Pad Connections

| | |
|--------|---|
| Input | 1 |
| Output | 2 |
| Ground | 3 |

Demo Board MCL P/N: TB-BFHK-2582C+ Suggested PCB Layout (PL-677)



NOTES:

- TRACE WIDTH AND GAP ARE SHOWN FOR MEGTRON7 WITH DIELECTRIC THICKNESS: .0079±.001"; COPPER: HVLP/HVLP. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.




Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data


| FREQUENCY (MHz) | INSERTION LOSS (dB) | RETURN LOSS (dB) |
|--------------------|------------------------|---------------------|
| 10 | 53.79 | 0.01 |
| 500 | 82.01 | 0.29 |
| 1000 | 76.49 | 0.38 |
| 2000 | 72.06 | 0.33 |
| 4000 | 63.57 | 0.50 |
| 6000 | 60.71 | 0.88 |
| 8000 | 60.85 | 0.90 |
| 10000 | 56.27 | 1.26 |
| 12000 | 51.65 | 1.39 |
| 14000 | 49.14 | 1.29 |
| 16000 | 43.63 | 1.87 |
| 18000 | 41.98 | 1.52 |
| 20000 | 39.84 | 1.86 |
| 21700 | 53.55 | 2.26 |
| 22000 | 42.83 | 2.30 |
| 24000 | 2.32 | 12.94 |
| 24100 | 2.28 | 11.68 |
| 24200 | 2.21 | 11.39 |
| 24250 | 2.17 | 11.47 |
| 24300 | 2.12 | 11.80 |
| 24350 | 2.06 | 12.10 |
| 24400 | 2.00 | 12.53 |
| 24450 | 1.94 | 13.23 |
| 24500 | 1.86 | 13.94 |
| 24550 | 1.81 | 14.78 |
| 24560 | 1.79 | 14.97 |
| 25000 | 1.46 | 26.07 |
| 25200 | 1.43 | 21.47 |
| 25400 | 1.42 | 19.49 |
| 25600 | 1.44 | 18.64 |
| 25800 | 1.49 | 17.15 |
| 26000 | 1.64 | 14.78 |
| 26050 | 1.68 | 14.32 |
| 26100 | 1.74 | 13.64 |
| 26150 | 1.80 | 13.02 |
| 26200 | 1.85 | 12.67 |
| 26250 | 1.92 | 12.16 |
| 26300 | 1.98 | 11.66 |
| 26350 | 2.05 | 11.47 |
| 26400 | 2.11 | 11.08 |
| 26450 | 2.18 | 10.73 |
| 26500 | 2.23 | 10.68 |
| 26600 | 2.34 | 10.30 |
| 26700 | 2.42 | 10.43 |
| 26800 | 2.48 | 10.58 |
| 26900 | 2.52 | 10.88 |
| 27000 | 2.54 | 11.86 |
| 27100 | 2.55 | 12.82 |
| 27200 | 2.57 | 14.40 |
| 27300 | 2.66 | 16.25 |
| 27400 | 2.87 | 16.29 |
| 27500 | 3.24 | 14.47 |
| 28000 | 8.70 | 5.33 |
| 29000 | 26.16 | 3.12 |
| 29430 | 32.68 | 2.86 |
| 30000 | 38.18 | 2.42 |
| 31000 | 38.68 | 2.46 |
| 32000 | 44.43 | 2.67 |
| 33000 | 38.27 | 3.08 |
| 34000 | 38.11 | 2.86 |
| 35000 | 40.95 | 2.58 |
| 35400 | 43.16 | 2.51 |
| 36000 | 44.59 | 2.49 |
| 38000 | 32.82 | 2.99 |
| 40000 | 39.07 | 2.56 |
| 42000 | 37.50 | 2.67 |
| 44000 | 38.74 | 3.60 |
| 46000 | 49.95 | 2.87 |
| 48000 | 25.72 | 4.29 |
| 50000 | 10.66 | 4.74 |

Typical Performance Curves



Outline Dimensions

NM1812C-2



Weight: .064 grams.

Dimensions are in inches (mm). Tolerances: 2 Pl.±.01; 3 Pl. ±.005

Notes:

1. Case material: Ceramic.
2. Termination Finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin Plate over Nickel plate. All models, (+) suffix.

 **Mini-Circuits**[®]
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
 minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|------------|-----------------|----------|-----|------|
| OR | ECO-003081 | NEW RELEASE | 06/24/20 | ITG | WY |
| A | ECO-003526 | UPDATED PATTERN | 08/03/20 | GF | WY |
| | | | | | |

SUGGESTED MOUNTING CONFIGURATION FOR
NM1812C-2 CASE STYLE



NOTES:

- TRACE WIDTH AND GAP ARE SHOWN FOR MEGTRON7 WITH DIELECTRIC THICKNESS: $.0079 \pm .001$ "; COPPER: HVLP/HVLP.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|----------------------------|----------|----------|
| DIMENSIONS ARE IN INCHES | ITG | 06/24/20 |
| TOLERANCES ON: | GF | 06/24/20 |
| 2 PL DECIMALS ± | WY | 06/24/20 |
| 3 PL DECIMALS ± .005 | | |
| ANGLES ± | | |
| FRACTIONS ± | | |


Mini-Circuits[®] 13 Neptune Avenue
Brooklyn NY 11235

PL, NM1812C-2, TB-1135+


Mini-Circuits[®]
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

| | | | |
|------------------|---------------------|--------------------------|-----------|
| SIZE A | CODE IDENT 15542 | DRAWING NO: 98-PL-677 | REV: A |
| FILE: 98PL677 | SCALE: 10:1 | SHEET: 1 OF 1 | |

Evaluation Board and Circuit



TB-BFHK-2582+



Schematic Diagram

1. 50 Ohm 1.85 mm Female end launch connectors.
2. PCB Material: Megtron 7 R5785(N) or equivalent, Dielectric Constant=3.6 Thickness=.008 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|-----------------------|---|--|
| Operating Temperature | -55° to 125° C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 125° C Ambient Environment | Individual Model Data Sheet |
| Thermal Cycling | -55 to 125°C, 100 cycles, Dwell Time 15 minutes. | MIL-STD-202, Method 107, Condition A-3 |
| Mechanical Shock | 50g, 11ms half-sine, 18 shocks applied each to 3 axes | MIL-STD-202 Method 213, Condition A |
| Vibration | 10-2000Hz sine, 20g, 12 cycles applied each to 3 axes | MIL-STD-202, Method 204, Condition D |
| Constant Acceleration | 30Kg, Y1 Direction | MIL-STD-883, Method 2001, Condition E |
| Humidity | 85°C, 90-95% Relative Humidity, 250hours | |
| Solderability | 10X / 30X Magnification | J-STD-002C Test S, J-STD-002C Test S1 |
| High Temp Storage | 125°C, 250 hours | |