

# Coaxial Low Pass Filter

## BLP-15+

50Ω DC to 15 MHz

### Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input 0.5W max.

Permanent damage may occur if any of these limits are exceeded.

### Features

- rugged shielded case
- other standard and custom PLP models available with wide selection of fco

### Applications

- test equipment
- lab use
- transmitters/receivers
- military/hi-rel applications



Generic photo used for illustration purposes only

CASE STYLE: FF55

Connectors	Model
BNC	BLP-15+


### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)		VSWR (:1)	
		(loss > 20 dB)	(loss > 40 dB)	Passband Typ.	Stopband Typ.
DC-15	17	23-32	32-200	1.7	18


### Outline Drawing




### Outline Dimensions (inch/mm)

B	D	wt
.57	2.59	grams
14.47	65.79	40.0

### typical frequency response





### electrical schematic



### Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$	$\sigma$			
1.00	0.21	0.04	24.91	1.00	48.07
3.00	0.26	0.04	20.32	1.10	47.91
5.00	0.30	0.04	20.46	1.30	48.21
7.00	0.33	0.05	25.27	1.40	47.67
9.00	0.38	0.05	24.09	1.60	48.07
11.00	0.47	0.07	20.00	1.80	47.68
13.00	0.58	0.07	19.00	2.00	48.30
15.00	0.81	0.06	16.36	2.30	48.44
17.00	2.32	0.37	7.61	2.50	48.37
19.00	8.82	0.63	2.63	2.90	48.63
19.80	12.25	0.57	2.04	3.20	48.63
20.60	15.66	0.53	1.72	3.60	48.80
21.40	18.93	0.50	1.51	4.00	48.88
22.20	22.02	0.48	1.36	4.60	49.48
23.00	24.94	0.48	1.25	5.10	49.49
23.80	27.72	0.47	1.15	5.80	50.43
25.40	32.87	0.50	0.99	6.50	50.77
27.10	37.90	0.60	0.86	7.30	51.87
28.70	42.24	0.70	0.76	8.20	53.05
30.40	46.55	0.86	0.67	9.30	54.47
32.00	50.45	1.02	0.60	10.40	56.61
33.60	54.18	1.48	0.55	11.70	60.33
54.40	77.82	6.04	0.22	13.10	66.08
75.20	77.17	4.69	0.12	15.00	80.27
96.00	81.80	4.39	0.09	17.00	100.53
116.80	80.95	4.80	0.08	18.80	81.42
137.60	80.75	3.87	0.07	21.10	43.84
158.40	83.26	4.95	0.07	23.00	28.31
179.20	79.58	3.64	0.06	26.60	15.72
200.00	80.96	5.21	0.06	30.00	10.37



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Coaxial Low Pass Filter

# BLP-15+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.21	24.91	1.0	48.070
3.0	0.26	20.32	1.1	47.910
5.0	0.30	20.46	1.3	48.210
7.0	0.33	25.27	1.4	47.670
9.0	0.38	24.09	1.6	48.070
11.0	0.47	20.00	1.8	47.680
13.0	0.58	19.00	2.0	48.300
15.0	0.81	16.36	2.3	48.440
17.0	2.32	7.61	2.5	48.370
19.0	8.82	2.63	2.9	48.630
19.8	12.25	2.04	3.2	48.630
20.6	15.66	1.72	3.6	48.800
21.4	18.93	1.51	4.0	48.880
22.2	22.02	1.36	4.6	49.480
23.0	24.94	1.25	5.1	49.490
23.8	27.72	1.15	5.8	50.430
25.4	32.87	0.99	6.5	50.770
27.1	37.90	0.86	7.3	51.870
28.7	42.24	0.76	8.2	53.050
30.4	46.55	0.67	9.3	54.470
32.0	50.45	0.60	10.4	56.610
33.6	54.18	0.55	11.7	60.330
54.4	77.82	0.22	13.1	66.080
75.2	77.17	0.12	15.0	80.270
96.0	81.80	0.09	17.0	100.530
116.8	80.95	0.08	18.8	81.420
137.6	80.75	0.07	21.1	43.840
158.4	83.26	0.07	23.0	28.310
179.2	79.58	0.06	26.6	15.720
200.0	80.96	0.06	30.0	10.370

REV. X1  
BLP-15+  
060724  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661






The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Coaxial Low Pass Filter

## Typical Performance Curves

# BLP-15+



REV. X1  
BLP-15+  
060724  
Page 1 of 1




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



### Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF55	--	.57 (14.47)	--	2.59 (65.79)	--	40.0

Dimensions are in inches (mm). Tolerances: 2Pl. +.03/-.04; 3Pl. ± .015

#### Note:

1. Case material: Stainless steel.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

<b>Specification</b>	<b>Test/Inspection Condition</b>	<b>Reference/Spec</b>
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I