

Bandpass Filter

BPF-A730+

50Ω 670 to 795 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input*	0.5W at 25°C

*Passband rating, derate linearly to 0.25W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

Pin Connections

RF IN	1
RF OUT	8
GROUND	2-7,9-14

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
.365	1.360	.35	.100	.180	.140	.100	.100
9.27	34.54	8.89	2.54	4.57	3.56	2.54	2.54

J	K	L	M	N	P	Q	Wt.
.305	.150	.120	.275	.152	.405	1.400	grams
7.75	3.81	3.05	6.99	3.86	10.29	35.56	4.0

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-363+
Suggested PCB Layout(PL-227)



NOTES:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025" ± .002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Features

- High rejection
- Shielded case
- Aqueous washable

Applications

- Mobile TV (DVB)
- Harmonic rejection
- Transmitters/receivers



Generic photo used for illustration purposes only

CASE STYLE: HQ1157


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 5dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss > 40dB		Passband		Stopband
F _c	F ₁ - F ₂	F ₃	F ₄	F ₅	F ₆	Typ.	Max.	Typ.
730	670 - 795	610	910	575	1100 - 1800	1.5	2.3	20

Typical Frequency Response





Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
0.5	92.82	6220.49
100.0	82.20	1395.51
300.0	81.87	214.15
575.0	55.60	25.50
610.0	34.24	14.57
640.0	16.18	7.93
655.0	7.72	3.94
670.0	3.30	1.60
700.0	2.51	1.72
730.0	1.97	1.32
770.0	2.23	1.62
795.0	2.45	1.12
810.0	4.72	1.35
820.0	6.77	3.83
840.0	13.45	10.65
910.0	30.74	30.16
1100.0	50.00	42.90
1800.0	49.55	63.65



Surface Mount Band Pass Filter

BPF-A730+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
0.5	92.80	88.44	99.26	0.00	0.00	0.00	0.00	0.00	0.00
20	92.76	95.62	90.98	0.00	0.01	0.01	0.00	0.01	0.01
50	91.87	99.23	99.03	0.01	0.02	0.02	0.02	0.01	0.04
75	92.70	98.00	93.74	0.01	0.02	0.03	0.02	0.02	0.05
100	99.89	96.48	95.01	0.01	0.03	0.04	0.01	0.03	0.05
150	99.64	95.33	101.01	0.01	0.04	0.07	0.02	0.04	0.09
200	95.07	100.37	92.90	0.02	0.06	0.09	0.01	0.06	0.11
250	105.34	98.09	95.33	0.03	0.08	0.11	0.00	0.08	0.14
300	93.61	90.84	89.79	0.06	0.11	0.15	0.01	0.10	0.17
350	88.45	95.11	90.73	0.08	0.14	0.18	0.03	0.14	0.20
400	85.05	83.52	86.68	0.10	0.17	0.22	0.05	0.17	0.24
450	82.74	84.51	81.61	0.15	0.23	0.28	0.10	0.22	0.29
500	81.83	83.99	82.10	0.24	0.34	0.40	0.15	0.30	0.37
550	64.56	63.04	61.52	0.49	0.65	0.80	0.29	0.46	0.55
575	49.00	47.72	45.95	0.82	1.10	1.42	0.42	0.63	0.77
590	39.92	38.60	36.74	1.13	1.56	2.05	0.55	0.81	1.01
600	33.93	32.62	30.81	1.37	1.89	2.46	0.68	1.00	1.27
610	28.11	26.87	25.15	1.56	2.13	2.67	0.87	1.27	1.67
620	22.53	21.38	19.79	1.65	2.22	2.69	1.14	1.70	2.33
630	17.19	16.16	14.74	1.73	2.31	2.79	1.59	2.41	3.41
640	12.09	11.29	10.22	2.04	2.76	3.44	2.42	3.64	5.07
655	5.75	5.63	5.34	4.28	5.56	7.05	5.46	7.45	9.39
670	2.58	3.02	3.29	11.76	14.21	17.41	13.96	17.75	22.11
680	1.97	2.55	3.01	20.23	18.69	15.64	39.05	24.99	18.17
690	1.87	2.51	3.02	15.34	13.60	11.86	17.15	15.34	13.21
700	1.92	2.54	3.02	12.14	11.42	10.69	13.22	12.65	11.75
710	1.95	2.53	2.94	11.07	10.90	10.87	11.97	11.96	11.83
720	1.93	2.48	2.82	10.97	11.24	11.84	11.69	12.10	12.70
730	1.90	2.41	2.73	11.36	11.97	13.14	11.72	12.44	13.72
740	1.87	2.38	2.69	11.81	12.70	14.21	11.72	12.62	14.24
750	1.87	2.38	2.72	12.03	13.07	14.57	11.53	12.52	14.15
760	1.90	2.42	2.78	11.93	13.05	14.36	11.30	12.43	14.03
770	1.92	2.47	2.87	11.98	13.32	14.59	11.51	13.03	15.07
780	1.91	2.52	3.03	13.23	15.04	16.02	13.35	16.19	20.72
795	2.16	3.22	4.29	15.94	12.72	9.97	24.12	16.03	12.15
810	4.75	6.60	8.39	5.20	4.49	3.86	5.53	4.85	4.29
820	8.16	10.14	12.05	2.52	2.50	2.39	2.60	2.66	2.62
830	11.89	13.80	15.65	1.46	1.65	1.71	1.46	1.73	1.87
840	15.41	17.21	18.98	0.99	1.24	1.36	0.97	1.30	1.49
850	18.62	20.31	21.99	0.74	1.01	1.15	0.71	1.05	1.26
910	32.58	33.88	35.21	0.35	0.59	0.72	0.29	0.60	0.80
950	38.80	39.99	41.19	0.28	0.51	0.64	0.23	0.52	0.70
1000	44.69	45.77	46.86	0.25	0.46	0.58	0.19	0.47	0.65
1050	49.28	50.31	51.21	0.23	0.44	0.55	0.17	0.45	0.61
1100	52.91	53.94	54.78	0.23	0.43	0.54	0.17	0.44	0.59
1200	59.39	60.42	61.09	0.23	0.41	0.51	0.16	0.43	0.57
1300	64.31	65.41	66.51	0.23	0.40	0.49	0.15	0.42	0.56
1350	64.61	66.51	67.92	0.23	0.40	0.49	0.16	0.41	0.56
1400	61.82	63.27	64.21	0.24	0.40	0.49	0.15	0.40	0.56
1450	64.32	63.64	65.36	0.23	0.39	0.48	0.14	0.40	0.56
1500	71.27	69.52	72.53	0.23	0.39	0.48	0.14	0.39	0.56
1550	74.84	61.75	63.38	0.23	0.38	0.47	0.14	0.39	0.56
1600	60.35	60.91	58.34	0.23	0.38	0.46	0.13	0.39	0.56
1700	67.96	65.73	64.52	0.22	0.36	0.46	0.11	0.37	0.55
1800	60.04	55.28	53.85	0.21	0.36	0.46	0.10	0.36	0.56

REV. X1

BPF-A730+

100104

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Band Pass Filter

BPF-A730+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
670	13.37	12.88	12.34
674	12.78	12.30	11.75
675	12.64	12.16	11.60
678	12.17	11.69	11.14
680	11.85	11.40	10.85
684	11.24	10.82	10.30
685	11.10	10.68	10.16
688	10.68	10.29	9.80
690	10.41	10.04	9.59
694	9.95	9.63	9.23
695	9.84	9.52	9.15
698	9.54	9.26	8.95
700	9.37	9.12	8.83
704	9.09	8.87	8.65
705	9.02	8.83	8.61
706	8.96	8.77	8.57
708	8.86	8.68	8.51
710	8.74	8.60	8.46
714	8.58	8.47	8.38
715	8.53	8.44	8.36
716	8.51	8.43	8.36
718	8.46	8.38	8.33
720	8.39	8.32	8.30
724	8.28	8.25	8.25
725	8.26	8.23	8.24
726	8.27	8.23	8.24
728	8.21	8.20	8.22
730	8.17	8.17	8.20
734	8.13	8.14	8.18
735	8.11	8.13	8.17
736	8.10	8.11	8.17
738	8.08	8.10	8.15
740	8.04	8.07	8.12
744	8.01	8.05	8.11
745	8.01	8.05	8.11
748	7.98	8.03	8.10
750	7.97	8.03	8.10
754	7.96	8.04	8.13
755	7.96	8.04	8.14
758	7.95	8.04	8.16
760	7.97	8.07	8.20
764	8.00	8.14	8.29
765	8.02	8.15	8.33
768	8.05	8.24	8.43
770	8.11	8.32	8.55
774	8.26	8.51	8.80
775	8.30	8.58	8.88
778	8.48	8.81	9.16
780	8.63	8.99	9.37
784	9.01	9.41	9.81
785	9.13	9.54	9.94
788	9.50	9.92	10.28
790	9.78	10.17	10.46
794	10.35	10.60	10.69
795	10.50	10.68	10.70

REV. X1
BPF-A730+
100104
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



Typical Performance Curves




Case Style

HQ

Outline Dimensions

HQ1157



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
HQ1157	.365 (9.27)	1.360 (34.54)	.350 (8.89)	.100 (2.54)	.180 (4.57)	.140 (3.56)	.100 (2.54)	.100 (2.54)	.305 (7.75)	.150 (3.81)	.120 (3.05)	.275 (6.99)

CASE#	N	P	Q	WT.GRAM
HQ1157	.152 (3.87)	.405 (10.29)	1.400 (35.56)	4.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F83



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
56	16	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101212	NEW RELEASE (FROM RAVON)	11/05	DK	YB
A	M108938	SWITCH HATCHES	12/06	DK	HH
B	M118075	CHANGE LINE PLACES	06/08	HB	HH
C	M173459	CORRECTED CASE STYLE & TB PART#	03/27/19	ITG	IL

**SUGGESTED MOUNTING CONFIGURATION
FOR HQ1157 CASE STYLE, rf PIN CONNECTION**



NOTE:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	HB (RAVON)	12 JUN 2008
	CHECKED	RZ (RAVON)	12 JUN 2008
	APPROVED	HH (RAVON)	12 JUN 2008


Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, rf, HQ1157, TB-363+, 50 OHM


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-227	REV: C
FILE: 98PL227	SCALE: 2:1	SHEET: 1 OF 1	

Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Evaluation Board and Circuit



TB-363+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent,
Dielectric Constant=3.48, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D