

# Surface Mount Bandpass Filter

50Ω 110 to 180 MHz

## Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.2W Max.

Permanent damage may occur if any of these limits are exceeded.

## Pin Connections


INPUT	2
OUTPUT	9
NOT CONNECTED	6,13
GROUND	1, 3, 4, 5, 7,8,10,11,12,14

## Outline Drawing



## Outline Dimensions (inch/mm)




## Demo Board MCL P/N: TB-500+ Suggested PCB Layout (PL-294)



### NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B. DIELECTRIC THICKNESS: .030"±.002"; COPPER: 1/2 OZ EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

# BPF-C141+



Generic photo used for illustration purposes only

CASE STYLE: HU1186

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Features

- Good VSWR, 1.3:1 Typ @ Passband
- Flat Group Delay
- Shielded case
- Aqueous washable


## Applications

- Military communications
- Receivers / Transmitters
- Harmonic rejection


## Bandpass Filter Electrical Specifications (T<sub>AMB</sub> = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 2dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB	Loss 40dB Typ.			Passband	Stopband	
F <sub>c</sub>	F <sub>1</sub> - F <sub>2</sub>	F <sub>3</sub>	F <sub>4</sub>	F <sub>5</sub>	F <sub>6</sub>	Typ.	Max.	Typ.
141	110 - 180	92	213	90	217 - 2500	1.3	1.7	18

## Typical Frequency Response



## Functional Schematic



## Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
	$\bar{x}$	$\sigma$			
0.5	72.15	0.59	0.01	108.0	25.97
90.0	44.81	2.20	1.10	110.0	22.54
92.0	37.23	1.95	1.28	113.6	18.47
96.0	17.01	1.27	1.96	116.0	16.79
98.4	9.41	0.97	3.33	120.8	14.45
100.8	4.46	0.58	6.68	126.4	12.72
103.2	2.27	0.22	12.23	132.0	11.63
110.0	1.07	0.03	31.61	137.6	10.90
120.8	0.74	0.01	25.27	141.0	10.62
141.0	0.75	0.03	15.86	148.8	10.31
160.0	0.79	0.03	17.53	153.6	10.37
180.0	1.12	0.03	14.39	154.4	10.38
199.2	3.19	0.28	13.24	160.0	10.70
204.0	8.23	0.82	5.73	165.6	11.09
208.8	18.43	1.13	2.45	171.2	11.67
213.0	30.56	1.54	1.30	176.8	12.52
217.0	42.20	1.22	1.00	180.0	13.48
2500.0	45.14	1.32	0.24	188.0	16.72

# Surface Mount Band Pass Filter

# BPF-C141+

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
0.5	71.96	72.74	72.28	0.00	0.00	0.00	0.01	0.01	0.00
10	46.28	46.28	46.28	0.00	0.00	0.00	0.01	0.02	0.03
20	41.64	41.61	41.59	0.00	0.01	0.01	0.05	0.08	0.10
30	40.79	40.82	40.82	0.01	0.02	0.02	0.13	0.18	0.21
40	43.61	43.75	43.87	0.03	0.04	0.04	0.25	0.31	0.34
50	61.75	62.15	62.99	0.05	0.06	0.07	0.38	0.44	0.47
60	43.38	43.39	43.32	0.09	0.11	0.12	0.48	0.55	0.59
70	38.78	38.80	38.77	0.16	0.19	0.21	0.54	0.64	0.71
80	45.33	45.73	46.02	0.29	0.34	0.38	0.61	0.75	0.84
90	47.46	47.65	47.50	0.62	0.72	0.80	0.80	0.98	1.10
92	39.47	37.88	36.77	0.75	0.88	0.98	0.89	1.08	1.21
96	18.89	18.37	17.96	1.32	1.56	1.74	1.28	1.56	1.73
100	6.70	6.58	6.47	4.05	4.70	5.19	3.55	4.13	4.53
110	1.03	1.19	1.30	21.14	20.92	20.79	19.64	19.49	19.35
120	0.73	0.86	0.95	24.10	24.43	24.47	22.00	21.81	21.57
130	0.70	0.82	0.89	18.06	18.23	18.35	18.30	18.27	18.18
140	0.72	0.84	0.92	15.83	15.83	15.79	16.22	16.11	15.92
141	0.72	0.84	0.92	15.80	15.80	15.75	16.16	16.05	15.86
150	0.72	0.84	0.93	16.83	16.87	16.79	16.76	16.66	16.38
160	0.74	0.88	0.97	20.23	20.19	19.92	18.70	18.40	17.93
170	0.85	1.00	1.10	18.41	18.80	18.96	17.18	17.31	17.28
180	1.05	1.23	1.33	16.05	16.92	17.72	16.01	16.83	17.62
190	1.33	1.59	1.76	21.71	23.44	25.39	22.45	24.32	26.63
200	3.12	3.80	4.32	11.46	10.79	10.23	13.34	12.85	12.33
204	7.38	8.50	9.38	4.22	4.18	4.12	5.35	5.36	5.25
210	20.96	22.29	23.35	1.32	1.50	1.61	1.81	2.01	2.09
213	30.27	31.75	32.93	0.98	1.15	1.26	1.34	1.51	1.59
215	38.46	39.85	40.79	0.86	1.01	1.11	1.14	1.30	1.38
217	45.22	44.19	43.49	0.77	0.91	1.01	0.99	1.14	1.22
250	53.64	53.73	53.82	0.40	0.47	0.52	0.34	0.43	0.46
300	64.65	63.99	63.44	0.38	0.44	0.47	0.16	0.26	0.30
400	49.40	49.32	49.31	0.31	0.39	0.45	0.06	0.16	0.20
500	53.46	53.60	53.56	0.23	0.34	0.40	0.02	0.13	0.18
600	59.97	60.16	60.28	0.21	0.33	0.40	0.00	0.13	0.18
700	74.85	74.54	75.25	0.22	0.36	0.43	0.00	0.14	0.20
800	49.01	49.95	50.82	0.25	0.41	0.49	0.02	0.18	0.24
900	58.96	59.11	59.05	0.29	0.47	0.56	0.00	0.18	0.25
950	52.75	52.52	52.33	0.36	0.55	0.66	0.02	0.19	0.26
1000	47.14	48.39	49.54	0.54	0.71	0.79	0.01	0.20	0.27
1100	61.28	62.23	62.24	0.36	0.56	0.66	0.03	0.22	0.30
1200	62.94	63.46	64.04	0.38	0.58	0.69	0.03	0.24	0.32
1300	68.40	71.90	71.05	0.39	0.59	0.70	0.25	0.40	0.45
1400	68.07	69.15	69.45	0.38	0.58	0.70	0.05	0.28	0.36
1500	70.57	74.52	71.91	0.36	0.57	0.69	0.06	0.30	0.40
1600	62.67	64.22	64.56	0.35	0.56	0.68	0.08	0.32	0.43
1700	62.38	60.08	64.08	0.34	0.53	0.66	0.08	0.34	0.46
1800	67.41	71.01	66.48	0.31	0.52	0.62	0.08	0.34	0.49
1900	66.44	60.39	65.65	0.30	0.50	0.60	0.08	0.36	0.52
2000	62.61	60.63	59.68	0.30	0.49	0.61	0.09	0.37	0.54
2100	61.67	62.41	60.16	0.31	0.51	0.61	0.09	0.39	0.56
2200	58.79	55.22	58.96	0.46	0.60	0.70	0.09	0.39	0.57
2300	57.04	58.00	56.71	0.33	0.49	0.61	0.08	0.41	0.58
2400	51.29	54.49	50.55	0.37	0.52	0.65	0.07	0.41	0.59
2500	58.11	49.13	60.01	0.44	0.61	0.73	0.05	0.43	0.57

REV. X1  
BPF-C141+  
100331  
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Surface Mount Band Pass Filter

# BPF-C141+

## Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
108.0	26.87	26.74	26.10
108.5	26.15	25.52	25.23
109.0	25.37	24.83	24.54
109.5	24.18	23.82	23.40
110.0	23.33	22.66	22.46
110.5	22.56	22.25	22.09
111.0	21.83	21.47	21.34
111.5	21.40	21.33	20.90
112.0	20.72	20.40	20.18
112.5	20.49	20.08	19.92
113.0	19.57	19.50	19.15
113.5	19.33	18.86	19.05
114.0	18.85	19.07	18.67
114.5	18.34	18.13	18.19
115.0	18.14	18.06	17.91
117.5	16.62	16.49	16.41
120.0	15.39	15.29	15.22
122.5	14.38	14.27	14.25
125.0	13.59	13.58	13.49
127.5	12.85	12.87	12.80
130.0	12.26	12.24	12.22
132.5	11.81	11.79	11.84
135.0	11.43	11.42	11.42
137.5	11.09	11.07	11.03
140.0	10.88	10.89	10.84
141.0	10.84	10.88	10.84
142.0	10.81	10.78	10.80
143.0	10.71	10.76	10.72
144.0	10.67	10.68	10.73
145.0	10.71	10.62	10.57
147.5	10.57	10.57	10.57
150.0	10.59	10.55	10.60
152.5	10.57	10.55	10.51
155.0	10.68	10.66	10.65
157.5	10.73	10.75	10.69
160.0	10.86	10.92	10.88
162.5	10.92	10.97	10.91
165.0	11.17	11.19	11.19
167.5	11.55	11.51	11.57
170.0	11.73	11.72	11.79
175.0	12.36	12.43	12.58
176.0	12.60	12.69	12.73
177.0	12.74	12.83	12.96
178.0	12.95	13.25	13.20
179.0	13.29	13.52	13.52
180.0	13.42	13.65	13.81
181.0	13.84	13.90	14.25
182.0	14.06	14.21	14.35
183.0	14.76	14.93	15.11
184.0	14.90	15.24	15.28
185.0	15.27	15.51	15.90
186.0	16.08	16.21	16.50
187.0	16.66	16.78	17.03
188.0	17.15	17.32	17.60

REV. X1  
BPF-C141+  
100331  
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


### INSERTION LOSS vs. TEMPERATURE




### INPUT RETURN LOSS vs. TEMPERATURE



### OUTPUT RETURN LOSS vs. TEMPERATURE




## Typical Performance Curves




## Outline Dimensions

HU1186



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm 0.002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT, GRAM
HU1186	.870 (22.10)	.800 (20.32)	.25 (6.35)	.100 (2.54)	.097 (2.46)	-	.060 (1.52)	.040 (1.02)	.105 (2.67)	.910 (23.11)	-	.060 (1.52)	.060 (1.52)	-	2.85

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:  
For RoHS Case Styles: 2-5  $\mu$  inch (.05-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate.  
For RoHS-5 Case Styles: Tin-Lead plate.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F21



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	32	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M119979	NEW RELEASE (FROM RAVON)	11/08	DK	HH
OR	R74463	NEW RELEASE (FROM RAVON)	11/08	DK	HH

**SUGGESTED MOUNTING CONFIGURATION FOR HU1186 CASE STYLE, "14FL03" PIN CODE**



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B, DIELECTRIC THICKNESS: .030" ± .002"; COPPER: 1/2 OZ ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN DK (RAVON)	02 NOV 08
TOLERANCES ON:	CHECKED DH (RAVON)	02 NOV 08
2 PL DECIMALS ±	APPROVED HH (RAVON)	02 NOV 08
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		

**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235



**PL, 14FL03, HU1186, BPF-C  
TB-500+ (50 OHM)**

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-294	REV: OR
FILE: 98PL294	SCALE: 3:1	SHEET: 1 OF 1	

Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.




# Evaluation Board and Circuit



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent.  
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D