


# Surface Mount Bandpass Filter

## BPF-A355+

50Ω 310 to 400 MHz



Generic photo used for illustration purposes only

CASE STYLE: HQ1157

### The Big Deal

- Broader bandwidth
- High Rejection
- Good VSWR, 1.2:1 typical
- Miniature shielded package

### Product Overview

BPF-A355+ is a 50Ω bandpass filter in a shielded package fabricated using SMT technology. This bandpass filter covers from 310 to 400 MHz. This filter build with high Q capacitors and wire welded inductors for high reliability. This filter has fast roll-off and general application in the UHF range

### Key Features

Feature	Advantages
Low insertion loss	Can be used in industrial and medical application
Good rejection	This enables the filter attenuate spurious signals and reject harmonics for broad frequency band
Shielded package	The small surface mount package enables the BPF-A355+ to used in compact design

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Surface Mount Bandpass Filter

## BPF-A355+

50Ω 310 to 400 MHz



Generic photo used for illustration purposes only  
CASE STYLE: HQ1157

### Features

- Broader bandwidth
- High rejection
- Miniature shielded package

### Applications

- UHF antenna
- Radio link
- Transmitters / Receivers

### Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Center Frequency	—	—	355	—	MHz	
	Insertion Loss	F1-F2	310-400	—	1.90	3.50	dB
	VSWR	F1-F2	310-400	—	1.22	1.92	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-237	20	27	—	dB
	VSWR	DC-F3	DC-237	—	20	—	:1
Stop Band, Upper	Insertion Loss	F4-F5	450-1400	20	30	—	dB
	VSWR	F4-F5	450-1400	—	20	—	:1

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.8W

Permanent damage may occur if any of these limits are exceeded.

### Functional Schematic



### Typical Frequency Response







### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	56.16	868.59	310	9.96
201	74.51	86.86	315	9.65
211	58.58	72.39	320	9.42
237	29.66	39.49	325	9.25
249	19.42	25.19	330	9.14
265	7.19	6.71	335	9.06
273	3.28	2.78	340	9.02
300	1.14	1.13	345	9.03
310	1.08	1.10	350	9.08
355	1.15	1.17	355	9.19
400	1.77	1.12	356	9.21
411	3.18	1.89	360	9.35
420	7.37	3.62	365	9.57
427	12.75	5.25	370	9.85
435	19.95	6.81	375	10.19
445	29.71	8.90	380	10.62
450	34.93	10.07	385	11.16
570	73.46	35.46	390	11.88
750	64.45	29.46	395	12.89
1400	65.76	27.59	400	14.31

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.B  
M174392  
BPF-A355+  
EDU1841  
URJ  
190620  
Page 2 of 3

## Pad Connections

INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7,9,10,11,12,13,14

**Demo Board MCL P/N: TB-363+**  
**Suggested PCB Layout (PL-227)**




**NOTE:**

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

## Outline Drawing



## Outline Dimensions (inch / mm)

A	B	C	D	E	F	G	H
.365	1.360	.35	.100	.180	.140	.100	.100
9.27	34.54	8.89	2.54	4.57	3.56	2.54	2.54
J	K	L	M	N	P	Q	Wt.
.305	.150	.120	.275	.152	.405	1.400	grams
7.75	3.81	3.05	6.99	3.86	10.29	35.56	4.0

*Note: Please refer to case style drawing for details*

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

*Typical Performance Data*

FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	56.67	56.16	61.41	0.00	0.02	0.02	0.04	0.03	0.03
10	78.34	77.76	72.18	0.00	0.00	0.00	0.00	0.01	0.01
47	60.14	60.21	60.22	0.01	0.02	0.02	0.12	0.15	0.16
81	60.84	60.89	60.96	0.02	0.03	0.05	0.35	0.41	0.45
113	83.35	80.74	82.63	0.03	0.05	0.07	0.46	0.53	0.58
133	62.37	62.34	62.41	0.04	0.07	0.09	0.43	0.52	0.58
159	58.57	58.60	58.65	0.07	0.11	0.13	0.42	0.53	0.61
167	59.07	59.17	59.07	0.08	0.12	0.14	0.44	0.55	0.63
205	69.21	68.52	67.72	0.17	0.22	0.25	0.73	0.86	0.95
215	53.28	52.90	52.41	0.21	0.26	0.29	0.85	0.99	1.07
237	29.92	29.66	29.40	0.36	0.44	0.48	1.06	1.25	1.36
247	21.38	21.08	20.80	0.53	0.63	0.70	1.16	1.39	1.54
249	19.72	19.42	19.14	0.58	0.69	0.77	1.19	1.43	1.60
255	14.87	14.55	14.25	0.85	1.01	1.12	1.38	1.66	1.88
274	2.93	2.97	2.96	6.48	7.27	8.00	6.56	7.25	7.90
278	1.97	2.10	2.16	9.76	10.70	11.64	9.66	10.34	11.02
291	1.06	1.25	1.38	22.97	22.52	22.24	22.31	21.10	20.40
299	0.96	1.15	1.28	26.71	24.45	22.80	27.35	24.60	22.74
305	0.93	1.11	1.24	27.13	25.32	23.58	28.92	26.66	24.46
306	0.92	1.10	1.23	27.13	25.48	23.78	29.03	27.01	24.82
310	0.91	1.08	1.21	27.09	26.15	24.75	29.12	28.38	26.45
321	0.89	1.06	1.18	27.65	27.34	27.10	28.88	30.35	31.83
323	0.88	1.06	1.18	27.90	27.24	26.93	29.01	30.18	31.76
332	0.88	1.07	1.19	28.47	25.39	23.99	29.92	27.88	26.97
339	0.89	1.08	1.22	27.06	23.51	21.70	29.71	25.94	24.00
350	0.92	1.12	1.27	24.31	21.92	20.12	27.52	24.51	22.24
355	0.95	1.15	1.29	23.80	22.01	20.31	26.96	24.75	22.53
360	0.97	1.17	1.32	23.93	22.75	21.19	27.03	25.71	23.60
366	1.00	1.21	1.36	25.05	24.79	23.46	28.03	28.07	26.18
375	1.06	1.27	1.43	28.95	32.16	32.28	30.54	32.36	30.79
381	1.11	1.34	1.51	31.92	41.70	46.72	30.77	30.26	27.99
382	1.12	1.36	1.53	32.19	41.16	41.12	30.66	29.80	27.45
384	1.15	1.39	1.56	32.42	38.52	35.93	30.51	29.10	26.58
388	1.20	1.45	1.64	32.07	35.32	32.20	30.95	28.87	25.90
390	1.23	1.49	1.68	31.84	35.29	32.11	31.87	29.64	26.26
396	1.34	1.62	1.84	28.87	33.60	41.21	36.07	48.77	33.35
400	1.47	1.77	2.01	23.65	24.97	27.23	25.46	26.09	26.78
407	1.95	2.38	2.71	14.60	14.37	14.41	13.91	13.30	12.93
420	6.35	7.37	8.27	4.84	4.92	4.89	3.38	3.24	3.08
435	18.83	19.95	21.00	2.26	2.57	2.73	0.97	1.09	1.14
437	20.73	21.84	22.88	2.12	2.43	2.60	0.90	1.02	1.07
439	22.67	23.76	24.78	2.00	2.30	2.47	0.84	0.96	1.01
450	33.85	34.93	35.92	1.48	1.73	1.91	0.67	0.79	0.84
451	34.92	36.01	37.00	1.44	1.69	1.86	0.66	0.78	0.83
475	67.12	66.03	65.18	0.83	1.01	1.15	0.52	0.62	0.68
505	63.93	64.31	64.88	0.53	0.68	0.79	0.43	0.53	0.59
560	74.51	73.55	73.75	0.37	0.50	0.58	0.34	0.44	0.51
700	65.13	65.12	65.17	0.43	0.54	0.59	0.23	0.35	0.44
820	62.62	65.76	62.94	0.54	0.67	0.77	0.20	0.34	0.45
835	62.67	62.93	63.19	0.53	0.68	0.78	0.20	0.34	0.45
995	70.96	71.18	72.11	0.46	0.69	0.88	0.20	0.36	0.48
1125	101.69	95.96	92.76	0.40	0.66	0.84	0.21	0.38	0.51
1150	84.73	85.70	83.66	0.40	0.65	0.83	0.21	0.39	0.52
1175	79.71	79.03	80.12	0.39	0.64	0.82	0.21	0.39	0.52
1200	76.89	76.91	76.87	0.39	0.64	0.82	0.22	0.40	0.53
1225	74.88	74.16	74.81	0.39	0.63	0.81	0.22	0.40	0.53
1250	72.95	73.51	73.19	0.39	0.63	0.80	0.22	0.40	0.54
1300	70.18	70.51	70.81	0.39	0.63	0.79	0.24	0.41	0.54
1325	68.99	69.54	69.77	0.39	0.63	0.78	0.24	0.42	0.55
1400	65.36	65.76	66.11	0.40	0.63	0.77	0.25	0.43	0.56



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site







The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS


*Typical Performance Data*

FREQ.  (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
310	9.99	9.96	9.93
313	9.78	9.76	9.74
316	9.61	9.60	9.59
319	9.46	9.46	9.46
320	9.42	9.42	9.42
321	9.38	9.38	9.39
323	9.31	9.31	9.32
324	9.27	9.28	9.29
325	9.25	9.25	9.27
327	9.19	9.20	9.21
328	9.17	9.17	9.19
329	9.15	9.15	9.17
332	9.09	9.10	9.11
336	9.04	9.05	9.06
343	9.02	9.02	9.03
348	9.04	9.05	9.07
349	9.05	9.07	9.08
350	9.06	9.08	9.09
351	9.08	9.10	9.12
357	9.22	9.25	9.27
358	9.25	9.28	9.31
359	9.28	9.32	9.35
360	9.31	9.35	9.38
361	9.35	9.39	9.43
362	9.39	9.43	9.47
365	9.52	9.57	9.62
366	9.56	9.62	9.67
367	9.61	9.67	9.73
369	9.72	9.79	9.85
370	9.78	9.85	9.92
371	9.83	9.91	9.98
372	9.90	9.98	10.05
373	9.97	10.04	10.12
374	10.04	10.12	10.20
375	10.11	10.19	10.27
376	10.19	10.27	10.36
377	10.27	10.35	10.44
378	10.35	10.44	10.53
379	10.43	10.53	10.62
380	10.53	10.62	10.72
381	10.62	10.72	10.82
382	10.72	10.82	10.92
383	10.82	10.93	11.04
384	10.94	11.05	11.16
385	11.05	11.16	11.27
386	11.17	11.29	11.42
387	11.30	11.43	11.55
388	11.44	11.57	11.70
389	11.59	11.72	11.86
390	11.74	11.88	12.03
391	11.91	12.06	12.22
392	12.08	12.25	12.41
393	12.27	12.45	12.62
394	12.47	12.67	12.85
395	12.68	12.89	13.09
396	12.91	13.14	13.36
397	13.16	13.40	13.64
398	13.42	13.68	13.94
399	13.71	13.99	14.27
400	14.01	14.31	14.61

## Typical Performance Curves



## Typical Performance Curves




# Case Style

# HQ

## Outline Dimensions

## HQ1157



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
HQ1157	.365 (9.27)	1.360 (34.54)	.350 (8.89)	.100 (2.54)	.180 (4.57)	.140 (3.56)	.100 (2.54)	.100 (2.54)	.305 (7.75)	.150 (3.81)	.120 (3.05)	.275 (6.99)

CASE#	N	P	Q	WT.GRAM
HQ1157	.152 (3.87)	.405 (10.29)	1.400 (35.56)	4.0

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:  
 For RoHS Case Styles: 3-5  $\mu$  inch (.08-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate.  
 For RoHS-5 Case Styles: Tin-Lead plate.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



# Tape & Reel Packaging TR-F83



<b>Tape Width, mm</b>	<b>Device Cavity Pitch, mm</b>	<b>Reel Size, inches</b>	<b>Devices per Reel</b>
56	16	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101212	NEW RELEASE (FROM RAVON)	11/05	DK	YB
A	M108938	SWITCH HATCHES	12/06	DK	HH
B	M118075	CHANGE LINE PLACES	06/08	HB	HH
C	M173459	CORRECTED CASE STYLE & TB PART#	03/27/19	ITG	IL

**SUGGESTED MOUNTING CONFIGURATION  
FOR HQ1157 CASE STYLE, rf PIN CONNECTION**



**NOTE:**

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	HB (RAVON)	12 JUN 2008
	CHECKED	RZ (RAVON)	12 JUN 2008
	APPROVED	HH (RAVON)	12 JUN 2008


**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

**PL, rf, HQ1157, TB-363+, 50 OHM**


SIZE <b>A</b>	CODE IDENT <b>15542</b>	DRAWING NO: <b>98-PL-227</b>	REV: <b>C</b>
FILE: <b>98PL227</b>	SCALE: <b>2:1</b>	SHEET: <b>1 OF 1</b>	

Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

# Evaluation Board and Circuit




TB-363+



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent,  
Dielectric Constant=3.48, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D