

Surface Mount Bandpass Filter

50Ω 60 to 90 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W Max.

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT	2
OUTPUT	9
NOT CONNECTED	6, 13
GROUND	1, 3, 4, 5, 7, 8, 10, 11, 12, 14

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	G	H	J	K	M	N	wt.
.870	.800	.25	.100	.097	.060	.040	.105	.910	.060	.060	grams
22.10	20.32	6.35	2.54	2.46	1.52	1.02	2.67	23.11	1.52	1.52	2.85




Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-500+
Suggested PCB Layout (PL-294)



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B, DIELECTRIC THICKNESS: .030"±.002"; COPPER: 1/2 OZ EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

BPF-C75+



Generic photo used for illustration purposes only
CASE STYLE: HU1186

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Features

- High rejection
- Good VSWR, 1.2:1 typ @ passband
- Shielded case
- Aqueous washable


Applications

- Industrial microwave and RF
- Receivers / transmitters
- Harmonic rejection


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 3dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss > 40dB		Passband		Stopband
F _c	F ₁ - F ₂	F ₃	F ₄	F ₅	F ₆	Typ.	Max.	Typ.
75	60 - 90	46	102	42	108 - 1800	1.2	1.6	18

Typical Frequency Response



Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
	\bar{x}	σ			
0.5	79.67	1.09	0.01	60.0	40.28
42.0	63.82	3.90	0.41	62.0	35.98
46.0	37.45	5.83	0.59	64.0	32.52
53.0	11.02	3.22	3.86	66.0	30.64
55.0	5.30	2.56	5.74	68.0	29.36
57.0	2.41	1.17	10.55	70.0	28.50
60.0	1.06	0.16	19.07	72.0	26.84
66.0	0.83	0.05	25.39	74.0	27.19
75.0	0.95	0.04	19.29	75.0	27.77
80.0	1.10	0.05	24.31	76.0	28.24
90.0	2.09	0.09	26.65	78.0	28.76
93.0	4.17	0.46	12.07	80.0	29.98
95.0	8.13	0.86	5.05	82.0	30.52
97.0	14.22	0.93	3.53	84.0	32.29
102.0	30.02	1.06	1.07	86.0	35.19
108.0	51.30	1.66	0.67	87.0	37.89
500.0	61.34	5.48	0.31	88.0	38.39
1800.0	49.59	0.61	0.85	90.0	45.97

Surface Mount Band Pass Filter

BPF-C75+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
0.5	78.24	78.14	77.80	0.00	0.00	0.00	0.00	0.01	0.01
10	54.52	54.55	54.50	0.00	0.01	0.00	0.03	0.05	0.06
20	59.90	59.67	60.01	0.01	0.02	0.02	0.15	0.18	0.21
30	57.98	57.99	58.19	0.04	0.05	0.05	0.30	0.33	0.35
40	61.89	61.61	61.54	0.11	0.12	0.14	0.39	0.44	0.49
42	63.96	63.85	64.56	0.14	0.15	0.17	0.41	0.47	0.53
46	40.96	40.54	40.21	0.22	0.24	0.27	0.49	0.57	0.64
50	23.73	23.52	23.40	0.39	0.42	0.47	0.71	0.79	0.86
52	16.69	16.52	16.47	0.62	0.68	0.74	0.99	1.07	1.15
53	13.35	13.21	13.17	0.87	0.94	1.02	1.26	1.35	1.44
54	10.18	10.05	10.03	1.32	1.42	1.52	1.73	1.85	1.95
55	7.27	7.16	7.15	2.14	2.29	2.44	2.58	2.75	2.89
56	4.82	4.74	4.74	3.61	3.85	4.09	4.07	4.33	4.56
57	3.01	2.96	2.99	6.07	6.46	6.85	6.55	6.98	7.37
58	1.89	1.89	1.94	9.84	10.48	11.12	10.31	11.01	11.74
60	1.06	1.12	1.20	24.51	26.91	29.14	23.88	26.79	31.27
66	0.81	0.87	0.94	22.28	22.84	23.79	25.14	26.47	28.48
70	0.80	0.87	0.95	21.10	20.61	20.20	22.50	22.01	21.40
75	0.89	0.97	1.07	17.95	17.41	16.81	18.12	17.51	16.75
80	0.96	1.04	1.14	22.48	22.29	22.09	22.23	21.88	21.28
85	1.19	1.29	1.41	26.01	25.30	24.35	24.73	23.93	22.64
90	1.82	1.98	2.17	26.75	27.16	27.32	23.53	22.26	20.76
93	3.82	4.18	4.53	8.85	8.56	8.42	8.33	7.93	7.64
95	7.94	8.46	8.94	3.92	3.87	3.89	3.36	3.28	3.24
97	13.78	14.33	14.83	2.25	2.30	2.37	1.65	1.68	1.71
100	23.19	23.70	24.16	1.56	1.62	1.70	0.92	0.97	1.02
102	29.52	30.01	30.44	1.39	1.45	1.52	0.75	0.80	0.85
105	39.29	39.79	40.17	1.24	1.30	1.37	0.61	0.67	0.72
108	49.76	50.24	50.67	1.14	1.19	1.25	0.54	0.59	0.64
110	57.02	57.61	57.85	1.08	1.13	1.19	0.51	0.56	0.60
120	61.36	61.28	61.46	0.84	0.90	0.95	0.43	0.47	0.51
130	61.97	62.29	62.17	0.70	0.75	0.79	0.39	0.43	0.46
140	77.56	78.04	77.65	0.63	0.66	0.71	0.37	0.41	0.43
150	63.35	63.17	63.47	0.60	0.62	0.66	0.35	0.39	0.41
160	58.41	58.40	58.39	0.59	0.61	0.64	0.34	0.38	0.40
170	56.29	56.39	56.26	0.60	0.61	0.64	0.32	0.37	0.40
180	55.45	55.45	55.46	0.61	0.62	0.65	0.31	0.36	0.40
190	55.17	55.19	55.31	0.63	0.64	0.67	0.31	0.36	0.39
200	55.38	55.45	55.47	0.65	0.66	0.69	0.30	0.36	0.39
300	62.80	62.93	62.55	0.69	0.77	0.83	0.25	0.33	0.37
400	69.91	70.24	69.39	0.74	0.83	0.91	0.24	0.33	0.38
500	68.51	68.52	67.78	0.79	0.90	0.99	0.25	0.35	0.41
600	73.46	74.48	75.38	0.85	0.99	1.08	0.26	0.38	0.45
700	92.55	85.35	89.07	0.93	1.08	1.19	0.28	0.42	0.49
800	74.07	74.10	73.34	1.00	1.18	1.30	0.30	0.46	0.54
900	66.00	66.07	66.46	1.07	1.26	1.41	0.33	0.50	0.58
1000	62.06	63.40	64.44	1.14	1.34	1.50	0.38	0.56	0.65
1100	73.60	77.55	75.87	1.17	1.38	1.55	0.41	0.61	0.70
1200	75.93	73.30	71.71	1.19	1.39	1.56	0.45	0.66	0.77
1300	87.59	69.05	72.41	1.16	1.37	1.54	0.49	0.71	0.83
1400	77.35	75.44	80.30	1.11	1.33	1.49	0.52	0.76	0.89
1500	73.60	70.80	68.96	1.06	1.27	1.42	0.55	0.81	0.96
1600	69.10	70.12	72.88	1.01	1.23	1.37	0.57	0.85	1.03
1700	61.63	64.44	64.13	0.98	1.18	1.31	0.60	0.89	1.09
1800	69.56	68.70	64.90	0.95	1.16	1.29	0.62	0.91	1.14

REV. X1

BPF-C75+

091124

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Band Pass Filter

BPF-C75+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
60.0	52.11	51.57	51.16
61.0	46.56	46.09	45.73
62.0	42.37	42.03	41.74
63.0	39.30	39.06	38.80
63.5	38.04	37.86	37.70
64.0	37.01	36.88	36.74
64.5	36.10	35.98	35.88
65.0	35.24	35.18	35.10
65.5	34.55	34.46	34.44
66.0	33.91	33.85	33.83
66.5	33.33	33.27	33.25
67.0	32.80	32.77	32.75
67.5	32.34	32.32	32.30
68.0	31.96	31.89	31.93
68.5	31.49	31.43	31.43
69.0	31.14	31.09	31.10
69.5	30.82	30.79	30.77
70.0	30.49	30.44	30.44
70.5	30.23	30.18	30.14
71.0	29.97	29.96	29.87
71.5	29.73	29.67	29.62
72.0	29.50	29.48	29.41
72.5	29.30	29.28	29.21
73.0	29.17	29.13	29.10
73.5	29.06	29.03	28.98
74.0	28.97	28.95	28.89
74.5	28.90	28.87	28.81
75.0	28.88	28.89	28.82
75.5	28.88	28.90	28.84
76.0	28.95	28.96	28.92
76.5	29.02	29.01	29.00
77.0	29.11	29.11	29.14
77.5	29.28	29.31	29.30
78.0	29.44	29.49	29.50
78.5	29.62	29.70	29.69
79.0	29.88	29.93	29.98
79.5	30.17	30.21	30.32
80.0	30.46	30.54	30.63
80.5	30.77	30.87	30.95
81.0	31.14	31.25	31.34
81.5	31.52	31.63	31.75
82.0	31.91	32.07	32.21
82.5	32.37	32.52	32.65
83.0	32.85	33.03	33.15
83.5	33.34	33.56	33.66
84.0	33.92	34.09	34.23
84.5	34.48	34.67	34.83
85.0	35.14	35.35	35.48
85.5	35.81	36.04	36.21
86.0	36.60	36.81	36.95
86.5	37.45	37.69	37.87
87.0	38.48	38.74	38.93
88.0	40.90	41.24	41.49
89.0	44.24	44.71	45.07
90.0	48.76	49.34	49.81

REV. X1
BPF-C75+
091124
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



Typical Performance Curves



REV. X1
BPF-C75+
091124
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Outline Dimensions

HU1186



PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.002

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT, GRAM
HU1186	.870 (22.10)	.800 (20.32)	.25 (6.35)	.100 (2.54)	.097 (2.46)	-	.060 (1.52)	.040 (1.02)	.105 (2.67)	.910 (23.11)	-	.060 (1.52)	.060 (1.52)	-	2.85

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F21



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	32	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M119979	NEW RELEASE (FROM RAVON)	11/08	DK	HH
OR	R74463	NEW RELEASE (FROM RAVON)	11/08	DK	HH

SUGGESTED MOUNTING CONFIGURATION FOR HU1186 CASE STYLE, "14FL03" PIN CODE



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B, DIELECTRIC THICKNESS: .030" ± .002"; COPPER: 1/2 OZ ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	DK (RAVON) 02 NOV 08
	CHECKED	DH (RAVON) 02 NOV 08
	APPROVED	HH (RAVON) 02 NOV 08



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

**PL, 14FL03, HU1186, BPF-C
TB-500+ (50 OHM)**

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-294	REV: OR
FILE: 98PL294	SCALE: 3:1	SHEET: 1 OF 1	

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent.
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D