

# Bandpass Filter

## BPF-A580+

50Ω 520 to 640 MHz

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input*	0.5W at 25°C

\*Passband rating, derate linearly to 0.25W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

### Pin Connections

RF IN	1
RF OUT	8
GROUND	2,-7,9-14

### Outline Drawing



Suggested Layout  
Tolerance to be within ±.002


METALLIZATION SOLDER RESIST

### Outline Dimensions (inch)


A	B	C	D	E	F	G	H
.365	1.360	.35	.100	.180	.140	.100	.100
9.27	34.54	8.89	2.54	4.57	3.56	2.54	2.54
J	K	L	M	N	P	Q	Wt.
.305	.150	.120	.275	.152	.405	1.400	grams
7.75	3.81	3.05	6.99	3.86	10.29	35.56	4.0

Note: Please refer to case style drawing for details

### Demo Board MCL P/N: TB-363+ Suggested PCB Layout (PL-227)



- NOTES:
- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .0027 ± .0002" COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- Linear phase, up to ±6 deg typ @ Fc ± 60 MHz
- High rejection
- Shielded case
- Aqueous washable

### Applications

- Military radio
- Harmonic rejection
- Transmitters/receivers



Generic photo used for illustration purposes only

CASE STYLE: HQ1157


### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


### Bandpass Filter Electrical Specifications (T<sub>AMB</sub> = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 4dB)	STOPBANDS (MHz)				MAXIMUM DEVIATION FROM LINEAR PHASE (deg.)	VSWR (:1)		
		Loss > 20dB		Loss > 40dB			Passband		Stopband
Fc	F1 - F2	F3	F4	F5	F6	Fc ± 60MHz	Typ.	Max.	Typ.
580	520 - 640	440	720	380	760-2500	±11	1.4	1.9	20

### Typical Frequency Response





### Functional Schematic



### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Deviation from Linear Phase (deg.)
0.5	95.26	1980.07	520	3.84
100	76.30	2647.93	525	1.52
380	56.02	53.15	530	-0.14
440	29.37	19.85	540	-1.98
465	16.02	7.35	550	-2.34
480	7.55	4.68	560	-1.72
495	4.19	2.23	570	-0.83
520	2.52	1.63	575	-0.48
550	2.06	1.39	580	0.26
580	1.94	1.32	585	1.02
600	1.99	1.27	590	1.75
640	2.40	1.18	595	2.42
670	5.93	2.39	600	2.96
690	14.73	6.25	610	3.45
720	34.40	17.09	620	2.68
760	54.52	17.82	630	0.01
1000	71.03	23.12	635	-2.33
2500	59.76	27.65	640	-5.52



# Surface Mount Band Pass Filter

# BPF-A580+

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
0.5	89.50	90.09	94.48	0.00	0.00	0.00	0.00	0.01	0.01
100	75.99	75.63	76.45	0.01	0.03	0.05	0.49	0.57	0.61
200	93.97	91.76	97.99	0.06	0.10	0.13	0.53	0.68	0.80
300	77.27	77.18	76.50	0.18	0.22	0.25	0.76	0.93	1.05
380	57.72	57.59	57.48	0.37	0.43	0.48	1.22	1.51	1.76
400	48.86	48.72	48.61	0.46	0.54	0.58	1.05	1.30	1.50
440	27.94	27.78	27.59	0.82	0.95	1.05	1.23	1.50	1.70
450	22.29	22.09	21.85	1.02	1.18	1.31	1.59	1.93	2.19
460	16.50	16.28	16.01	1.39	1.62	1.82	2.23	2.73	3.16
465	13.63	13.42	13.16	1.72	2.00	2.26	2.76	3.39	3.97
470	10.87	10.71	10.50	2.23	2.59	2.94	3.51	4.29	5.07
480	6.32	6.40	6.41	4.21	4.73	5.26	5.84	6.81	7.77
490	3.84	4.12	4.33	7.31	7.81	8.38	8.53	9.09	9.49
495	3.23	3.55	3.79	8.78	9.28	9.88	9.58	9.96	10.20
500	2.85	3.17	3.42	10.04	10.60	11.31	10.51	10.87	11.09
510	2.41	2.72	2.96	12.16	12.93	14.01	12.39	12.98	13.51
520	2.16	2.46	2.70	14.01	14.84	16.06	14.16	15.04	16.08
530	2.00	2.31	2.56	15.26	15.85	16.65	15.29	16.18	17.38
540	1.91	2.23	2.49	15.52	15.73	15.87	15.56	16.14	16.81
550	1.85	2.18	2.45	15.28	15.24	14.95	15.36	15.61	15.66
560	1.80	2.13	2.42	15.37	15.24	14.73	15.37	15.42	15.10
570	1.74	2.07	2.36	16.40	16.30	15.67	16.19	16.19	15.69
580	1.69	2.02	2.31	19.02	19.04	18.30	18.59	18.71	18.15
590	1.66	2.00	2.29	23.53	23.38	22.25	24.60	25.39	24.90
600	1.69	2.05	2.36	22.76	21.74	20.56	33.91	33.09	32.67
620	1.88	2.27	2.61	17.64	17.55	17.00	18.39	18.38	17.98
630	1.98	2.40	2.76	20.46	21.54	22.19	17.67	17.88	17.81
640	2.27	2.76	3.19	17.26	17.00	17.12	14.28	14.07	13.97
650	3.08	3.69	4.24	9.49	9.22	9.00	8.95	8.81	8.66
660	4.39	5.06	5.68	5.67	5.66	5.58	5.72	5.82	5.80
670	5.42	6.00	6.58	4.33	4.55	4.64	4.58	4.93	5.09
680	5.16	5.78	6.48	5.69	6.38	6.68	6.70	7.96	8.75
690	7.55	9.64	11.48	4.98	4.13	3.63	7.27	5.91	5.17
700	17.04	18.98	20.66	1.53	1.65	1.71	2.06	2.24	2.33
720	32.56	33.99	35.24	0.92	1.09	1.19	1.12	1.35	1.49
750	49.84	50.96	51.81	0.87	1.03	1.15	0.89	1.10	1.23
760	54.87	55.80	56.90	0.89	1.06	1.18	0.87	1.07	1.19
800	73.13	71.72	74.01	1.04	1.25	1.44	0.83	1.03	1.17
900	77.73	77.41	78.22	1.08	1.37	1.61	1.02	1.31	1.58
1000	72.12	72.37	72.74	0.68	0.88	1.03	1.56	2.04	2.45
1100	74.95	75.29	76.58	0.53	0.67	0.78	2.21	2.62	2.91
1200	70.17	85.61	64.90	0.48	0.61	0.71	1.95	2.30	2.62
1300	70.10	70.89	68.65	0.46	0.63	0.75	5.02	7.21	9.42
1400	60.20	57.51	60.80	0.49	0.71	0.89	1.37	1.68	1.94
1500	62.77	65.46	64.99	0.53	0.82	1.06	0.87	1.21	1.48
1600	66.25	71.15	70.90	0.57	0.91	1.20	0.71	1.06	1.33
1700	74.98	74.31	77.03	0.60	0.94	1.25	0.62	0.97	1.25
1800	82.67	80.37	87.00	0.60	0.93	1.25	0.54	0.90	1.18
1900	75.97	74.50	75.93	0.58	0.89	1.20	0.49	0.83	1.12
2000	86.61	88.31	84.08	0.55	0.85	1.13	0.44	0.78	1.06
2100	95.23	91.76	81.49	0.52	0.81	1.08	0.40	0.72	1.01
2200	74.84	77.32	77.74	0.49	0.76	1.01	0.35	0.68	0.96
2300	79.70	66.68	73.41	0.46	0.73	0.96	0.33	0.64	0.91
2400	67.76	65.66	68.44	0.44	0.70	0.92	0.30	0.60	0.86
2500	63.81	61.87	61.77	0.42	0.68	0.89	0.26	0.57	0.81

REV. X1

BPF-A580+

091124

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Surface Mount Band Pass Filter

# BPF-A580+

## Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
520	9.58	9.55	9.51
521	9.52	9.48	9.45
522	9.46	9.41	9.38
523	9.39	9.35	9.32
524	9.34	9.28	9.27
525	9.27	9.23	9.20
526	9.22	9.18	9.16
527	9.17	9.12	9.10
528	9.10	9.07	9.03
529	9.05	9.01	8.99
530	8.99	8.96	8.94
531	8.94	8.91	8.88
532	8.90	8.86	8.84
533	8.85	8.81	8.78
534	8.80	8.76	8.73
535	8.75	8.72	8.68
536	8.72	8.68	8.65
537	8.67	8.64	8.61
538	8.63	8.59	8.57
539	8.59	8.56	8.53
540	8.56	8.53	8.50
541	8.52	8.49	8.46
542	8.50	8.46	8.44
543	8.45	8.42	8.39
544	8.42	8.40	8.36
545	8.39	8.36	8.32
546	8.36	8.33	8.29
547	8.33	8.30	8.25
548	8.31	8.28	8.25
549	8.27	8.24	8.20
550	8.25	8.22	8.18
551	8.22	8.19	8.16
552	8.20	8.18	8.14
553	8.17	8.15	8.11
554	8.14	8.13	8.09
555	8.11	8.10	8.05
560	8.09	8.08	8.05
565	8.07	8.07	8.04
570	8.07	8.07	8.05
575	8.07	8.07	8.07
580	8.09	8.10	8.11
585	8.13	8.15	8.16
590	8.18	8.20	8.22
595	8.24	8.27	8.30
600	8.32	8.35	8.38
605	8.41	8.45	8.48
610	8.53	8.58	8.62
615	8.69	8.75	8.80
620	8.91	8.98	9.05
625	9.17	9.26	9.34
630	9.48	9.57	9.66
635	9.79	9.87	9.96
640	10.07	10.14	10.22

REV. X1  
BPF-A580+  
091124  
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


### INSERTION LOSS vs. TEMPERATURE




### INPUT RETURN LOSS vs. TEMPERATURE



### OUTPUT RETURN LOSS vs. TEMPERATURE



## Typical Performance Curves



REV. X1  
BPF-A580+  
091124  
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




# Case Style

# HQ

## Outline Dimensions

## HQ1157



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
HQ1157	.365 (9.27)	1.360 (34.54)	.350 (8.89)	.100 (2.54)	.180 (4.57)	.140 (3.56)	.100 (2.54)	.100 (2.54)	.305 (7.75)	.150 (3.81)	.120 (3.05)	.275 (6.99)

CASE#	N	P	Q	WT.GRAM
HQ1157	.152 (3.87)	.405 (10.29)	1.400 (35.56)	4.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
  - For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
  - For RoHS-5 Case Styles: Tin-Lead plate.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F83



<b>Tape Width, mm</b>	<b>Device Cavity Pitch, mm</b>	<b>Reel Size, inches</b>	<b>Devices per Reel</b>
56	16	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified






# Evaluation Board and Circuit




TB-363+



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent,  
Dielectric Constant=3.48, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D