

# Bandpass Filter

## BPF-A69+

50Ω 55 to 83 MHz

### Maximum Ratings



Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input*	0.5W at 25°C

\*Passband rating, derate linearly to 0.25W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.


### Pin Connections

RF IN	1
RF OUT	8
GROUND	2,3,4,5,6,7,9,10,11,12,13,14

### Outline Drawing



PCB Land Pattern



Suggested Layout  
Tolerance to be within ±.002


METALLIZATION  
 SOLDER RESIST

### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
.365	1.360	.35	.100	.180	.140	.100	.100
9.27	34.54	8.89	2.54	4.57	3.56	2.54	2.54
J	K	L	M	N	P	Q	Wt.
.305	.150	.120	.275	.152	.405	1.400	grams
7.75	3.81	3.05	6.99	3.86	10.29	35.56	4.0

Note: Please refer to case style drawing for details

### Demo Board MCL P/N: TB-363+ Suggested PCB Layout(PL-227)



#### NOTES:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025" ± .002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

#### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

### Features

- Good VSWR, 1.3:1 typ @ passband
- High stop band rejection

### Application

- Harmonic rejection
- Transmitters/receivers



Generic photo used for illustration purposes only

CASE STYLE: HQ1157


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


### Bandpass Filter Electrical Specifications (T<sub>AMB</sub> = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 3dB) F1 - F2	STOPBANDS (MHz)		VSWR (:1)	
		Loss > 20dB F3 F4	Loss > 40dB F5 F6	Passband Max.	Stopband Typ.
69	55 - 83	40 97	32 103 - 500	1.6	20

### Typical Frequency Response





### Functional Schematic



### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1	87.50	1737.18
25	78.02	157.93
32	50.82	69.49
40	28.30	31.03
43	21.02	21.46
48	9.52	7.80
50	5.80	4.30
52	3.40	2.47
55	1.97	1.55
69	1.16	1.15
83	2.03	1.34
85	3.20	2.06
87	5.74	3.37
89	9.56	5.07
94	21.75	8.43
97	29.95	10.31
103	49.46	13.70
120	78.14	18.30
500	53.55	44.55



# Surface Mount Band Pass Filter

# BPF-A69+

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
0.5	96.07	94.68	96.71	0.01	0.01	0.01	0.00	0.00	0.00
2	93.14	91.02	92.18	0.01	0.00	0.01	0.00	0.00	0.00
4	94.17	94.63	96.34	0.01	0.02	0.03	0.05	0.06	0.06
6	90.19	88.53	88.32	0.03	0.03	0.01	0.04	0.03	0.06
8	101.44	98.43	97.46	0.02	0.01	0.02	0.06	0.08	0.09
10	86.86	89.85	88.25	0.02	0.03	0.04	0.10	0.12	0.12
20	74.74	74.85	76.89	0.07	0.07	0.09	0.17	0.21	0.25
30	60.03	60.05	59.56	0.21	0.24	0.27	0.42	0.46	0.51
40	27.40	27.22	27.09	0.53	0.60	0.69	0.74	0.86	0.96
50	5.73	5.81	5.88	4.13	4.49	4.82	4.28	4.66	5.01
60	1.19	1.35	1.48	29.27	29.60	29.54	29.72	29.10	28.45
70	1.10	1.23	1.35	17.76	17.49	17.41	18.18	18.03	17.97
80	1.33	1.47	1.62	20.86	21.10	21.39	22.76	23.27	23.65
90	6.59	7.03	7.41	4.33	4.36	4.42	4.77	4.71	4.81
100	34.37	34.94	35.31	1.05	1.16	1.26	1.13	1.22	1.31
110	63.19	63.42	62.55	0.82	0.91	1.02	0.61	0.66	0.71
120	77.32	76.21	81.95	0.76	0.86	0.95	0.40	0.45	0.50
130	74.56	73.97	77.85	0.72	0.81	0.90	0.27	0.31	0.36
140	76.07	84.82	76.73	0.68	0.78	0.86	0.21	0.25	0.30
150	92.80	86.01	101.11	0.60	0.70	0.77	0.19	0.22	0.26
160	80.46	78.77	78.11	0.53	0.63	0.69	0.18	0.22	0.28
170	80.24	76.42	76.14	0.46	0.55	0.63	0.13	0.17	0.22
180	79.87	74.35	78.39	0.42	0.50	0.57	0.11	0.16	0.23
190	78.10	78.45	79.11	0.36	0.47	0.53	0.12	0.14	0.20
200	83.34	79.57	85.96	0.37	0.42	0.50	0.13	0.19	0.24
210	84.94	83.63	81.64	0.30	0.40	0.45	0.12	0.14	0.20
220	81.29	85.98	87.46	0.29	0.35	0.42	0.10	0.15	0.21
230	85.13	90.41	99.43	0.27	0.34	0.40	0.10	0.15	0.21
240	85.08	92.09	90.66	0.24	0.33	0.39	0.11	0.13	0.20
250	91.25	90.51	85.89	0.24	0.29	0.35	0.11	0.16	0.23
260	87.83	92.88	91.64	0.22	0.30	0.37	0.11	0.15	0.21
270	89.63	87.85	87.62	0.24	0.29	0.36	0.09	0.12	0.18
280	90.93	98.92	95.91	0.22	0.27	0.33	0.11	0.17	0.24
290	87.54	90.36	103.39	0.22	0.29	0.35	0.11	0.14	0.21
300	96.79	100.77	79.12	0.21	0.23	0.32	0.10	0.16	0.22
310	82.18	79.81	84.04	0.20	0.29	0.33	0.08	0.15	0.22
320	83.86	80.62	83.19	0.23	0.30	0.35	0.11	0.12	0.21
330	80.52	82.26	81.57	0.21	0.23	0.31	0.10	0.18	0.24
340	78.41	79.38	77.44	0.22	0.30	0.33	0.11	0.15	0.23
350	77.16	75.97	75.36	0.23	0.25	0.33	0.11	0.15	0.21
360	76.65	73.06	75.57	0.18	0.23	0.28	0.10	0.18	0.24
370	74.61	72.93	74.35	0.24	0.32	0.34	0.10	0.14	0.21
380	73.09	72.65	73.09	0.23	0.24	0.32	0.10	0.15	0.21
390	72.12	72.11	71.54	0.18	0.25	0.28	0.10	0.18	0.24
400	71.77	72.08	69.83	0.24	0.30	0.35	0.10	0.14	0.21
410	70.02	70.76	69.98	0.21	0.24	0.31	0.11	0.16	0.23
420	70.11	70.33	68.64	0.19	0.28	0.29	0.12	0.20	0.26
430	68.68	69.86	69.11	0.26	0.28	0.35	0.10	0.13	0.22
440	69.18	69.79	68.43	0.22	0.24	0.30	0.11	0.18	0.24
450	67.82	67.94	69.53	0.20	0.28	0.30	0.11	0.18	0.26
460	66.90	68.33	68.15	0.27	0.27	0.36	0.10	0.14	0.21
470	67.70	67.00	68.47	0.19	0.26	0.29	0.12	0.20	0.26
480	67.84	67.95	68.07	0.24	0.29	0.32	0.13	0.19	0.26
490	68.57	68.45	68.56	0.28	0.28	0.36	0.10	0.15	0.21
500	67.48	67.81	68.33	0.21	0.28	0.29	0.11	0.20	0.26

REV. X1

BPF-A69+

090226

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Surface Mount Band Pass Filter

# BPF-A69+

## Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
55.0	45.41	44.86	44.47
55.5	43.85	43.45	43.04
56.0	42.40	41.95	41.64
56.5	41.02	40.63	40.36
57.0	39.75	39.44	39.20
57.5	38.61	38.39	38.17
58.0	37.61	37.35	37.17
58.5	36.65	36.52	36.41
59.0	35.98	35.83	35.71
59.5	35.29	35.13	35.01
60.0	34.77	34.65	34.48
60.5	34.17	34.08	33.98
61.0	33.76	33.57	33.45
61.5	33.19	33.11	33.02
62.0	32.78	32.71	32.68
62.5	32.33	32.24	32.25
63.0	32.01	31.94	31.94
63.5	31.68	31.67	31.68
64.0	31.37	31.37	31.29
64.5	31.13	31.12	31.04
65.0	30.91	30.83	30.82
65.5	30.70	30.61	30.64
66.0	30.44	30.39	30.39
66.5	30.31	30.22	30.25
67.0	30.14	30.15	30.13
67.5	30.01	30.06	30.03
68.0	29.90	29.94	29.87
68.5	29.87	29.92	29.82
69.0	29.79	29.77	29.77
69.5	29.73	29.76	29.69
70.0	29.71	29.69	29.64
70.5	29.66	29.66	29.67
71.0	29.63	29.64	29.67
71.5	29.69	29.79	29.76
72.0	29.81	29.80	29.91
72.5	29.91	29.95	30.01
73.0	30.07	30.13	30.12
73.5	30.31	30.32	30.41
74.0	30.43	30.47	30.56
74.5	30.63	30.66	30.70
75.0	30.83	30.92	30.99
75.5	31.14	31.21	31.27
76.0	31.38	31.52	31.48
76.5	31.70	31.83	31.86
77.0	32.11	32.26	32.29
77.5	32.52	32.63	32.70
78.0	32.95	33.08	33.15
78.5	33.41	33.55	33.66
79.0	33.97	34.08	34.18
79.5	34.48	34.68	34.77
80.0	35.12	35.34	35.45
80.5	35.79	36.09	36.19
81.0	36.57	36.83	36.99
82.0	38.25	38.48	38.76
83.0	40.39	40.68	40.93

REV. X1  
BPF-A69+  
090226  
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


### INSERTION LOSS vs. TEMPERATURE



### INPUT RETURN LOSS vs. TEMPERATURE



### OUTPUT RETURN LOSS vs. TEMPERATURE



REV. X1  
BPF-A69+  
090226  
Page 1 of 2




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



## Typical Performance Curves



REV. X1  
BPF-A69+  
090226  
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Case Style

# HQ

## Outline Dimensions

## HQ1157



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
HQ1157	.365 (9.27)	1.360 (34.54)	.350 (8.89)	.100 (2.54)	.180 (4.57)	.140 (3.56)	.100 (2.54)	.100 (2.54)	.305 (7.75)	.150 (3.81)	.120 (3.05)	.275 (6.99)

CASE#	N	P	Q	WT.GRAM
HQ1157	.152 (3.87)	.405 (10.29)	1.400 (35.56)	4.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
  - For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
  - For RoHS-5 Case Styles: Tin-Lead plate.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F83



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
56	16	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101212	NEW RELEASE (FROM RAVON)	11/05	DK	YB
A	M108938	SWITCH HATCHES	12/06	DK	HH
B	M118075	CHANGE LINE PLACES	06/08	HB	HH
C	M173459	CORRECTED CASE STYLE & TB PART#	03/27/19	ITG	IL

**SUGGESTED MOUNTING CONFIGURATION  
FOR HQ1157 CASE STYLE, rf PIN CONNECTION**



**NOTE:**

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025" ± .002". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	HB (RAVON)	12 JUN 2008
	CHECKED	RZ (RAVON)	12 JUN 2008
	APPROVED	HH (RAVON)	12 JUN 2008

**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235


**PL, rf, HQ1157, TB-363+, 50 OHM**

Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-227	C
FILE:	98PL227	SCALE:	2:1
		SHEET:	1 OF 1



# Evaluation Board and Circuit



TB-363+



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent,  
Dielectric Constant=3.48, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D