

# Bandpass Filter

## BPF-A800+

50Ω 795 to 805 MHz

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input*	0.5W at 25°C

\*Passband rating, derate linearly to 0.25W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.


### Pin Connections

RF IN	1
RF OUT	8
GROUND	2,3,4,5,6,7,9,10,11,12,13,14

### Outline Drawing



PCB Land Pattern



Suggested Layout  
Tolerance to be within ±.002


METALLIZATION SOLDER RESIST

### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
.365	1.360	.35	.100	.180	.140	.100	.100
9.27	34.54	8.89	2.54	4.57	3.56	2.54	2.54
J	K	L	M	N	P	Q	Wt.
.305	.150	.120	.275	.152	.405	1.400	grams
7.75	3.81	3.05	6.99	3.86	10.29	35.56	4.0

Note: Please refer to case style drawing for details

### Demo Board MCL P/N: TB-363+ Suggested PCB Layout (PL-227)




NOTES: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025" ± .002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.  
DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

### Features

- Linear phase, up to ±0.3 deg typ @ Fc ± 7.5 MHz
- Good VSWR, 1.3:1 typ @ passband
- High rejection
- Shielded case
- Aqueous washable

### Applications

- Military radio
- Harmonic rejection
- Transmitters/receivers



Generic photo used for illustration purposes only

CASE STYLE: HQ1157


### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


### Bandpass Filter Electrical Specifications (T<sub>AMB</sub> = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 4.5dB)	STOPBANDS (MHz)				MAXIMUM DEVIATION FROM LINEAR PHASE (deg.)	VSWR (:1)		
		Loss > 20dB		Loss > 40dB			Passband		Stopband
Fc	F1 - F2	F3	F4	F5	F6	Fc ± 7.5MHz	Typ.	Max.	Typ.
800	795 - 805	700	900	660	1000-2500	±1	1.3	1.8	20

### Typical Frequency Response






### Functional Schematic



### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Deviation from Linear Phase (deg.)
0.5	92.80	2173.44	792.5	0.15
300	84.93	379.70	793.0	0.15
660	54.83	32.89	793.5	0.14
700	35.84	19.27	794.0	0.12
725	20.14	10.67	795.0	0.08
740	11.89	5.27	796.0	0.05
775	5.28	3.17	797.0	-0.03
795	2.97	1.17	798.0	-0.06
798	2.91	1.13	799.0	-0.13
800	2.90	1.19	800.0	-0.14
802	2.92	1.25	801.0	-0.16
805	2.99	1.31	802.0	-0.14
820	5.55	1.53	803.0	-0.09
835	11.43	2.52	803.5	-0.06
850	18.46	11.66	804.0	-0.03
900	34.54	34.18	805.0	0.04
1000	51.34	42.01	806.0	0.13
2500	56.18	54.41	807.5	0.27



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Surface Mount Band Pass Filter

# BPF-A800+

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
0.5	105.17	95.00	93.76	0.00	0.01	0.01	0.00	0.01	0.00
10	103.11	93.09	97.65	0.01	0.01	0.00	0.00	0.01	0.00
50	92.54	87.06	84.88	0.01	0.01	0.02	0.01	0.02	0.04
100	93.70	89.01	93.32	0.01	0.03	0.05	0.00	0.04	0.07
150	90.68	92.68	89.47	0.02	0.05	0.07	0.00	0.05	0.10
200	99.15	95.86	91.21	0.03	0.08	0.10	0.02	0.09	0.13
250	86.14	91.05	84.57	0.05	0.10	0.12	0.02	0.10	0.14
300	89.22	87.79	83.01	0.06	0.12	0.17	0.06	0.15	0.19
350	81.70	85.36	83.42	0.08	0.13	0.17	0.08	0.17	0.21
400	84.97	88.92	82.74	0.10	0.16	0.21	0.09	0.18	0.22
450	104.52	82.26	82.21	0.13	0.21	0.25	0.10	0.21	0.24
500	82.56	80.11	80.54	0.15	0.23	0.29	0.12	0.23	0.26
560	79.42	82.49	84.43	0.20	0.29	0.34	0.14	0.25	0.28
570	80.68	84.94	90.33	0.20	0.30	0.36	0.14	0.25	0.28
580	82.47	92.30	84.16	0.23	0.32	0.37	0.14	0.25	0.29
590	88.02	89.95	98.38	0.24	0.34	0.38	0.14	0.27	0.30
600	82.62	82.11	80.73	0.24	0.34	0.40	0.15	0.27	0.30
650	58.47	57.84	57.54	0.36	0.48	0.54	0.19	0.32	0.36
660	54.35	53.56	53.13	0.39	0.52	0.58	0.19	0.33	0.38
670	49.91	49.05	48.49	0.44	0.57	0.64	0.22	0.36	0.41
680	45.40	44.37	43.57	0.49	0.64	0.71	0.24	0.40	0.45
690	40.67	39.60	38.56	0.56	0.73	0.83	0.28	0.45	0.52
700	35.47	34.24	33.09	0.66	0.85	0.98	0.34	0.54	0.63
710	29.40	27.96	26.62	0.77	1.03	1.21	0.45	0.71	0.88
725	17.76	15.83	14.14	1.33	1.89	2.45	1.26	2.16	3.18
740	6.15	7.09	7.64	4.80	4.42	4.33	12.18	7.00	5.29
750	7.48	8.04	8.17	3.18	3.60	4.07	2.81	2.83	2.88
760	7.45	7.53	7.41	3.39	4.21	4.98	2.32	2.78	3.19
775	5.00	5.04	4.99	5.50	7.03	8.36	4.15	5.31	6.45
795	2.56	3.11	3.49	17.83	20.78	20.77	18.01	23.81	24.77
798	2.48	3.08	3.52	21.59	23.00	21.71	24.24	26.19	20.47
800	2.44	3.09	3.56	23.74	23.77	22.40	28.80	23.38	18.29
802	2.44	3.13	3.63	24.99	24.52	23.60	27.40	20.78	16.63
805	2.47	3.22	3.78	25.91	26.83	27.14	22.51	17.96	14.61
820	4.01	5.55	6.86	11.40	9.37	8.10	8.24	6.40	5.14
835	10.36	12.27	13.82	2.86	2.89	2.88	1.88	1.79	1.66
850	17.58	19.08	20.31	1.30	1.54	1.67	0.72	0.86	0.89
900	33.57	34.40	35.02	0.51	0.73	0.85	0.25	0.43	0.49
950	42.80	43.27	43.77	0.39	0.56	0.67	0.22	0.41	0.49
1000	49.22	49.60	50.12	0.37	0.53	0.62	0.23	0.45	0.56
1100	56.58	57.16	57.17	0.41	0.57	0.64	0.53	0.86	1.11
1200	62.45	67.79	64.36	0.46	0.62	0.70	1.71	2.39	2.90
1300	70.93	73.36	70.71	0.54	0.70	0.81	1.29	1.63	1.77
1400	71.28	69.36	70.02	0.59	0.80	0.96	0.45	0.70	0.83
1500	57.43	66.00	62.74	0.64	0.90	1.11	0.24	0.48	0.63
1600	61.67	69.46	65.73	0.61	0.91	1.15	0.16	0.42	0.60
1700	66.55	69.46	65.20	0.58	0.88	1.12	0.14	0.42	0.62
1800	66.07	73.80	68.34	0.57	0.84	1.08	0.14	0.47	0.67
1900	77.15	78.61	84.14	0.52	0.79	1.00	0.15	0.49	0.74
2000	84.25	82.33	83.39	0.48	0.75	0.94	0.23	0.62	0.89
2100	82.87	77.09	90.88	0.45	0.69	0.88	0.39	0.85	1.22
2200	68.67	80.52	65.80	0.40	0.65	0.82	1.51	2.42	3.29
2300	62.19	64.91	58.34	0.38	0.62	0.80	2.21	2.49	2.60
2400	70.15	70.05	65.84	0.34	0.58	0.76	0.49	0.95	1.35
2500	59.38	68.80	61.72	0.31	0.56	0.74	0.32	0.84	1.33

REV. X1

BPF-A800+

100105

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Surface Mount Band Pass Filter

# BPF-A800+

## Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
795.00	12.65	12.60	12.46
795.50	12.65	12.61	12.51
796.00	12.66	12.60	12.50
796.50	12.66	12.61	12.55
797.00	12.71	12.68	12.59
797.50	12.70	12.59	12.63
798.00	12.75	12.64	12.63
798.50	12.70	12.59	12.71
799.00	12.71	12.70	12.68
799.50	12.73	12.65	12.73
800.00	12.79	12.71	12.78
800.50	12.73	12.71	12.81
801.00	12.79	12.85	12.83
801.50	12.80	12.75	12.96
802.00	12.81	12.80	12.90
802.50	12.81	12.83	12.93
803.00	12.86	12.90	13.00
803.50	12.83	12.88	13.02
804.00	12.90	13.00	13.13
804.50	12.89	13.05	13.19
805.00	12.92	13.10	13.26

REV. X1  
BPF-A800+  
100105  
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


### INSERTION LOSS vs. TEMPERATURE




### INPUT RETURN LOSS vs. TEMPERATURE



### OUTPUT RETURN LOSS vs. TEMPERATURE



## Typical Performance Curves



# Case Style

# HQ

## Outline Dimensions

## HQ1157



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
HQ1157	.365 (9.27)	1.360 (34.54)	.350 (8.89)	.100 (2.54)	.180 (4.57)	.140 (3.56)	.100 (2.54)	.100 (2.54)	.305 (7.75)	.150 (3.81)	.120 (3.05)	.275 (6.99)

CASE#	N	P	Q	WT.GRAM
HQ1157	.152 (3.87)	.405 (10.29)	1.400 (35.56)	4.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
  - For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
  - For RoHS-5 Case Styles: Tin-Lead plate.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F83



<b>Tape Width, mm</b>	<b>Device Cavity Pitch, mm</b>	<b>Reel Size, inches</b>	<b>Devices per Reel</b>
56	16	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS



REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101212	NEW RELEASE (FROM RAVON)	11/05	DK	YB
A	M108938	SWITCH HATCHES	12/06	DK	HH
B	M118075	CHANGE LINE PLACES	06/08	HB	HH
C	M173459	CORRECTED CASE STYLE & TB PART#	03/27/19	ITG	IL

**SUGGESTED MOUNTING CONFIGURATION  
FOR HQ1157 CASE STYLE, rf PIN CONNECTION**



**NOTE:**

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	HB (RAVON) 12 JUN 2008
	CHECKED	RZ (RAVON) 12 JUN 2008
	APPROVED	HH (RAVON) 12 JUN 2008

 **Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235


PL, rf, HQ1157, TB-363+, 50 OHM

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-227	C
FILE:	98PL227	SCALE:	2:1
SHEET:		1 OF 1	


 Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.



# Evaluation Board and Circuit



TB-363+



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent,  
Dielectric Constant=3.48, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D