


# Surface Mount Bandpass Filter

## BPF-A950+

50Ω 700 to 1200 MHz



Generic photo used for illustration purposes only  
CASE STYLE: HQ1157

### The Big Deal

- Wide bandwidth
- Better rejection
- Miniature shielded package

### Product Overview

The BPF-A950+ is a 50Ω bandpass filter fabricated using SMT technology. This bandpass filter covers from 700-1200 MHz. This filter is built with high Q capacitors and air-coil inductors for superior performance. This filter is developed for square kilometer array telescope systems for radio astronomy. It has repeatable performance across lots and consistent performance across temperature.

### Key Features

Feature	Advantages
Low insertion loss	Can be used in high performance applications such as radio astronomy.
Good rejection	This enables the filter to attenuate spurious signals and reject harmonics for broad frequency band.
Shielded case	Reduced interference with and from the surrounding components.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Surface Mount Bandpass Filter

## BPF-A950+

50Ω 700 to 1200 MHz



Generic photo used for illustration purposes only  
CASE STYLE: HQ1157

### Features

- Wide bandwidth
- Better rejection
- Miniature shielded package

### Applications

- Radio telescope applications
- Aeronautical radio navigation
- Defense systems
- Private and public land mobile

### Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Center Frequency	—	—	950	—	MHz	
	Insertion Loss	F1-F2	700-1200	—	2.0	4.0	dB
	VSWR	F1-F2	700-1200	—	1.5	1.9	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-620	20	30	—	dB
	VSWR	DC-F3	DC-620	—	11	—	:1
Stop Band, Upper	Insertion Loss	F4-F5	1310-2600	20	30	—	dB
	VSWR	F4-F5	1310-2600	—	11	—	:1

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	1 W

Permanent damage may occur if any of these limits are exceeded.

### Functional Schematic



### Typical Frequency Response







### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
10	105.32	1737.18	700	7.29
450	58.94	86.86	730	5.47
620	30.79	28.96	760	4.31
645	15.97	14.87	790	3.68
660	7.94	6.15	810	3.41
670	4.11	2.87	830	3.21
680	2.26	1.56	850	3.06
700	1.43	1.14	880	2.88
810	0.96	1.14	910	2.77
950	1.04	1.33	930	2.72
1140	1.43	1.24	950	2.69
1200	2.21	1.30	980	2.69
1230	5.35	2.50	1010	2.73
1245	10.85	5.72	1040	2.81
1270	23.00	11.93	1070	2.94
1310	49.59	17.22	1100	3.16
1350	42.70	19.54	1130	3.51
1900	53.32	19.76	1160	4.12
2500	61.18	22.29	1180	4.80
2600	60.54	21.20	1200	5.71

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.B  
M174392  
BPF-A950+  
EDU1655  
URJ  
190627  
Page 2 of 3

## Pad Connections

INPUT	1
OUTPUT	8
GROUND	2-7,9-14

Demo Board MCL P/N: TB-363+  
Suggested PCB Layout (PL-227)




### NOTE:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS  $.025 \pm .002$ ". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

## Outline Drawing



## Outline Dimensions ( inch / mm)

A	B	C	D	E	F	G	H
.365	1.360	.35	.100	.180	.140	.100	.100
9.27	34.54	8.89	2.54	4.57	3.56	2.54	2.54
J	K	L	M	N	P	Q	Wt.
.305	.150	.120	.275	.152	.405	1.400	grams
7.75	3.81	3.05	6.99	3.86	10.29	35.56	4.0

Note: Please refer to case style drawing for details

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)







*Typical Performance Data*

FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
10	100.79	105.32	101.85	0.00	0.00	0.00	0.00	0.00	0.00
30	117.25	99.31	93.74	0.01	0.01	0.01	0.01	0.02	0.02
40	120.19	95.97	108.49	0.01	0.01	0.02	0.02	0.03	0.03
100	82.79	83.68	83.17	0.01	0.03	0.04	0.08	0.11	0.13
200	67.20	67.03	67.18	0.04	0.07	0.09	0.29	0.35	0.39
235	63.89	64.13	64.13	0.05	0.08	0.11	0.37	0.44	0.48
275	62.09	62.16	62.29	0.07	0.10	0.14	0.44	0.52	0.57
300	61.76	61.83	61.93	0.08	0.11	0.15	0.46	0.56	0.62
380	72.17	72.16	73.03	0.11	0.15	0.19	0.46	0.57	0.67
395	87.57	85.67	82.96	0.12	0.16	0.20	0.45	0.57	0.67
415	68.07	67.61	67.48	0.14	0.18	0.21	0.45	0.57	0.67
440	60.76	60.79	60.73	0.15	0.19	0.23	0.45	0.58	0.68
465	56.83	56.95	56.99	0.17	0.21	0.24	0.47	0.60	0.70
500	54.70	54.78	54.95	0.20	0.24	0.28	0.51	0.65	0.75
540	57.47	57.68	57.94	0.25	0.29	0.33	0.62	0.77	0.87
570	63.23	62.46	61.96	0.30	0.35	0.39	0.73	0.90	1.01
575	61.83	60.82	60.02	0.31	0.37	0.41	0.75	0.92	1.03
600	44.98	43.93	43.05	0.39	0.46	0.52	0.88	1.08	1.21
620	31.62	30.79	29.98	0.49	0.60	0.69	1.03	1.27	1.43
635	22.54	21.77	20.97	0.65	0.83	0.98	1.22	1.51	1.74
645	16.70	15.97	15.20	0.91	1.17	1.42	1.48	1.85	2.15
660	8.42	7.94	7.42	2.25	2.85	3.48	2.76	3.43	4.08
675	2.90	2.97	2.96	8.03	9.27	10.43	8.17	9.36	10.52
690	1.42	1.64	1.79	22.32	22.80	22.96	18.91	20.00	21.48
695	1.29	1.51	1.66	23.94	24.63	25.42	20.37	21.76	23.87
700	1.21	1.43	1.57	22.19	23.68	25.73	20.24	21.93	24.44
750	0.91	1.11	1.25	20.27	20.28	20.20	19.53	19.74	20.05
810	0.79	0.96	1.09	22.00	23.96	25.62	21.78	24.49	28.87
830	0.76	0.94	1.07	23.59	27.15	34.42	23.22	26.38	32.20
910	0.80	1.00	1.15	17.38	17.73	17.86	17.76	18.18	18.60
950	0.82	1.04	1.20	17.17	16.99	16.35	17.87	18.17	18.00
1010	0.83	1.07	1.27	19.52	18.01	16.40	21.77	20.13	18.19
1030	0.85	1.11	1.31	19.32	17.91	16.51	21.49	19.58	17.85
1110	1.03	1.30	1.50	17.77	18.19	18.26	18.85	19.66	20.69
1130	1.08	1.38	1.61	19.15	19.34	18.54	21.53	23.53	24.46
1200	1.73	2.21	2.58	18.08	17.65	17.94	16.64	15.54	15.02
1210	1.97	2.54	3.01	24.78	25.94	28.06	17.01	15.74	14.92
1215	2.19	2.85	3.43	22.77	21.41	19.07	15.73	14.29	13.09
1235	5.51	6.89	8.18	5.62	5.32	4.93	5.50	5.09	4.70
1250	11.42	13.10	14.61	2.30	2.47	2.52	2.47	2.56	2.59
1265	18.71	20.40	21.94	1.36	1.60	1.74	1.53	1.74	1.87
1275	24.02	25.71	27.30	1.11	1.35	1.50	1.26	1.49	1.64
1285	29.97	31.71	33.42	0.98	1.21	1.35	1.10	1.33	1.49
1300	42.17	44.14	46.27	0.86	1.07	1.21	0.95	1.17	1.33
1310	50.18	49.59	48.75	0.81	1.01	1.14	0.88	1.10	1.26
1330	42.23	42.79	43.31	0.76	0.94	1.05	0.77	1.00	1.16
1400	49.01	50.62	51.70	0.70	0.84	0.93	0.58	0.80	0.98
1425	63.05	73.80	81.12	0.71	0.84	0.94	0.54	0.77	0.95
1435	68.85	62.65	60.20	0.71	0.84	0.93	0.53	0.75	0.94
1500	47.79	47.56	47.55	0.72	0.87	0.99	0.47	0.70	0.89
1600	44.79	44.95	45.08	0.74	0.96	1.14	0.43	0.66	0.86
1650	45.51	45.62	45.82	0.73	0.99	1.20	0.42	0.65	0.85
1775	48.43	49.02	49.28	0.66	0.95	1.20	0.40	0.63	0.83
1800	49.21	50.03	50.23	0.65	0.94	1.18	0.40	0.63	0.82
1900	52.83	53.32	53.79	0.60	0.88	1.10	0.39	0.62	0.80
2100	57.89	58.52	58.86	0.54	0.79	0.98	0.39	0.60	0.78
2200	59.45	59.84	59.77	0.53	0.76	0.95	0.38	0.59	0.75
2400	61.08	60.42	60.71	0.51	0.75	0.93	0.37	0.57	0.72
2500	58.88	61.18	58.22	0.53	0.78	0.97	0.37	0.56	0.72
2600	56.53	60.54	55.42	0.56	0.82	1.05	0.36	0.55	0.70

*Typical Performance Data*

FREQ.  (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
700	7.51	7.29	7.09
710	6.78	6.60	6.45
720	6.13	5.99	5.88
730	5.57	5.47	5.38
740	5.09	5.02	4.96
750	4.69	4.63	4.58
760	4.35	4.31	4.27
770	4.09	4.06	4.02
780	3.88	3.85	3.82
790	3.70	3.68	3.65
800	3.55	3.53	3.52
810	3.42	3.41	3.40
820	3.31	3.30	3.29
830	3.22	3.21	3.20
840	3.14	3.13	3.12
850	3.06	3.06	3.05
860	3.00	2.99	2.99
870	2.94	2.94	2.93
880	2.89	2.88	2.88
890	2.84	2.84	2.84
900	2.80	2.80	2.80
910	2.77	2.77	2.77
920	2.74	2.74	2.74
930	2.72	2.72	2.72
940	2.70	2.70	2.70
950	2.69	2.69	2.69
960	2.69	2.69	2.69
970	2.69	2.69	2.69
980	2.69	2.69	2.69
990	2.70	2.70	2.70
1000	2.72	2.72	2.71
1010	2.73	2.73	2.73
1020	2.75	2.75	2.75
1030	2.77	2.78	2.78
1040	2.80	2.81	2.81
1050	2.84	2.84	2.85
1060	2.87	2.89	2.90
1070	2.92	2.94	2.96
1080	2.98	3.00	3.02
1090	3.04	3.07	3.10
1100	3.13	3.16	3.19
1110	3.22	3.26	3.29
1120	3.33	3.37	3.41
1130	3.47	3.51	3.55
1140	3.62	3.67	3.72
1150	3.81	3.87	3.92
1160	4.05	4.12	4.19
1170	4.34	4.43	4.53
1180	4.68	4.80	4.93
1190	5.08	5.23	5.38
1200	5.54	5.71	5.89


## Typical Performance Curves



# Band Pass Filter

# BPF-A950+

## Typical Performance Curves




# Case Style

# HQ

## Outline Dimensions

## HQ1157



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
HQ1157	.365 (9.27)	1.360 (34.54)	.350 (8.89)	.100 (2.54)	.180 (4.57)	.140 (3.56)	.100 (2.54)	.100 (2.54)	.305 (7.75)	.150 (3.81)	.120 (3.05)	.275 (6.99)

CASE#	N	P	Q	WT.GRAM
HQ1157	.152 (3.87)	.405 (10.29)	1.400 (35.56)	4.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
  - For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
  - For RoHS-5 Case Styles: Tin-Lead plate.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



# Tape & Reel Packaging TR-F83



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
56	16	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101212	NEW RELEASE (FROM RAVON)	11/05	DK	YB
A	M108938	SWITCH HATCHES	12/06	DK	HH
B	M118075	CHANGE LINE PLACES	06/08	HB	HH
C	M173459	CORRECTED CASE STYLE & TB PART#	03/27/19	ITG	IL

**SUGGESTED MOUNTING CONFIGURATION  
FOR HQ1157 CASE STYLE, rf PIN CONNECTION**



**NOTE:**

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025" ± .002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	HB (RAVON)	12 JUN 2008
	CHECKED	RZ (RAVON)	12 JUN 2008
	APPROVED	HH (RAVON)	12 JUN 2008


**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

**PL, rf, HQ1157, TB-363+, 50 OHM**


SIZE <b>A</b>	CODE IDENT <b>15542</b>	DRAWING NO: <b>98-PL-227</b>	REV: <b>C</b>
FILE: <b>98PL227</b>	SCALE: <b>2:1</b>	SHEET: <b>1 OF 1</b>	

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

# Evaluation Board and Circuit




TB-363+



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent,  
Dielectric Constant=3.48, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D